

H TIMING PULLEYS

0.500" Trapezoidal Pitch

For 3" Wide Belts



Iron

Black Oxide Plating


QD® Style



Part Number	No. of Teeth	Type	Pitch Dia. (in)	Out. Dia. (in)	Flange Dia. (in)	Bushing	Face Width (in)	Overall Length (in)
QD22H300	22	E1F	3.501	3.447	3.735	SD	3.375	3.375
QD24H300	24	E1F	3.820	3.766	4.050	SD	3.375	3.375
QD26H300	26	D1F	4.138	4.084	4.369	SD	3.375	3.375
QD28H300	28	D1F	4.456	4.402	4.687	SD	3.375	3.375
QD30H300	30	A1F	4.775	4.721	5.000	SD	3.375	3.375
QD32H300	32	B1F	5.093	5.039	5.320	SK	3.375	3.375
QD36H300	36	B1F	5.730	5.676	5.959	SK	3.375	3.375
QD40H300	40	B1F	6.366	6.312	6.600	SK	3.375	3.375
QD44H300	44	B1F	7.003	6.949	7.231	SK	3.375	3.375
QD48H300	48	B1F	7.639	7.585	7.867	SF	3.375	3.375
QD60H300	60	A3	9.549	9.495	-	SF	3.375	3.375
QD72H300	72	A3	11.459	11.405	-	SF	3.375	3.375
QD84H300	84	A3	13.369	13.315	-	SF	3.375	3.375
QD96H300	96	A3	15.279	15.225	-	E	3.375	3.375
QD120H300	120	A3	19.099	19.045	-	E	3.375	3.375
QD156H300	156	A3	24.828	24.774	-	E	3.375	3.375



For matching QD® bushings, see page 372.



For matching H pitch belts, see page 199.

