


XL TIMING PULLEY BAR STOCK


0.200" / 5.08 mm Pitch

Aluminum



Part Number	No. of Teeth	Metric		Inch		Shank Diameter	Shank Length	Minimum Usable Length	Overall Length
		Pitch Diameter	Outside Diameter	Pitch Diameter	Outside Diameter				
34XL-PS8A	34	55.0 mm	54.5 mm	2.165"	2.145"	0.500"	1.000"	8.000"	9.000"
35XL-PS8A	35	56.6 mm	56.1 mm	2.228"	2.208"	0.750"	1.000"	8.000"	9.000"
36XL-PS8A	36	58.2 mm	57.7 mm	2.292"	2.272"	0.750"	1.000"	8.000"	9.000"
37XL-PS8A	37	59.8 mm	59.3 mm	2.355"	2.335"	0.750"	1.000"	8.000"	9.000"
38XL-PS8A	38	61.4 mm	60.9 mm	2.419"	2.399"	0.750"	1.000"	8.000"	9.000"
40XL-PS8A	40	64.7 mm	64.2 mm	2.546"	2.526"	0.750"	1.000"	8.000"	9.000"
42XL-PS8A	42	67.9 mm	67.4 mm	2.674"	2.654"	0.750"	1.000"	8.000"	9.000"
43XL-PS8A	43	69.5 mm	69.0 mm	2.737"	2.717"	0.750"	1.000"	8.000"	9.000"
44XL-PS8A	44	71.1 mm	70.6 mm	2.801"	2.781"	0.750"	1.000"	8.000"	9.000"
45XL-PS8A	45	72.8 mm	72.3 mm	2.865"	2.845"	0.750"	1.000"	8.000"	9.000"
46XL-PS8A	46	74.4 mm	73.9 mm	2.928"	2.908"	0.750"	1.000"	8.000"	9.000"
48XL-PS8A	48	77.6 mm	77.1 mm	3.056"	3.036"	0.750"	1.000"	8.000"	9.000"
50XL-PS8A	50	80.8 mm	80.3 mm	3.183"	3.163"	0.750"	1.000"	8.000"	9.000"
60XL-PS8A	60	97.0 mm	96.5 mm	3.820"	3.800"	0.750"	1.000"	8.000"	9.000"
62XL-PS8A	62	100.3 mm	99.7 mm	3.947"	3.927"	0.750"	1.000"	8.000"	9.000"
72XL-PS8A	72	116.4 mm	115.9 mm	4.584"	4.564"	1.000"	1.000"	8.000"	9.000"
80XL-PS8A	80	129.4 mm	128.9 mm	5.093"	5.073"	1.000"	1.000"	8.000"	9.000"

g Pulley Stock



For matching XL pitch belts,
see page 187.



For XL pitch timing pulleys,
see page 15.