

T10 TIMING PULLEYS

10 mm Pitch


For 32 mm Wide Belts

Hub




Zinc Plated Steel Flanges

Aluminum

METRIC TIMING PULLEY



Part Number	No. of Teeth	Type	Pitch Dia. (mm)	Out. Dia. (mm)	Flange Dia. (mm)	Bore (mm)	Face Width (mm)	Overall Length (mm)	Hub Dia. (mm)
47T10/18-2	18	6F	57.3	55.5	60.0	10.0	37.0	47.0	40.0
47T10/19-2	19	6F	60.5	58.7	66.0	10.0	37.0	47.0	44.0
47T10/20-2	20	6F	63.7	61.8	66.0	12.0	37.0	47.0	46.0
47T10/24-2	24	6F	76.4	74.6	83.0	12.0	37.0	47.0	58.0
47T10/25-2	25	6F	79.6	77.8	83.0	21.0	37.0	47.0	60.0
47T10/27-2	27	6F	86.0	84.1	91.0	12.0	37.0	47.0	60.0
47T10/30-2	30	6F	95.5	93.7	97.0	12.0	37.0	47.0	60.0
47T10/32-2	32	6F	101.9	100.0	106.0	12.0	37.0	47.0	65.0
47T10/36-2	36	6F	114.6	112.8	119.0	16.0	37.0	47.0	70.0
47T10/40-2	40	6F	127.3	125.5	131.0	16.0	37.0	47.0	80.0
47T10/48-0	48	6	152.8	151.0	-	16.0	37.0	47.0	95.0
47T10/60-0	60	6	191.0	189.2	-	16.0	37.0	47.0	110.0



B&B Manufacturing is equipped to hob pulleys, gears, and sprockets in a large variety of tooth profiles from a large variety of materials. The possibilities are virtually endless with our state-of-the-art machining capabilities. B&B Manufacturing's Custom Shop can handle virtually all precision mechanical component requests.