


QD® BUSHINGS

Steel/Iron



| BORE | KEYWAY |
|-----------------|-----------------|
| 0.500" - 0.563" | 0.125" x 0.063" |
| 0.625" - 0.875" | 0.188" x 0.094" |
| 0.938" - 1.250" | 0.250" x 0.125" |
| 1.438" - 1.750" | 0.375" x 0.188" |
| 1.813" - 2.250" | 0.500" x 0.250" |
| 2.313" - 2.750" | 0.625" x 0.313" |
| 2.813" - 3.250" | 0.750" x 0.375" |
| 3.313" - 3.750" | 0.875" x 0.438" |
| 3.813" - 4.333" | 1.000" x 0.500" |



| Bushing | Bore Range | Dimensions | | | | | | Torque Capacity In-Lbs |
|---------|------------------|------------|---------|---------|---------|---------|---------|---------------------------|
| | | A | B | D | E | F | L | |
| H | 0.438" - 1.500" | 0.250" | 1.625" | 2.500" | 1.000" | 0.875" | 1.250" | 1,750 |
| JA | 0.500" - 1.250" | 0.313" | 1.375" | 2.000" | 0.688" | 0.588" | 1.000" | 1,750 |
| SH | 0.500" - 1.625" | 0.375" | 1.871" | 2.688" | 0.875" | 0.813" | 1.250" | 3,500 |
| SDS | 0.500" - 2.000" | 0.438" | 2.188" | 3.188" | 0.875" | 0.750" | 1.313" | 5,000 |
| SD | 0.500" - 2.000" | 0.438" | 2.188" | 3.188" | 1.375" | 1.250" | 1.813" | 5,000 |
| SK | 0.500" - 2.625" | 0.500" | 2.813" | 3.875" | 1.375" | 1.250" | 1.875" | 7,000 |
| SF | 0.500" - 2.938" | 0.500" | 3.125" | 4.625" | 1.500" | 1.250" | 2.000" | 11,000 |
| E | 0.875" - 3.500" | 0.750" | 3.834" | 6.000" | 1.875" | 1.625" | 2.625" | 20,000 |
| F | 1.000" - 4.000" | 0.813" | 4.438" | 6.625" | 2.813" | 2.500" | 3.625" | 40,000 |
| J | 1.500" - 4.500" | 1.000" | 5.148" | 7.250" | 3.500" | 3.188" | 4.500" | 55,000 |
| M | 2.000" - 5.500" | 1.250" | 6.500" | 9.125" | 5.500" | 5.188" | 6.750" | 125,000 |
| N | 2.438" - 5.875" | 1.500" | 7.000" | 10.000" | 6.625" | 6.250" | 8.125" | 150,000 |
| P | 2.938" - 7.000" | 1.750" | 8.250" | 11.750" | 7.625" | 7.250" | 9.375" | 250,000 |
| W | 4.250" - 8.500" | 2.000" | 10.437" | 15.000" | 9.375" | 9.000" | 11.375" | 375,000 |
| S | 6.000" - 10.000" | 3.250" | 12.125" | 17.750" | 12.500" | 12.000" | 15.750" | 625,000 |