

H TIMING PULLEYS

0.500" Trapezoidal Pitch

For 1.5" Wide Belts





Steel/Iron

Black Oxide Plating

Taper-Lock® Style



Part Number	No. of Teeth	Type	Pitch Dia. (in)	Out. Dia. (in)	Flange Dia. (in)	Bushing	Face Width (in)	Overall Length (in)
TL14H150-1008	14	3F	2.228	2.174	2.461	1008	1.812	1.812
TL14H150-1108	14	3F	2.228	2.174	2.461	1108	1.812	1.812
TL16H150	16	3F	2.546	2.492	2.780	1008	1.812	1.812
TL18H150	18	3F	2.865	2.811	3.100	1215	1.812	1.812
TL20H150	20	3F	3.183	3.129	3.256	1215	1.812	1.812
TL22H150	22	3F	3.501	3.447	3.735	1615	1.812	1.812
TL24H150	24	3F	3.820	3.766	4.050	2012	1.812	1.812
TL26H150	26	3F	4.138	4.084	4.369	2012	1.812	1.812
TL28H150	28	3F	4.456	4.402	4.687	2012	1.812	1.812
TL30H150	30	3F	4.775	4.721	5.000	2012	1.812	1.812
TL32H150	32	3F	5.093	5.039	5.320	2517	1.312	1.312
TL40H150	40	3F	6.366	6.312	6.600	2517	3.375	3.375
TL48H150	48	3F	7.639	7.585	7.867	2517	2.344	2.344
TL60H150	60	E2	9.549	9.495	-	3020	1.812	2.000
TL72H150	72	7	11.459	11.405	-	3020	1.812	1.812
TL84H150	84	7	13.369	13.315	-	3020	1.812	1.812
TL96H150	96	C2	15.279	15.225	-	3020	1.812	1.812
TL120H150	120	C2	19.099	19.045	-	3020	1.812	1.812



For H pitch pulley stock and flanges, see page 199.



For matching Taper-Lock® bushings, see page 373.