



POWERHOUSE™ HTD® TIMING PULLEYS

3 mm Pitch
For 9 mm Wide Belts
Hub
Aluminum
Clear Anodized
Finished Bore



Part Number	No. of Teeth	Type	Pitch Dia. (in)	Out. Dia. (in)	Bore (in)	Face Width (in)	Overall Length (in)	Hub Dia. (in)	Set Screw
18-3M09-6A3	18	6	0.677	0.647	0.250	0.506	0.812	0.442	2 x 8-32 @ 90°
19-3M09-6A3	19	6	0.714	0.684	0.250	0.506	0.812	0.468	2 x 8-32 @ 90°
20-3M09-6A3	20	6	0.752	0.722	0.250	0.506	0.812	0.500	2 x 8-32 @ 90°
22-3M09-6A3	22	6	0.827	0.797	0.250	0.506	0.812	0.562	2 x 8-32 @ 90°
24-3M09-6A3	24	6	0.902	0.872	0.250	0.506	0.812	0.625	2 x 8-32 @ 90°
25-3M09-6A3	25	6	0.940	0.910	0.250	0.506	0.812	0.625	2 x 8-32 @ 90°
26-3M09-6A3	26	6	0.977	0.947	0.250	0.506	0.812	0.625	2 x 8-32 @ 90°
28-3M09-6A3	28	6	1.053	1.023	0.250	0.506	0.812	0.701	2 x 8-32 @ 90°
30-3M09-6A3	30	6	1.128	1.098	0.250	0.506	0.812	0.776	2 x 8-32 @ 90°
32-3M09-6A3	32	6	1.203	1.173	0.250	0.506	0.812	0.851	2 x 8-32 @ 90°
34-3M09-6A3	34	6	1.278	1.248	0.250	0.527	0.834	0.921	2 x 8-32 @ 90°
36-3M09-6A3	36	6	1.353	1.323	0.250	0.527	0.834	1.000	2 x 8-32 @ 90°
38-3M09-6A3	38	6	1.429	1.399	0.250	0.527	0.834	1.075	2 x 8-32 @ 90°
40-3M09-6A3	40	6	1.504	1.474	0.250	0.527	0.834	1.150	2 x 8-32 @ 90°
44-3M09-6A3	44	6	1.654	1.624	0.250	0.527	0.834	1.300	2 x 8-32 @ 90°
48-3M09-6A4	48	6	1.805	1.775	0.313	0.500	0.875	1.250	2 x 8-32 @ 90°
50-3M09-6A4	50	6	1.880	1.850	0.313	0.500	0.875	1.250	2 x 8-32 @ 90°
56-3M09-6A4	56	6	2.105	2.075	0.313	0.500	0.875	1.250	2 x 8-32 @ 90°
60-3M09-6A4	60	6	2.256	2.226	0.313	0.500	0.875	1.250	2 x 8-32 @ 90°
62-3M09-6A4	62	6	2.331	2.301	0.313	0.500	0.875	1.250	2 x 8-32 @ 90°
72-3M09-6A4	72	6	2.707	2.677	0.313	0.500	0.875	1.250	2 x 8-32 @ 90°



Save time and money on the printing and placement of labels by taking advantage of our custom eco-friendly marking options. B&B Manufacturing offers custom laser marking for smaller parts with our ElectroX Laser Marking Machine and our Epilog Laser Marking Machine. For larger parts, our Telesis Pin Stamp Marking Machine is available for custom marking.