


3 MM POWERHOUSE™ HTD® TIMING PULLEY BAR STOCK

3 mm Pitch
Aluminum



Part Number	No. of Teeth	Metric		Inch		Shank Diameter	Shank Length	Minimum Usable Length	Overall Length
		Pitch Diameter	Outside Diameter	Pitch Diameter	Outside Diameter				
33-3M-PS7A	33	31.5 mm	30.8 mm	1.241"	1.211"	0.500"	0.750"	7.000"	7.750"
34-3M-PS7A	34	32.5 mm	31.7 mm	1.278"	1.248"	0.500"	0.750"	7.000"	7.750"
35-3M-PS7A	35	33.4 mm	32.7 mm	1.316"	1.286"	0.500"	0.750"	7.000"	7.750"
36-3M-PS8A	36	34.4 mm	33.6 mm	1.353"	1.323"	0.500"	0.750"	8.000"	8.750"
37-3M-PS8A	37	35.3 mm	34.6 mm	1.391"	1.361"	0.500"	0.750"	8.000"	8.750"
38-3M-PS8A	38	36.3 mm	35.5 mm	1.429"	1.399"	0.500"	0.750"	8.000"	8.750"
39-3M-PS8A	39	37.2 mm	36.5 mm	1.466"	1.436"	0.500"	0.750"	8.000"	8.750"
40-3M-PS8A	40	38.2 mm	37.4 mm	1.504"	1.474"	0.500"	0.750"	8.000"	8.750"
42-3M-PS8A	42	40.1 mm	39.3 mm	1.579"	1.549"	0.500"	0.750"	8.000"	8.750"
44-3M-PS8A	44	42.0 mm	41.2 mm	1.654"	1.624"	0.500"	0.750"	8.000"	8.750"
45-3M-PS8A	45	43.0 mm	42.2 mm	1.692"	1.662"	0.500"	0.750"	8.000"	8.750"
48-3M-PS8A	48	45.8 mm	45.1 mm	1.805"	1.775"	0.500"	0.750"	8.000"	8.750"
50-3M-PS8A	50	47.8 mm	47.0mm	1.880"	1.850"	0.750"	0.750"	8.000"	8.750"
52-3M-PS8A	52	49.7 mm	48.9 mm	1.955"	1.925"	0.750"	0.750"	8.000"	8.750"
54-3M-PS8A	54	51.6 mm	50.8 mm	2.030"	2.000"	0.750"	0.750"	8.000"	8.750"
56-3M-PS8A	56	53.5 mm	52.7 mm	2.105"	2.075"	0.750"	0.750"	8.000"	8.750"
60-3M-PS8A	60	57.3 mm	56.5 mm	2.256"	2.226"	0.750"	0.750"	8.000"	8.750"
62-3M-PS8A	62	59.2 mm	58.4 mm	2.331"	2.301"	0.750"	0.750"	8.000"	8.750"
64-3M-PS8A	64	61.1 mm	60.4 mm	2.406"	2.376"	0.750"	0.750"	8.000"	8.750"
66-3M-PS8A	66	63.0 mm	62.3 mm	2.481"	2.451"	0.750"	0.750"	8.000"	8.750"
68-3M-PS8A	68	64.9 mm	64.2 mm	2.557"	2.527"	0.750"	0.750"	8.000"	8.750"
70-3M-PS8A	70	66.9 mm	66.1 mm	2.632"	2.602"	0.750"	0.750"	8.000"	8.750"
72-3M-PS8A	72	68.8 mm	68.0 mm	2.707"	2.677"	0.750"	0.750"	8.000"	8.750"