




SECTION 1 - IDENTIFICATION

<b>Manufacturer:</b> Black Swan Mfg. Co. 4540 W. Thomas St. Chicago, IL 60651-3318 Tel.: 800-252-5796 Fax: 773-227-3705 Web Site : <a href="http://www.blackswanmfg.com">www.blackswanmfg.com</a> E-mail : <a href="mailto:info@blackswanmfg.com">info@blackswanmfg.com</a>	For any Transportation or Medical Chemical Emergencies call:  <p style="text-align: center;"><b>INFOTRAC</b></p> <p style="text-align: center;">(800) 535-5053 <b>OR</b> (352) 323-3500</p> <p style="text-align: center;">24 hours per day - 7 days a week</p>
<b>Product Name: Silicone Sealant – Almond</b>	<b>Recommended Use:</b> Sealant for indoor or outdoor use. Ideal for use in bathtubs, shower stalls, vanities, windows, etc.

SECTION 2 – HAZARD(S) IDENTIFICATION

<u>Labels</u> None	<p style="text-align: center;"><b>NFPA</b></p> <table style="width: 100%; border: none;"> <tr> <td style="width: 50%; border: none;"> <b>HEALTH HAZARD</b>            4 – Deadly            3 – Extreme Danger            2 – Hazardous            1 – Slight Hazardous            0 – Normal Material         </td> <td style="width: 50%; border: none;"> <b>FIRE HAZARD</b>            Flash Points            4 – Below 73°F            3 – Below 100°F            2 – Above 100°F, Not exceeding 200°F            1 – Above 200°F            0 – Will not burn         </td> </tr> <tr> <td style="border: none;"> <b>SPECIFIC HAZARD</b>            Oxidizer OX            Acid ACID            Alkali ALK            Corrosive COR            Use NO WATER W            Radioactive ☣         </td> <td style="border: none;"> <b>REACTIVITY</b>            4 – May detonate            3 – Shock and heat may detonate            2 – Violent chemical change            1 – Unstable if heated            0 – Stable         </td> </tr> </table> 	<b>HEALTH HAZARD</b> 4 – Deadly 3 – Extreme Danger 2 – Hazardous 1 – Slight Hazardous 0 – Normal Material	<b>FIRE HAZARD</b> Flash Points 4 – Below 73°F 3 – Below 100°F 2 – Above 100°F, Not exceeding 200°F 1 – Above 200°F 0 – Will not burn	<b>SPECIFIC HAZARD</b> Oxidizer OX Acid ACID Alkali ALK Corrosive COR Use NO WATER W Radioactive ☣	<b>REACTIVITY</b> 4 – May detonate 3 – Shock and heat may detonate 2 – Violent chemical change 1 – Unstable if heated 0 – Stable	<p style="text-align: center;"><b>GHS Classification</b></p> <table style="width: 100%; border: none;"> <tr> <td style="width: 50%; border: none;"> <p style="text-align: center;"><u>Health</u></p>           Acute Toxicity: Not Established            Skin Irritation: Not Established            Eye Irritation: Not Established            Skin Sensitization: NO         </td> <td style="width: 50%; border: none;"> <p style="text-align: center;"><u>Environmental</u></p>           Acute Aquatic Toxicity: Not Established            Chronic Aquatic Toxicity: Not Established         </td> </tr> <tr> <td colspan="2" style="border: none;"> <p style="text-align: center;"><u>Physical</u></p>           None         </td> </tr> </table>	<p style="text-align: center;"><u>Health</u></p> Acute Toxicity: Not Established Skin Irritation: Not Established Eye Irritation: Not Established Skin Sensitization: NO	<p style="text-align: center;"><u>Environmental</u></p> Acute Aquatic Toxicity: Not Established Chronic Aquatic Toxicity: Not Established	<p style="text-align: center;"><u>Physical</u></p> None	
<b>HEALTH HAZARD</b> 4 – Deadly 3 – Extreme Danger 2 – Hazardous 1 – Slight Hazardous 0 – Normal Material		<b>FIRE HAZARD</b> Flash Points 4 – Below 73°F 3 – Below 100°F 2 – Above 100°F, Not exceeding 200°F 1 – Above 200°F 0 – Will not burn								
<b>SPECIFIC HAZARD</b> Oxidizer OX Acid ACID Alkali ALK Corrosive COR Use NO WATER W Radioactive ☣		<b>REACTIVITY</b> 4 – May detonate 3 – Shock and heat may detonate 2 – Violent chemical change 1 – Unstable if heated 0 – Stable								
<p style="text-align: center;"><u>Health</u></p> Acute Toxicity: Not Established Skin Irritation: Not Established Eye Irritation: Not Established Skin Sensitization: NO	<p style="text-align: center;"><u>Environmental</u></p> Acute Aquatic Toxicity: Not Established Chronic Aquatic Toxicity: Not Established									
<p style="text-align: center;"><u>Physical</u></p> None										
<u>Signal Word</u> None	<p style="text-align: center;"><u>Health</u></p> Acute Toxicity: Not Established Skin Irritation: Not Established Eye Irritation: Not Established Skin Sensitization: NO									
<p style="text-align: center;"><b>HMIS</b></p> <table style="width: 100%; border: none;"> <tr> <td style="background-color: #000080; color: white; padding: 2px;">HEALTH</td> <td style="border: 1px solid black; text-align: center; width: 30px;">0</td> </tr> <tr> <td style="background-color: #FF0000; color: white; padding: 2px;">FLAMMABILITY</td> <td style="border: 1px solid black; text-align: center;">1</td> </tr> <tr> <td style="background-color: #FFD700; padding: 2px;">REACTIVITY</td> <td style="border: 1px solid black; text-align: center;">0</td> </tr> </table>	HEALTH	0	FLAMMABILITY	1	REACTIVITY	0	<p style="text-align: center;"><u>Physical</u></p> None			
HEALTH	0									
FLAMMABILITY	1									
REACTIVITY	0									
<p style="text-align: center;"><b>Hazardous Statements</b></p> None	<p style="text-align: center;"><b>Precautionary Statements</b></p> P102: Keep out of reach of children P271: Use only outdoors or in a well-ventilated area									

SECTION 3 – COMPOSITION / INFORMATION ON INGREDIENTS

<u>Chemicals</u>	<u>CAS#</u>	<u>EINECS#</u>	<u>REACH</u> <u>Pre-registration Number</u>	<u>Approx %</u>
DISTILLATES (PETROLEUM), HYDROTREATED MIDDLE	64742-46-7	N/A	N/A	20 - 30%
SILICON DIOXIDE	7631-86-9	N/A	N/A	5 - 10%

\*Unlisted ingredients are not classified as hazardous according to OSHA 1910.1200.

SECTION 4 – FIRST-AID MEASURES

<p><b>Inhalation:</b> Move into fresh air. If breathing is difficult, give oxygen and call physician.</p> <p><b>Skin:</b> Remove contaminated clothing and shoes and wash before reuse. Wash skin thoroughly with soap and water. If irritation persists get medical attention.</p> <p><b>Eyes:</b> Flush with water for 15 minutes. If irritation persists get medical attention.</p> <p><b>Ingestion:</b> Rinse mouth with water. DO NOT INDUCE VOMITING. Get medical attention.</p>
--

## GHS SAFETY DATA SHEET

### SECTION 5 – FIRE-FIGHTING MEASURES

**Fire Hazard:** None.

**Combustion Products:** Carbon Dioxides, Silicone Dioxides, and Formaldehyde.

**Extinguishing Media:** Use water, alcohol resistant foam, dry chemical, and carbon dioxide.

**Unsuitable Extinguishing Media:** None known.

**Protective Equipment:** Self-contained breathing apparatus {(SCBA), MSHA/NIOSH}. Full protective gear.

**Special Fire Fighting Procedures:** Evacuate enclosed areas, stay upwind. Closed or confined quarters require self-contained breathing apparatus, positive pressure hose masks or airline masks. Use water spray to cool containers, to flush spills from sources of ignition and to disperse vapors.

### SECTION 6 – ACCIDENTAL RELEASE MEASURES

**Personal Precautions:** Wash walking surfaces with detergent and water to reduce slipping hazard.

**Protective Equipment:** As specified in the protective equipment section.

**Emergency Procedures:** None.

**Environmental Precautions:** None.

**Methods for Cleaning Up:** Wipe, scrape or soak up in an inert material and put in a container for disposal. Clean area as appropriate since spilled materials, even in small quantities, may present a slip hazard.

### SECTION 7 – HANDLING AND STORAGE

#### Handling

Use with adequate ventilation.

#### Storage

Store away from oxidizing materials. Store in accordance with the particular national regulations.

### SECTION 8 – EXPOSURE CONTROLS / PERSONAL PROTECTION

<u>Hazardous Chemicals</u>	<u>Exposure Limits</u>		
	<u>ACGIH-TLV</u>	<u>ACGIH-STEL</u>	<u>OSHA-PEL</u>
DISTILLATES (PETROLEUM), HYDROTREATED MIDDLE	N/A	N/A	N/A
SILICON DIOXID	N/A	N/A	N/A

**Engineering Controls:** Eye wash stations; Showers.

**Ventilation:** Exhaust ventilation.

**Personal Protective Equipment – Respiratory:** If exposure limits are exceeded or respiratory irritation is experienced, NIOSH/MSHA approved respiratory protection should be worn. Supplied air respirators may be required for non-routine or emergency situations. Respiratory protection must be provided in accordance with OSHA regulations (see 29CFR 1910.134).

**Personal Protective Equipment – Skin:** Rubber gloves.

**Personal Protective Equipment – Eyes:** Safety glasses / face protection.

### SECTION 9 – PHYSICAL & CHEMICAL PROPERTIES

<b>Appearance:</b> Paste	<b>Flash Point:</b> Not Established	<b>Vapor Pressure:</b> Not Established
<b>Odor:</b> Acetic Acid	<b>Specific Gravity:</b> Not Established	<b>Flammability:</b> Not Established
<b>pH:</b> Not Established	<b>Solubility (H2O):</b> Not Established	<b>Flammability Limits:</b> LEL – Not Established
<b>Melting Point:</b> Not Established	<b>Evaporation Rate:</b> Not Established	UEL – Not Established
<b>Freezing Point:</b> Not Established	<b>Vapor Density:</b> Not Established	
<b>Boiling Point:</b> Not Established	<b>VOC:</b> Not Established	

### SECTION 10 – STABILITY AND REACTIVITY

**Stability:** Stable under normal conditions.

**Hazardous polymerization:** Will not occur.

**Conditions to avoid:** Oxidizing materials can cause a reaction.

**Incompatible materials:** Oxidizing agents.

**Hazardous decomposition products:** Formaldehyde.

# GHS SAFETY DATA SHEET

## SECTION 11 – TOXICOLOGICAL INFORMATION

<u>Hazardous Chemicals</u>	<u>Toxicity</u>	
	<u>LD<sub>50</sub></u>	<u>LC<sub>50</sub></u>
DISTILLATES (PETROLEUM), HYDROTREATED MIDDLE	Oral: >5,000 mg/kg (rat) Dermal: >2,000 mg/kg (rat)	N/A
SILICON DIOXIDE	N/A	N/A
<b>Likely Routes of Exposure:</b> Not classified. <b>Symptoms and Effect - Inhalation:</b> Not classified. <b>Skin Contact:</b> Not classified. <b>Eye Contact:</b> Not classified. <b>Ingestion:</b> Not classified. <b>Long-Term Effect:</b> None known. <b>Pre-Existing Conditions:</b> None known.		

## SECTION 12 – ECOLOGICAL INFORMATION

<b>Ecotoxicity:</b> None. <b>Persistence &amp; Degradability:</b> None. <b>Bioaccumulative Potential:</b> None. <b>Mobility in soil:</b> In normal use, emission of Volatile Organic Compounds (VOC's) to the air takes place, typically at a rate of $\leq 36$ g/l.
---

## SECTION 13 – DISPOSAL CONSIDERATION

Dispose of product or container in accordance with federal, state or local regulations.

## SECTION 14 – TRANSPORTATION INFORMATION

D.O.T. (U.S.): Not Regulated.

## SECTION 15 – REGULATORY INFORMATION

<b>Precautionary Label Information:</b> None. <b>Risk Phrases:</b> None. <b>Safety Phrases:</b> S2-Keep out of reach of children.
---

## SECTION 16 – OTHER INFORMATION

Information on this form is furnished solely for the purpose of compliance with the Occupational Safety and Health Act and shall not be used for any other purpose. Black Swan Mfg. Co. urges the customers receiving this Material Safety Data Sheet to study it carefully to become aware of the hazards, if any, of the product involved. In the interest of safety, you should notify your employees, agents and contractors of the information on the sheets. <b>DATE: 01/01/2021</b>
--