

T10 TIMING PULLEYS

10 mm Pitch


For 50 mm Wide Belts

Hub



Zinc Plated Steel Flanges

Aluminum

METRIC TIMING PULLEY



Part Number	No. of Teeth	Type	Pitch Dia. (mm)	Out. Dia. (mm)	Flange Dia (mm)	Bore (mm)	Face Width (mm)	Overall Length (mm)	Belt Width (mm)	Hub Dia. (mm)
66T10/18-2	18	6F	57.3	55.5	60.0	10.0	56.0	66.0	50.0	40.0
66T10/19-2	19	6F	60.5	58.7	66.0	10.0	56.0	66.0	50.0	44.0
66T10/20-2	20	6F	63.7	61.8	66.0	12.0	56.0	66.0	50.0	46.0
66T10/24-2	24	6F	76.4	74.6	83.0	12.0	56.0	66.0	50.0	58.0
66T10/25-2	25	6F	79.6	77.8	83.0	12.0	56.0	66.0	50.0	60.0
66T10/27-2	27	6F	86.0	84.1	91.0	12.0	56.0	66.0	50.0	60.0
66T10/30-2	30	6F	95.5	93.7	97.0	12.0	56.0	66.0	50.0	60.0
66T10/32-2	32	6F	101.9	100.0	106.0	12.0	56.0	66.0	50.0	65.0
66T10/36-2	36	6F	114.6	112.8	119.0	16.0	56.0	66.0	50.0	70.0
66T10/40-2	40	6F	127.3	125.5	131.0	16.0	56.0	66.0	50.0	80.0
66T10/48-0	48	6	152.8	151.0	-	16.0	56.0	66.0	50.0	95.0
66T10/60-0	60	6	191.0	189.2	-	16.0	56.0	66.0	50.0	110.0




B&B Manufacturing offers an online, interactive competitor's part number cross reference tool on our website.

This powerful cross reference tool is intended to be used to determine an equivalent B&B Manufacturing part number given another manufacturer's part number. Most major precision mechanical component and power transmission manufacturers and distributors are included in this utility.

For this and other useful tools, visit our website at:

www.bbman.com.



For T10 pitch pulley stock, see page 336.