

L TIMING PULLEYS

0.375" Trapezoidal Pitch

For 0.750" Wide Belts

Steel/Iron

Split Taper Style



Part Number	No. of Teeth	Type	Pitch Dia. (in)	Out. Dia. (in)	Flange Dia. (in)	Bushing	Face Width (in)	Overall Length (in)
18LG075	18	4	2.149	2.119	2.438	G	1.000	1.625
19LG075	19	4	2.268	2.238	2.625	G	1.000	1.625
20LG075	20	4	2.387	2.357	2.625	G	1.000	1.625
21LG075	21	4	2.507	2.477	2.875	G	1.000	1.625
22LG075	22	4	2.626	2.596	2.875	G	1.000	1.625
24LH075	24	4	2.865	2.835	3.125	H	1.000	1.625
26LH075	26	4	3.104	3.074	3.375	H	1.000	1.625
28LH075	28	4	3.342	3.312	3.625	H	1.000	1.625
30LH075	30	16	3.581	3.551	3.813	H	1.000	1.438
32LH075	32	16	3.820	3.790	4.063	H	1.000	1.438
36LH075	36	16	4.297	4.267	4.688	H	1.000	1.438
36LP075	36	7	4.297	4.267	4.688	P1	1.000	2.188
40LH075	40	16	4.775	4.745	5.000	H	1.000	1.438
40LP075	40	7	4.775	4.745	5.000	P1	1.000	2.188
44LH075	44	16	5.285	5.222	5.500	H	1.000	1.438
44LP075	44	7	5.252	5.222	5.500	P1	1.000	2.188
48LH075	48	16	5.730	5.700	6.000	H	1.000	1.438
48LP075	48	7	5.730	5.700	6.000	P1	1.000	2.188
60LH075	60	17	7.162	7.132	-	H	1.000	1.500
60LP075	60	13	7.162	7.132	-	P1	1.000	2.188
72LH075	72	17	8.594	8.564	-	H	1.000	1.500
72LP075	72	13	8.594	8.564	-	P1	1.000	2.188
84LH075	84	17	10.027	9.997	-	H	1.000	1.500
84LP075	84	13	10.027	9.997	-	P1	1.000	2.188
96LH075	96	17	11.459	11.429	-	H	1.000	1.500
96LP075	96	13	11.459	11.429	-	P1	1.000	2.188
120LH075	120	17	14.324	14.294	-	H	1.000	1.500

