

# H TIMING PULLEYS

0.500" Trapezoidal Pitch

For 2" Wide Belts






Steel/Iron

Black Oxide Plating

Taper-Lock® Style




| Part Number | No. of Teeth | Type | Pitch Dia (in) | Out. Dia (in) | Flange Dia. (in) | Bushing | Face Width (in) | Overall Length (in) |
|-------------|--------------|------|----------------|---------------|------------------|---------|-----------------|---------------------|
| TL16H200    | 16           | 3F   | 2.546          | 2.492         | 2.780            | 1008    | 2.344           | 2.344               |
| TL18H200    | 18           | 3F   | 2.865          | 2.811         | 3.100            | 1215    | 2.344           | 2.344               |
| TL20H200    | 20           | 3F   | 3.183          | 3.129         | 3.256            | 1215    | 2.344           | 2.344               |
| TL22H200    | 22           | 3F   | 3.501          | 3.447         | 3.735            | 1615    | 2.344           | 2.344               |
| TL24H200    | 24           | 3F   | 3.820          | 3.766         | 4.050            | 2012    | 2.344           | 2.344               |
| TL26H200    | 26           | 2F   | 4.138          | 4.084         | 4.369            | 2012    | 2.344           | 2.344               |
| TL28H200    | 28           | 2F   | 4.456          | 4.402         | 4.687            | 2012    | 2.344           | 2.344               |
| TL30H200    | 30           | 2F   | 4.775          | 4.721         | 5.000            | 2012    | 2.344           | 2.344               |
| TL32H200    | 32           | 3F   | 5.093          | 5.039         | 5.320            | 2517    | 1.812           | 1.812               |
| TL40H200    | 40           | 3F   | 6.366          | 6.312         | 6.600            | 2517    | 1.312           | 1.312               |
| TL48H200    | 48           | 3F   | 7.639          | 7.585         | 7.867            | 3020    | 3.375           | 3.375               |
| TL60H200    | 60           | 3    | 9.549          | 9.495         | -                | 3020    | 2.343           | 2.343               |
| TL72H200    | 72           | 3    | 11.459         | 11.405        | -                | 3020    | 2.343           | 2.343               |
| TL84H200    | 84           | 3    | 13.369         | 13.315        | -                | 3020    | 2.343           | 2.343               |
| TL96H200    | 96           | C2   | 15.279         | 15.225        | -                | 3535    | 2.343           | 2.343               |
| TL120H200   | 120          | C2   | 19.099         | 19.045        | -                | 3020    | 2.343           | 2.343               |



For H pitch pulley stock and flanges, see page 199.



For matching Taper-Lock® bushings, see page 373.



For idler pulleys, see page 366.