



JOB NAME:	CONTRACTOR:
JOB LOCATION:	APPROVAL:
ENGINEER:	CONTRACTOR P.O.:
APPROVAL:	REPRESENTATIVE:

8P3LDPVC

PVC-BV3T DIRECT MOUNT, 3-WAY PVC, FULL PORT T-PORT BALL VALVE W **DOUBLE ACTING** PNEUMATIC ACTUATOR

8P3TDAPVC

PVC-BV3T DIRECT MOUNT, 3-WAY PVC, FULL PORT T-PORT BALL VALVE W **SPRING RETURN** PNEUMATIC ACTUATOR

SIZES 1/2" TO 2"

8P3LSRPVC

PVC-BV3L DIRECT MOUNT, 3-WAY PVC, FULL PORT L-PORT BALL VALVE W **DOUBLE ACTING** PNEUMATIC ACTUATOR

8P3TSRPVC

PVC-BV3L DIRECT MOUNT, 3-WAY PVC, FULL PORT L-PORT BALL VALVE W **SPRING RETURN** PNEUMATIC ACTUATOR

SIZES 1/2" TO 2"

SPECIFICATIONS

The valve body, stem, ball and unions shall be made of PVC compound which shall meet classification 12454 of ASTM D 1784. The ball seats shall be made of PTFE and the O-Ring seals shall be made of EPDM.

The PVC IPS/Socket connectors shall conform to the dimensional standards ASTM D2466 and ASTM D2467, The NPT PVC connectors shall conform to the dimensional standards of ASTM D2464, ASTM F1498, and ANSI B1.20.1 thread depths.

The rack and pinion style pneumatic actuator body shall be made from hard anodized extruded aluminum, and shall incorporate adjustable side 0-90 adjustable limit stops that do not internally enter the cylinder bore. The actuator temperature range shall be -4°F to 302°F.


ACTUATOR FEATURES

- Hard anodized extruded aluminum body
- Concentric spring sets
- Die cast aluminum end caps
- Solid steel barstock pinion (not casting)
- 0°-90° rotation adjustment cam
- 0°-90° rotation adjustment bolts
- POM piston guides
- Minimum air pressure rating: 80 psi
- Maximum air pressure rating: 116 psi
- Working temperature: -4°F - 302°F
- No lubrication maintenance required for the entire actuator lifetime
- 100% factory tested

VALVE FEATURES


- 3-Way Full Port
- Size Range 1/2" Through 2"
- NPT and Socket Ends included
- EPDM Seats and Seals
- Dual Union Nut Locks
- 232 PSI at 73°F
- "L" and "T" Port Viton Seats and Seals Available

PRESSURE TEMPERATURE CHART FOR PVC-BV3*




FLOW PATH VARIATIONS

T-PORT FLOW PATH A




POSITION 1



POSITION 2

T-PORT FLOW PATH B



POSITION 1




POSITION 2

L-PORT FLOW PATH A




POSITION 1





POSITION 2

BILL OF MATERIALS FOR PVC-BV3L/PVC-BV3T



N POS	PART NAME	MATERIAL	N PCS
1	UNION NUT	PVC/CPVC/PP	3
2	BODY	PVC/CPVC/PP	1
3	LOCKING STRIP	PVDF	1
4	CARRIER	PVC/CPVC/PP	1
5	HANDLE	ABS	1
6	STEM	PVC/CPVC/PP	1
7	STEM O-RING	EPDM/VITON/Silicone	2
8	BALL SEAT	PTFE	3
9	BALL	PVC/CPVC/PP	1
10	CARRIER O-RING	EPDM/VITON/Silicone	1
11	FACE O-RING	EPDM/VITON/Silicone	3
12	CONNECTOR	PVC/CPVC/PP	3

DIMENSIONS



*G = Socket Depth

8P3LDAPVC

WITH DOUBLE ACTING ACTUATOR

8P3TDAPVC

WITH DOUBLE ACTING ACTUATOR

SIZE	A	B	C	D	E	F	G	ACT.
1/2"	5.55	4.96	4.87	2.80	4.96	7.21	0.89	DA52V
3/4"	5.55	5.76	5.08	2.80	5.76	7.21	1.00	DA52V
1"	5.55	6.56	5.17	2.80	6.56	7.21	1.13	DA52V
1-1/4"	5.55	7.71	5.43	2.80	7.71	7.21	1.26	DA52V
1-1/2"	6.46	8.32	5.92	3.17	8.32	7.66	1.38	DA63V
2"	6.46	9.99	6.30	3.17	9.99	7.66	1.50	DA63V

8P3LSRPVC

WITH SPRING RETURN ACTUATOR

8P3TSRPVC

WITH SPRING RETURN ACTUATOR

SIZE	A	B	C	D	E	F	G	ACT.
1/2"	5.55	4.96	3.80	2.80	4.96	7.21	0.89	SR52V
3/4"	5.55	5.76	3.80	2.80	5.76	7.21	1.00	SR52V
1"	6.46	6.56	4.17	3.17	6.56	7.66	1.13	SR63V
1-1/4"	8.27	7.71	4.72	3.72	7.71	8.37	1.26	SR75V
1-1/2"	8.27	8.32	4.72	3.72	8.32	8.37	1.38	SR75V
2"	9.47	9.99	5.17	4.17	9.99	8.92	1.50	SR85V