

# H TIMING PULLEYS

0.500" Trapezoidal Pitch

For 3" Wide Belts






Steel/Iron

Black Oxide Plating

Taper-Lock® Style



Part Number	No. of Teeth	Type	Pitch Dia. (in)	Out. Dia. (in)	Flange Dia. (in)	Bushing	Face Width (in)	Overall Length (in)
TL18H300	18	3F	2.865	2.811	3.100	1215	3.375	3.375
TL20H300	20	3F	3.183	3.129	3.256	1215	3.375	3.375
TL22H300	22	3F	3.501	3.447	3.735	1615	3.375	3.375
TL24H300	24	3F	3.820	3.766	4.050	2012	3.375	3.375
TL26H300	26	2F	4.138	4.084	4.369	2012	3.375	3.375
TL28H300	28	2F	4.456	4.402	4.687	2012	3.375	3.375
TL30H300	30	E1F	4.775	4.721	5.005	2012	3.375	3.375
TL32H300	32	E1F	5.093	5.039	5.320	2517	3.375	3.375
TL40H300	40	E1F	6.366	6.312	6.600	2517	3.375	3.375
TL48H300	48	E1F	7.639	7.585	7.867	3020	3.375	3.375
TL60H300	60	A2	9.549	9.495	-	3020	3.375	3.375
TL72H300	72	A2	11.459	11.405	-	3020	3.375	3.375
TL84H300	84	A3	13.369	13.315	-	3020	3.375	3.375
TL96H300	96	A3	15.279	15.225	-	3535	3.375	3.375
TL120H300	120	A3	19.099	19.045	-	3535	3.375	3.375



For H pitch pulley stock and flanges, see page 199.



For matching Taper-Lock® bushings, see page 373.