

MRCLP

PARTS LIST

ITEM#	PART #	DESCRIPTION	08/01/14	GENERAL INFORMATION
1	40058	TUB WELDMENT	632.91	
2	40056	LEFT LID PAINTED	145.62	OVERALL DIMENSIONS 38"L X 28"W X 23"H
3	40057	RIGHT LID PAINTED	145.62	CLEANING CHAMBER 29"L X 20 1/2"W X 3"D
4	40152	SHELF/PUMP SUPPORT	176.84	HEIGHT (LID OPEN)
5		PULL HANDLE	15.76	SOLVENT CAPACITY 7-10 GALLONS
6	40016	RIGHT LATCH BAR	20.27	
7	40017	LEFT LATCH BAR	20.27	PUMP SPECIFICATIONS 170GPH / AIR OPTION
8	12472	FUSIBLE LINK	8.85	ELECTRICAL REQUIRED 120V / 60HZ / 1.1AMP
	99-12472-5	FUSIBLE LINK - 5PK	33.18	SILL WORKING HEIGHT 8 1/2"
9	14912	TEK SCREW #10	0.53	WORKSHELF 4" FROM BOTTOM
10	10568	CASTER (EACH)	15.32	SHIPPING WEIGHT 65 POUNDS
11	13880	1/2"NPT DRAIN PLUG	2.10	
12	40033	FLOW THRU BRUSH ASSEMBLY	54.20	
13	14600	170GPH SUBMERSIBLE PUMP	123.54	
14	13680	PUMP PIPE	3.45	
14A	10808	1/2" CONDUIT LOCK NUT	0.90	
15	10776	PULL ELBOW	6.76	
16	40028	ELECTRICAL ASSEMBLY	81.97	
17	10848	POWER CORD	14.57	
18	15600	ROCKER SWITCH	6.31	
19	11584	CRUMB CUP	8.85	
20	11672	CLOTH FILTER BAG	4.66	

