


BLACK RHINO™

Self-Retracting Lifeline

Introducing the smallest and lightest 9-foot cable lifeline on the market

The industry's first global retractable

- Designed to endure the daily rigors of harsh environments
- Ideal for **concrete construction, welding, steel erection** and **warehouse** applications that require durability and reliability that only a cable lifeline can provide
- Repairable; no annual factory recertification required – lowering cost of ownership
- Arrests free falls within inches providing a quick, safe rescue



MILLER

by Honeywell

More Features/Benefits of the Miller® Black Rhino™ SRL

- **Quick-activating, high-strength stainless steel braking system** – arrests falls within inches
- **Variety of integral anchorage connectors available** – provides ultimate flexibility of use in a variety of applications
- **Global retractable** – single unit can be used around the world; meets all applicable industry standards including OSHA 1926.502, 1910.66, ANSI Z359.1, CSA Z259.2.2-98, CE
- **Integral load indicator** – indicates when the unit must be removed from service and returned for repair
- **Extended service life** – corrosion-resistant stainless steel and aluminum components
- **Integral internal shock absorber** – consistently reduces fall forces to 900 lbs./f (4 kN) or less for greater safety

MATERIALS

Cover:	Impact-resistant thermoplastic over aluminum
Housing:	Aluminum
Hub:	Aluminum
Braking Mechanism:	Stainless Steel
Lifeline:	Stainless Steel Cable
Snap Hook:	Zinc-plated, locking snap hook with 3/4" (19mm) gate opening and integral load indicator

TECHNICAL

Maximum Working Load:	310 lbs. (140.6 kg)
Working Capacity:	9 ft. (2.7m)
Lifeline Tension:	3 to 4 lbs./f (13.3 to 17.8 kN)
Maximum Arresting Force:	900 lbs./f (4 kN)
Weight:	4.3 lbs. (1.9 kg)



Model CFL-1



Model CFL-2



Model CFL-3



Model CFL-4



Model CFL-5

Miller® Black Rhino™ SRL Models

Model No.	Cable Lifeline Length	Anchorage Connection	Connection to Harness	Weight
CFL-1	9 ft. (2.7m)	None (<i>need carabiner, not included</i>)	Locking, swivel snap hook with load indicator	4.3 lbs. (1.9 kg)
CFL-2	9 ft. (2.7m)	Steel twist-lock carabiner	Locking, swivel snap hook with load indicator	4.8 lbs. (2.2 kg)
CFL-3	9 ft. (2.7m)	Stainless steel swivel (<i>need carabiner, not included</i>)	Locking, swivel snap hook with load indicator	4.5 lbs. (2.0 kg)
CFL-4	9 ft. (2.7m)	Stainless steel swivel and steel twist-lock carabiner	Locking, swivel snap hook with load indicator	5.0 lbs. (2.3 kg)
CFL-5	9 ft. (2.7m)	Stainless steel swivel and rebar locking snap hook	Locking, swivel snap hook with load indicator	5.7 lbs. (2.6 kg)

Miller brand products meet all applicable OSHA, ANSI including Z359.1 and  requirements.

This equipment should only be used after reading the manufacturer's instructions. Failure to follow instructions could result in serious injury or fatality.

MILLER®

by Honeywell

 Ask the Expert ... Ask Miller.

800/873-5242
or 814/432-2118

Fax 800/892-4078
or Fax 814/432-2415

www.millerfallprotection.com

For more information or to place an order, please contact your Miller® distributor:

LMBRHINO/0903/25M/RPI