

TOGO



SCONCES OUTDOOF

location:

SPECIFICATIONS:

DESCRIPTION

The captivating Togo wall luminaire showcases a half oval design, expertly crafted from skillfully blown glass. This luminaire's beauty lies in its molded glass diffuser, which is carefully hand-decorated with an opaque bronze or black finish, exuding sophistication and style. The warm smoke tint adds a touch of warmth to the light, creating a cozy and inviting atmosphere.

LAMPING

Standard: 75W A19 120V, lamps not included.

LED Filament: 7W Replaceable Filament A19 lamp, 120V, dimmable, 80+ CRI, 3000°K CCT, 800 lumens, 15,000 hours, lamp included.

DIFFUSER

Glass diffuser is molded glass in Black or Bronze finish, with a warm Smoke tint. Dimensions are $5.25''W \times 9.5''H \times 4''D$.

CONSTRUCTION


Stamped Stainless steel fitter. Glass is secured by stainless steel set screws.

MOUNTING

Installs directly to a 4" octagonal outlet box, centered on fixture. 75°C supply wire required for incandescent lamping.

LABELS

UL or ETL Listed. Suitable for Wet Locations. May be used in Interior or Exterior applications.





TOGO-BR



TOGO-BK Black/Smoke

ORDERING:

 FIXTURE
 - LAMP OPTIONS
 - FINISH

 TOGO Togo
 (blank) 75W A19
 BK Black/Smoke

 EDIL 7W LED
 BR Bronze/Smoke

Ex. TOGO-BKTogo Sconce w/ Smoke Bubble,
Black Finish

Project Information:

All dimensions provided are nominal. Allowance must be made for dimensional tolerance in handcrafted glasses.

REV 7/23