

PART NUMBER	AWG NO.	NO. OF COND.	CONDUCTOR STRANDING	JACKET THICKNESS (IN.)	NOM. O.D. (IN.)	STANDARD PUT-UPS	CONDUCTOR COLORS	APPRX LB/M
<b>2 CONDUCTOR, GREY JACKET</b>								
WR16/2DCG	16	2	26/0.0100	0.030	0.350	C,TL,D,M	BK, RD	50
WR14/2DCG	14	2	41/0.0100	0.030	0.390	C,TL,D,M	BK, RD	67
WR12/2DC	12	2	65/0.0100	0.030	0.410	C,TL,D,M	BK, RD	85
WR10/2DCG	10	2	105/0.0100	0.030	0.475	C,TL,D,M	BK, RD	130
<b>3 CONDUCTOR, GREY JACKET</b>								
WR16/3G	16	3	26/0.0100	0.045	0.395	C,TL,D,M	BK, GN, WH	73
WR14/3G	14	3	41/0.0100	0.045	0.410	C,TL,D,M	BK, GN, WH	96
WR12/3G	12	3	65/0.0100	0.045	0.470	C,TL,D,M	BK, GN, WH	131
WR10/3G	10	3	105/0.0100	0.045	0.545	C,TL,D	BK, GN, WH	178
<b>4 CONDUCTOR, GREY JACKET</b>								
WR16/4G	16	4	26/0.0100	0.045	0.420	L,C,TL,D,M	BK, GN, RD, WH	108
WR14/4G	14	4	41/0.0100	0.045	0.465	L,C,TL,D,M	BK, GN, RD, WH	136
WR12/4G	12	4	65/0.0100	0.045	0.560	L,C,TL,D,M	BK, GN, RD, WH	185
WR10/4G	10	4	105/0.0100	0.045	0.600	L,C,TL,D	BK, GN, RD, WH	253
WR8/4G	8	4	7x24/0.0100	0.080	0.830	L,C,TL,D	BK, GN, RD, WH	475
WR6/3-8/1G	6	4	6 AWG @ x38/0.0100 8 AWG @ 7x24/0.0100	0.080	0.985	L,C,TL,D	6 AWG @ BK, RD, WH (8 AWG @ GN)	650
WR4/3-6/1G	4	4	4 AWG @ 7x60/0.0100 6 AWG @ 7x38/0.0100	0.080	1.155	L,C,TL	4 AWG @ BK, BK/RD, WH (6 AWG @ GN)	920
<b>6 CONDUCTOR, GREY JACKET</b>								
WR16/6G	16	6	26/0.0100	0.450	0.455	L,C,TL,D	BK, BR, RD, GN, BL, WH	130
WR14/6G	14	6	41/0.0100	0.450	0.530	L,C,TL,D	BK, BR, RD, GN, BL, WH	200
<b>9 CONDUCTOR, GREY JACKET</b>								
WR14/9G	14	9	41/0.0100	0.450	0.680	L,C,TL	*	280
<b>12 CONDUCTOR, GREY JACKET</b>								
WR14/12G	14	12	41/0.0100	0.600	0.700	L,C,TL	**	375

\*WR14/9G Colors: Black, Red, Orange, Yellow, Green, Blue, Violet, Grey, White

\*\*WR14/12G Colors: Black, Brown, Red, Orange, Yellow, Green, Blue, Violet, Grey, White, White/Black, White/Brown

Standard Put-Ups: L=50 FT, C=100 ft, TL=250 ft, D=500 ft, M=1000 ft