



## DLAWS1-24D3



- Hybrid SAD-GDT Technology
- UL497B LISTED
- 20kA I<sub>max</sub> (1x 8/20us)
- 5kA I<sub>mp</sub> (2x 10/350us)
- 5kA I<sub>n</sub> (10x 8/20us)
- Modular with Fault Indicator
- 2W+SHIELD+G
- Common/Differential Mode Protection

	<table border="1"> <thead> <tr> <th colspan="2">Electrical Characteristics</th> </tr> </thead> <tbody> <tr> <td>Insertion loss</td> <td>&lt; 1 dB</td> </tr> <tr> <td>Protection mode(s)</td> <td>Common/Differential mode</td> </tr> <tr> <td>Nominal discharge current C2 Category</td> <td>In 5 kA</td> </tr> <tr> <td>DATA SPD TYPE</td> <td>UL497B LISTED</td> </tr> <tr> <td>VOLTS</td> <td>(V) 24</td> </tr> <tr> <td>WIRES</td> <td>2W+SHIELD+GROUND</td> </tr> <tr> <td>LINE CURRENT MAX</td> <td>(A) 0.3</td> </tr> <tr> <td>AMBIENT MIN</td> <td>(C) -50</td> </tr> <tr> <td>AMBIENT MAX</td> <td>(C) +85</td> </tr> <tr> <td>IN10 impulses 8/20µs</td> <td>(kA) 5</td> </tr> <tr> <td>IMAX8/20µs</td> <td>(kA) 20</td> </tr> <tr> <td>Iimp10/350µs</td> <td>(kA) 5</td> </tr> </tbody> </table>	Electrical Characteristics		Insertion loss	< 1 dB	Protection mode(s)	Common/Differential mode	Nominal discharge current C2 Category	In 5 kA	DATA SPD TYPE	UL497B LISTED	VOLTS	(V) 24	WIRES	2W+SHIELD+GROUND	LINE CURRENT MAX	(A) 0.3	AMBIENT MIN	(C) -50	AMBIENT MAX	(C) +85	IN10 impulses 8/20µs	(kA) 5	IMAX8/20µs	(kA) 20	Iimp10/350µs	(kA) 5										
Electrical Characteristics																																					
Insertion loss	< 1 dB																																				
Protection mode(s)	Common/Differential mode																																				
Nominal discharge current C2 Category	In 5 kA																																				
DATA SPD TYPE	UL497B LISTED																																				
VOLTS	(V) 24																																				
WIRES	2W+SHIELD+GROUND																																				
LINE CURRENT MAX	(A) 0.3																																				
AMBIENT MIN	(C) -50																																				
AMBIENT MAX	(C) +85																																				
IN10 impulses 8/20µs	(kA) 5																																				
IMAX8/20µs	(kA) 20																																				
Iimp10/350µs	(kA) 5																																				
 <p>G: 3-electrode gas tube Gb: 2-electrode gas tube PTC: Thermal resistor R: Resistor D : Clamping diode Vi : Indicator</p>	<table border="1"> <thead> <tr> <th colspan="2">Mechanical Characteristics</th> </tr> </thead> <tbody> <tr> <td>With line cut-off in case of removal plug-in module</td> <td>Yes</td> </tr> <tr> <td>TECHNOLOGY</td> <td>SAD-GDT</td> </tr> <tr> <td>NETWORK CONFIGURATION</td> <td>1 Channel (2W+SHIELD+G)</td> </tr> <tr> <td>CONNECTION METHOD</td> <td>Screw Terminal (16-22AWG)</td> </tr> <tr> <td>MOUNTING</td> <td>DIN RAIL</td> </tr> <tr> <td>MATERIAL</td> <td>Thermoplastic UL94-V0</td> </tr> <tr> <td>NEMA RATING (IP RATING)</td> <td>NEMA 2 (IP20)</td> </tr> <tr> <td>DIMENSIONS</td> <td>See diagram</td> </tr> <tr> <td>WEIGHT</td> <td>0.30 lbs</td> </tr> </tbody> </table> <table border="1"> <thead> <tr> <th colspan="2">Standards</th> </tr> </thead> <tbody> <tr> <td>UL STANDARD</td> <td>UL497B</td> </tr> <tr> <td>UL CATEGORY</td> <td>QVGQ</td> </tr> <tr> <td>UL FILE NUMBER</td> <td>E184939</td> </tr> <tr> <td>STANDARDS</td> <td>IEC 61643-11, NOM-003-SCFI-2014, NOM-001-SCFI-1993</td> </tr> <tr> <td>ENVIRONMENTAL STANDARDS</td> <td>ROHS</td> </tr> </tbody> </table> <table border="1"> <thead> <tr> <th colspan="2">Part number</th> </tr> </thead> <tbody> <tr> <td colspan="2">6419031</td> </tr> </tbody> </table>	Mechanical Characteristics		With line cut-off in case of removal plug-in module	Yes	TECHNOLOGY	SAD-GDT	NETWORK CONFIGURATION	1 Channel (2W+SHIELD+G)	CONNECTION METHOD	Screw Terminal (16-22AWG)	MOUNTING	DIN RAIL	MATERIAL	Thermoplastic UL94-V0	NEMA RATING (IP RATING)	NEMA 2 (IP20)	DIMENSIONS	See diagram	WEIGHT	0.30 lbs	Standards		UL STANDARD	UL497B	UL CATEGORY	QVGQ	UL FILE NUMBER	E184939	STANDARDS	IEC 61643-11, NOM-003-SCFI-2014, NOM-001-SCFI-1993	ENVIRONMENTAL STANDARDS	ROHS	Part number		6419031	
Mechanical Characteristics																																					
With line cut-off in case of removal plug-in module	Yes																																				
TECHNOLOGY	SAD-GDT																																				
NETWORK CONFIGURATION	1 Channel (2W+SHIELD+G)																																				
CONNECTION METHOD	Screw Terminal (16-22AWG)																																				
MOUNTING	DIN RAIL																																				
MATERIAL	Thermoplastic UL94-V0																																				
NEMA RATING (IP RATING)	NEMA 2 (IP20)																																				
DIMENSIONS	See diagram																																				
WEIGHT	0.30 lbs																																				
Standards																																					
UL STANDARD	UL497B																																				
UL CATEGORY	QVGQ																																				
UL FILE NUMBER	E184939																																				
STANDARDS	IEC 61643-11, NOM-003-SCFI-2014, NOM-001-SCFI-1993																																				
ENVIRONMENTAL STANDARDS	ROHS																																				
Part number																																					
6419031																																					