



SKU # RS-3528-5MR

Part # 1004013

Description

16ft (5M) 3528 LED Custom Tape Strip Reel Lighting (Red)

Categories

Auto Interior & Exterior, LED Tape Strip Lighting, 110-Volt, Marine Sport Lighting

Sub-Categories

LED Tape & POD strips, 3528 Consumer Tape Strip Reels, 16FT 110V Waterproof Light Strips

UPC 817363011297

Unit of Measure EA

Related Skus:

Cross Sell Skus:

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

Interior Tape Strip LED

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

SEMA Product Interior Accent Light

Part Type ID 18826

Reverse Polarity

Interior Accent Light

Operating Voltage

Current Draw

Wattage

Chip Type

IP Rating

IP67

LUX

Product Information

Super bright, universal lighting solution for your home, office, business, or any other application • 120° viewing angle, perfect for any area • Able to be cut at 3 LED intervals (approximately every 2") for virtually any application • Maintenance free, easy installation • Improved adhesive backing for better, longer lasting application • 100,000+ hour lifetime • IP65 Water Resistant • 1 Year Warranty

Est. Labor

Hours

Gross Weight

1.50

Width

7.50

Net Weight

1.50

Height

4.00

DIM Weight

2.16

Depth

10.00

Kelvin (ColorTemperature)

Red

Universal or Vehicle Specific

Universal

Made In

China

Warranty

1 year

Lumens

Beam Pattern

Linear

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

www.racesportinc.com

