



SKU # RS-5050-164FT-RGB

Part # 1004061

Description

110V Atmosphere Waterproof 5050 LED Strip Lighting (RGB Multi-Color)

Categories 110-Volt

Sub-Categories 164FT 110V 5050 Atmosphere Lighting Reels - RGB

UPC 811712025560

Unit of Measure EA

Related Skus:

Cross Sell Skus:

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

Atmosphere Lighting Reels

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

SEMA Product Interior Accent Light

Part Type ID 18826

Reverse Polarity

Interior Accent Light

Operating Voltage

110VAC

Current Draw

Wattage

Chip Type

IP Rating

IP67

LUX

Kelvin (ColorTemperature)

RGB

Universal or Vehicle Specific

Universal

Made In

China


Warranty

1 year

Lumens

Beam Pattern

Linear



Product Information

110V Atmosphere Waterproof 5050 LED Strip Lighting (RGB Multi-Color)

Est. Labor

Hours

Gross Weight

17.60

Width

13.00

Net Weight

17.60

Height

6.00

DIM Weight

7.29

Depth

13.00

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

www.racesportinc.com