

VL22



Value Lift Electric Base

- 2 Motor 2 Stage
- 4 Memory, 1 USB Controller with LED Display
- Steel frame construction for stability
- Weight capacity: 260 lbs.
- Available in Black -BLK, Brushed Silver -BS, or White -WH
- Includes Cable Cover



**Included Cable Management Cover
Keeps Cords Organized and Out of Sight**

Paint



Silver

White

Black

Item	Dual motor 2stage base
SKU	22000-BLK/WH/BS
Keypads	U/P+4memory+1USB port
Carton Size	42.32"x10.82"x7.87"
Weight G/N	59lbs/53.57lbs (26.8/24.3kgs)
Bracket size	22.64"
Feet size	23.62"
Frame width range	42.32"-70.86"
Frame height range	27.17"-44.88"
Max loading	260lbs
Speed	1.25"/s
Suit top size reference	Length 48", 60", 72" Depth 24", 30"



office furniture distributors