

Digital Portion Control Scale, 11 lb

Model: SD1112

A member of the *Master Scales* series, this exclusive NSF[®] Certified scale was designed for demanding foodservice kitchens. It features data-hold and field calibration to ensure accuracy over time. Medium profile and BioCote[®] antimicrobial technology. Batteries and power adapter included.



Features	Selectable units, tare function, data-hold, field calibration, overload indication, battery status indication, removable stainless steel platform, on/off button, AC adapter
Certification	NSF [®] Certified, WEEE, CE
Antimicrobial Protection	BioCote [®]
Measurement Range	11 lb/5 kg capacity
Unit of Measure	lb:oz/kg.g
Tare	Tare function
Accuracy	2 kg ±6g; 5 kg ±15g
Calibration	Field calibration
Water Resilience	IP54: protected from water splashes from any direction for 10 minutes; dust protected
Response Time	0.125 second response
On/Off	On/off button
Auto-off	Auto-off after 2 minutes; disabled when the AC adapter is used
Housing Material	Food-safe ABS plastic
Display Material	LCD
Display Size	3.35 W x 0.866 H (in)/8.5 W x 2.2 H (cm)
Load Cell	Single point load cell
Platform Material	304 stainless steel
Platform Size	7.12 W x 7.12 H (in)/18.1 W x 18.1 H (cm), removable
Resolution	0.1 oz, 1 g
Operating Range	32 to 104°F/0 to 40°C/≤90% RH
Power	AC Adapter: 100-240 VAC 50/60 Hz input, 9V DC (500mA) output
Battery	Two 1.5V AAA IEC LR03 alkaline batteries, included
Battery Life	2 years (3 times/day, 30 s/time)
Dimensions	7.48 W x 2.188 H x 9.72 D (in)/19.0 W x 5.56 H x 24.7 D (cm)
Weight	46.2 oz / 1309 g (including battery)
Warranty	1-Year Limited Warranty
Optional Accessories	5 kg Calibration Weight (WT05), Medium Profile Platform (AD-PF1112), Power Adapter (AD-AC3302)
Replacement Parts	Medium Profile Platform (AD-PF1112), Power Adapter (AD-AC3302)