



SAFETY DATA SHEET

1. Identification

Product number 1000002391
Product identifier 11 OZ CAMIE 1080 PNTABLE MLD RLS LT 12PK
Revision date 06-25-2018
Company information Camie-Campbell, Inc.
 1000 INTEGRAM DRIVE
 PACIFIC, MO 63069 United States
 www.camie.com
Company phone General Assistance 1-800-325-9572
Emergency telephone US 1-866-836-8855
Emergency telephone outside US 1-952-852-4646
Version # 02
Supersedes date 04-25-2017
Recommended use Not available.
Recommended restrictions None known.

2. Hazard(s) identification

Physical hazards Flammable aerosols Category 1
Health hazards Skin corrosion/irritation Category 2
 Reproductive toxicity Category 2
 Specific target organ toxicity, repeated exposure Category 2
 Aspiration hazard Category 1
OSHA defined hazards Not classified.

Label elements



Signal word Danger
Hazard statement Extremely flammable aerosol. May be fatal if swallowed and enters airways. Causes skin irritation. Suspected of damaging fertility or the unborn child. May cause damage to organs through prolonged or repeated exposure.

Precautionary statement

Prevention Obtain special instructions before use. Do not handle until all safety precautions have been read and understood. Keep away from heat/sparks/open flames/hot surfaces. - No smoking. Do not spray on an open flame or other ignition source. Pressurized container: Do not pierce or burn, even after use. Do not breathe gas. Wash thoroughly after handling. Wear protective gloves/protective clothing/eye protection/face protection.

Response If swallowed: Immediately call a poison center/doctor. Do NOT induce vomiting. If on skin: Wash with plenty of water. If exposed or concerned: Get medical advice/attention. If skin irritation occurs: Get medical advice/attention. Take off contaminated clothing and wash before reuse.

Storage Store locked up. Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F.

Disposal Dispose of contents/container in accordance with local/regional/national/international regulations.

Environmental hazards Hazardous to the aquatic environment, acute hazard Category 3
 Hazardous to the aquatic environment, long-term hazard Category 3

Hazard(s) not otherwise classified (HNOC) None known.
Supplemental information None.

3. Composition/information on ingredients

Mixtures

Chemical name	Common name and synonyms	CAS number	%
Butane		106-97-8	60 - 80
n-Hexane		110-54-3	10 - 20
2-Methylpentane		107-83-5	2.5 - 10
Propane		74-98-6	2.5 - 10
Other components below reportable levels			2.5 - 10

*Designates that a specific chemical identity and/or percentage of composition has been withheld as a trade secret.

4. First-aid measures

Inhalation Move to fresh air. Call a physician if symptoms develop or persist.

Skin contact Remove contaminated clothing. Wash with plenty of soap and water. If skin irritation occurs: Get medical advice/attention. Wash contaminated clothing before reuse.

Eye contact Rinse with water. Get medical attention if irritation develops and persists.

Ingestion Call a physician or poison control center immediately. Rinse mouth. Do not induce vomiting. If vomiting occurs, keep head low so that stomach content doesn't get into the lungs.

Most important symptoms/effects, acute and delayed Aspiration may cause pulmonary edema and pneumonitis. Skin irritation. May cause redness and pain. Prolonged exposure may cause chronic effects.

Indication of immediate medical attention and special treatment needed Provide general supportive measures and treat symptomatically. Keep victim under observation. Symptoms may be delayed.

General information IF exposed or concerned: Get medical advice/attention. If you feel unwell, seek medical advice (show the label where possible). Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves. Show this safety data sheet to the doctor in attendance.

5. Fire-fighting measures

Suitable extinguishing media Foam. Powder. Carbon dioxide (CO₂).

Unsuitable extinguishing media Do not use water jet as an extinguisher, as this will spread the fire.

Specific hazards arising from the chemical Contents under pressure. Pressurized container may explode when exposed to heat or flame. During fire, gases hazardous to health may be formed.

Special protective equipment and precautions for firefighters Firefighters must use standard protective equipment including flame retardant coat, helmet with face shield, gloves, rubber boots, and in enclosed spaces, SCBA.

Fire fighting equipment/instructions Move containers from fire area if you can do so without risk. Containers should be cooled with water to prevent vapor pressure build up. For massive fire in cargo area, use unmanned hose holder or monitor nozzles, if possible. If not, withdraw and let fire burn out.

Specific methods Use standard firefighting procedures and consider the hazards of other involved materials. Move containers from fire area if you can do so without risk. In the event of fire and/or explosion do not breathe fumes.

General fire hazards Extremely flammable aerosol.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures Keep unnecessary personnel away. Keep people away from and upwind of spill/leak. Wear appropriate protective equipment and clothing during clean-up. Do not breathe gas. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Ventilate closed spaces before entering them. Local authorities should be advised if significant spillages cannot be contained. For personal protection, see section 8 of the SDS.

Methods and materials for containment and cleaning up

Refer to attached safety data sheets and/or instructions for use. Stop leak if you can do so without risk. Move the cylinder to a safe and open area if the leak is irreparable. Isolate area until gas has dispersed. Eliminate all ignition sources (no smoking, flares, sparks, or flames in immediate area). Keep combustibles (wood, paper, oil, etc.) away from spilled material. Prevent product from entering drains. Cover with plastic sheet to prevent spreading. Absorb in vermiculite, dry sand or earth and place into containers. Following product recovery, flush area with water.

Small Spills: Wipe up with absorbent material (e.g. cloth, fleece). Clean surface thoroughly to remove residual contamination. For waste disposal, see section 13 of the SDS.

Environmental precautions

Avoid release to the environment. Inform appropriate managerial or supervisory personnel of all environmental releases. Prevent further leakage or spillage if safe to do so. Avoid discharge into drains, water courses or onto the ground.

7. Handling and storage**Precautions for safe handling**

Obtain special instructions before use. Do not handle until all safety precautions have been read and understood. Pressurized container: Do not pierce or burn, even after use. Do not use if spray button is missing or defective. Do not spray on a naked flame or any other incandescent material. Do not smoke while using or until sprayed surface is thoroughly dry. Do not cut, weld, solder, drill, grind, or expose containers to heat, flame, sparks, or other sources of ignition. All equipment used when handling the product must be grounded. Do not re-use empty containers. Do not breathe gas. Avoid contact with eyes, skin, and clothing. Pregnant or breastfeeding women must not handle this product. Should be handled in closed systems, if possible. Use only in well-ventilated areas. Wear appropriate personal protective equipment. Wash hands thoroughly after handling. Avoid release to the environment. Observe good industrial hygiene practices.

Conditions for safe storage, including any incompatibilities

Level 3 Aerosol.

Store locked up. Pressurized container. Protect from sunlight and do not expose to temperatures exceeding 50°C/122 °F. Do not puncture, incinerate or crush. Do not handle or store near an open flame, heat or other sources of ignition. This material can accumulate static charge which may cause spark and become an ignition source. Store away from incompatible materials (see Section 10 of the SDS).

8. Exposure controls/personal protection**Occupational exposure limits****US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)**

Components	Type	Value
n-Hexane (CAS 110-54-3)	PEL	1800 mg/m3 500 ppm
Propane (CAS 74-98-6)	PEL	1800 mg/m3 1000 ppm

US. ACGIH Threshold Limit Values

Components	Type	Value
2-Methylpentane (CAS 107-83-5)	STEL	1000 ppm
	TWA	500 ppm
Butane (CAS 106-97-8)	STEL	1000 ppm
n-Hexane (CAS 110-54-3)	TWA	50 ppm

US. NIOSH: Pocket Guide to Chemical Hazards

Components	Type	Value
Butane (CAS 106-97-8)	TWA	1900 mg/m3 800 ppm
n-Hexane (CAS 110-54-3)	TWA	180 mg/m3 50 ppm
Propane (CAS 74-98-6)	TWA	1800 mg/m3 1000 ppm

Biological limit values

ACGIH Biological Exposure Indices

Components	Value	Determinant	Specimen	Sampling Time
n-Hexane (CAS 110-54-3)	0.4 mg/l	2,5-Hexanedio n, without hydrolysis	Urine	*

* - For sampling details, please see the source document.

Exposure guidelines

US - California OELs: Skin designation

n-Hexane (CAS 110-54-3)

Can be absorbed through the skin.

US ACGIH Threshold Limit Values: Skin designation

n-Hexane (CAS 110-54-3)

Can be absorbed through the skin.

Appropriate engineering controls

Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level. Eye wash facilities and emergency shower must be available when handling this product.

Individual protection measures, such as personal protective equipment

Eye/face protection Wear safety glasses with side shields (or goggles).

Skin protection

Hand protection

Wear appropriate chemical resistant gloves. Suitable gloves can be recommended by the glove supplier.

Other

Wear appropriate chemical resistant clothing. Use of an impervious apron is recommended.

Respiratory protection

If permissible levels are exceeded use NIOSH mechanical filter / organic vapor cartridge or an air-supplied respirator.

Thermal hazards

Wear appropriate thermal protective clothing, when necessary.

General hygiene considerations

Observe any medical surveillance requirements. When using do not smoke. Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants.

9. Physical and chemical properties

Appearance

Physical state

Gas.

Form

Aerosol.

Color

Not available.

Odor

Not available.

Odor threshold

Not available.

pH

Not available.

Melting point/freezing point

Not available.

Initial boiling point and boiling range

95 °F (35 °C) estimated

Flash point

-156.0 °F (-104.4 °C) propellant estimated

Evaporation rate

Not available.

Flammability (solid, gas)

Not available.

Upper/lower flammability or explosive limits

Flammability limit - lower (%)

1 % estimated

Flammability limit - upper (%)

7.6 % estimated

Explosive limit - lower (%)

Not available.

Explosive limit - upper (%)

Not available.

Vapor pressure

Not available.

Vapor density

Not available.

Relative density	Not available.
Solubility(ies)	
Solubility (water)	Not available.
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	518.95 °F (270.53 °C) estimated
Decomposition temperature	Not available.
Viscosity	Not available.
Other information	
Explosive properties	Not explosive.
Oxidizing properties	Not oxidizing.
Specific gravity	0.126 estimated

10. Stability and reactivity

Reactivity	The product is stable and non-reactive under normal conditions of use, storage and transport.
Chemical stability	Material is stable under normal conditions.
Possibility of hazardous reactions	Hazardous polymerization does not occur.
Conditions to avoid	Avoid temperatures exceeding the flash point. Contact with incompatible materials.
Incompatible materials	Strong oxidizing agents. Nitrates. Fluorine. Chlorine.
Hazardous decomposition products	No hazardous decomposition products are known.

11. Toxicological information

Information on likely routes of exposure

Inhalation	May cause damage to organs through prolonged or repeated exposure by inhalation.
Skin contact	Causes skin irritation.
Eye contact	Direct contact with eyes may cause temporary irritation.
Ingestion	Droplets of the product aspirated into the lungs through ingestion or vomiting may cause a serious chemical pneumonia.

Symptoms related to the physical, chemical and toxicological characteristics	Aspiration may cause pulmonary edema and pneumonitis. Skin irritation. May cause redness and pain.
---	--

Information on toxicological effects

Acute toxicity	May be fatal if swallowed and enters airways.
-----------------------	---

Components	Species	Test Results
Butane (CAS 106-97-8)		
Acute		
Inhalation		
LC50	Mouse	1237 mg/l, 120 Minutes
		52 %, 120 Minutes
	Rat	1355 mg/l
n-Hexane (CAS 110-54-3)		
Acute		
Dermal		
LD50	Rabbit	> 2000 mg/kg, 4 Hours
		> 5 ml/kg, 4 Hours
Inhalation		
LC50	Rat	> 5000 ppm, 24 Hours
		> 31.86 mg/l
		73860 ppm, 4 Hours

Components	Species	Test Results
Oral		
LD50	Rat	24 ml/kg 24 g/kg
	Wistar rat	49 g/kg
Propane (CAS 74-98-6)		
Acute		
Inhalation		
LC50	Mouse	1237 mg/l, 120 Minutes 52 %, 120 Minutes
	Rat	1355 mg/l 658 mg/l/4h

* Estimates for product may be based on additional component data not shown.

Skin corrosion/irritation	Causes skin irritation.
Serious eye damage/eye irritation	Direct contact with eyes may cause temporary irritation.
Respiratory or skin sensitization	
Respiratory sensitization	Not a respiratory sensitizer.
Skin sensitization	This product is not expected to cause skin sensitization.
Germ cell mutagenicity	No data available to indicate product or any components present at greater than 0.1% are mutagenic or genotoxic.
Carcinogenicity	This product is not considered to be a carcinogen by IARC, ACGIH, NTP, or OSHA.
IARC Monographs. Overall Evaluation of Carcinogenicity	Not listed.
OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)	Not regulated.
US. National Toxicology Program (NTP) Report on Carcinogens	Not listed.
Reproductive toxicity	Suspected of damaging fertility or the unborn child.
Specific target organ toxicity - single exposure	Not classified.
Specific target organ toxicity - repeated exposure	Respiratory system. Skin. Central nervous system. Eyes. Peripheral nervous system. May cause damage to organs through prolonged or repeated exposure.
Aspiration hazard	May be fatal if swallowed and enters airways.
Chronic effects	May cause damage to organs through prolonged or repeated exposure.

12. Ecological information

Ecotoxicity	Harmful to aquatic life with long lasting effects.		
Components	Species	Test Results	
n-Hexane (CAS 110-54-3)			
Aquatic			
Fish	LC50	Fathead minnow (Pimephales promelas) 2.101 - 2.981 mg/l, 96 hours	

* Estimates for product may be based on additional component data not shown.

Persistence and degradability No data is available on the degradability of this product.

Bioaccumulative potential

Partition coefficient n-octanol / water (log Kow)

2-Methylpentane	3.74
Butane	2.89
n-Hexane	3.9
Propane	2.36

Mobility in soil No data available.

Other adverse effects No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.

13. Disposal considerations

Disposal instructions Collect and reclaim or dispose in sealed containers at licensed waste disposal site. Contents under pressure. Do not puncture, incinerate or crush. Do not allow this material to drain into sewers/water supplies. Do not contaminate ponds, waterways or ditches with chemical or used container. Dispose of contents/container in accordance with local/regional/national/international regulations.

Local disposal regulations Dispose in accordance with all applicable regulations.

Hazardous waste code The waste code should be assigned in discussion between the user, the producer and the waste disposal company.

Waste from residues / unused products Dispose of in accordance with local regulations. Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe manner (see: Disposal instructions).

Contaminated packaging Since emptied containers may retain product residue, follow label warnings even after container is emptied. Empty containers should be taken to an approved waste handling site for recycling or disposal. Do not re-use empty containers.

14. Transport information

DOT

UN number UN1950
UN proper shipping name Aerosols, flammable, (each not exceeding 1 L capacity)
Transport hazard class(es)
Class 2.1
Subsidiary risk -
Label(s) 2.1
Packing group Not applicable.
Special precautions for user Read safety instructions, SDS and emergency procedures before handling.
Special provisions N82
Packaging exceptions 306
Packaging non bulk None
Packaging bulk None

This product meets the exception requirements of section 173.306 as a limited quantity and may be shipped as a limited quantity. Until 12/31/2020, the "Consumer Commodity - ORM-D" marking may still be used in place of the new limited quantity diamond mark for packages of UN 1950 Aerosols. Limited quantities require the limited quantity diamond mark on cartons after 12/31/20 and may be used now in place of the "Consumer Commodity ORM-D" marking.

IATA

UN number UN1950
UN proper shipping name Aerosols, flammable
Transport hazard class(es)
Class 2.1
Subsidiary risk -
Label(s) 2.1
Packing group Not applicable.
Environmental hazards No.
ERG Code 10L
Special precautions for user Read safety instructions, SDS and emergency procedures before handling. Read safety instructions, SDS and emergency procedures before handling.

Other information
Passenger and cargo aircraft Allowed with restrictions.
Cargo aircraft only Allowed with restrictions.
Packaging Exceptions LTD QTY

IMDG

UN number UN1950
UN proper shipping name AEROSOLS
Transport hazard class(es)
Class 2.1
Subsidiary risk -
Label(s) None
Packing group Not applicable.

Environmental hazards

Marine pollutant

No.

EmS

F-D, S-U

Special precautions for user

Read safety instructions, SDS and emergency procedures before handling. Read safety instructions, SDS and emergency procedures before handling.

Packaging Exceptions

LTD QTY

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

Not applicable.

DOT



IATA; IMDG



15. Regulatory information

US federal regulations

This product is a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200.

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

CERCLA Hazardous Substance List (40 CFR 302.4)

n-Hexane (CAS 110-54-3)

Listed.

SARA 304 Emergency release notification

Not regulated.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)

Not regulated.

Superfund Amendments and Reauthorization Act of 1986 (SARA)

Hazard categories

Immediate Hazard - Yes
Delayed Hazard - Yes
Fire Hazard - Yes
Pressure Hazard - No
Reactivity Hazard - No

SARA 302 Extremely hazardous substance

Not listed.

SARA 311/312 Hazardous chemical

No

SARA 313 (TRI reporting)

Chemical name	CAS number	% by wt.
n-Hexane	110-54-3	10 - 20

Other federal regulations

Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List

n-Hexane (CAS 110-54-3)

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Butane (CAS 106-97-8)

Propane (CAS 74-98-6)

Safe Drinking Water Act (SDWA) Not regulated.

US state regulations

US. California Controlled Substances. CA Department of Justice (California Health and Safety Code Section 11100)

Not listed.

US. California. Candidate Chemicals List. Safer Consumer Products Regulations (Cal. Code Regs, tit. 22, 69502.3, subd. (a))

Butane (CAS 106-97-8)

n-Hexane (CAS 110-54-3)

US. Massachusetts RTK - Substance List

2-Methylpentane (CAS 107-83-5)

Butane (CAS 106-97-8)

n-Hexane (CAS 110-54-3)

Propane (CAS 74-98-6)

US. New Jersey Worker and Community Right-to-Know Act

2-Methylpentane (CAS 107-83-5)

Butane (CAS 106-97-8)

n-Hexane (CAS 110-54-3)

Propane (CAS 74-98-6)

US. Pennsylvania Worker and Community Right-to-Know Law

2-Methylpentane (CAS 107-83-5)

Butane (CAS 106-97-8)

n-Hexane (CAS 110-54-3)

Propane (CAS 74-98-6)

US. Rhode Island RTK

Butane (CAS 106-97-8)

n-Hexane (CAS 110-54-3)

Propane (CAS 74-98-6)

US. California Proposition 65

WARNING: This product contains a chemical known to the State of California to cause birth defects or other reproductive harm.

International Inventories

Country(s) or region	Inventory name	On inventory (yes/no)*
Australia	Australian Inventory of Chemical Substances (AICS)	No
Canada	Domestic Substances List (DSL)	Yes
Canada	Non-Domestic Substances List (NDSL)	No
China	Inventory of Existing Chemical Substances in China (IECSC)	No
Europe	European Inventory of Existing Commercial Chemical Substances (EINECS)	No
Europe	European List of Notified Chemical Substances (ELINCS)	No
Japan	Inventory of Existing and New Chemical Substances (ENCS)	No
Korea	Existing Chemicals List (ECL)	No
New Zealand	New Zealand Inventory	No
Philippines	Philippine Inventory of Chemicals and Chemical Substances (PICCS)	No
United States & Puerto Rico	Toxic Substances Control Act (TSCA) Inventory	Yes

*A "Yes" indicates that all components of this product comply with the inventory requirements administered by the governing country(s)

A "No" indicates that one or more components of the product are not listed or exempt from listing on the inventory administered by the governing country(s).

16. Other information, including date of preparation or last revision

Issue date 04-25-2017

Product name: 11 OZ CAMIE 1080 PNTABLE MLD RLS LT 12PK

SDS US

Product #: 1000002391 Version #: 02 Revision date: 06-25-2018 Issue date: 04-25-2017

9 / 10

Revision date 06-25-2018

Version # 02

Disclaimer The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

Revision information Fire-fighting measures: General fire hazards
Toxicological information: Carcinogenicity
Toxicological information: Mutagenicity
Toxicological information: Respiratory sensitization
Toxicological information: Skin contact
Toxicological information: Specific target organ toxicity - single exposure
Regulatory information: California Prop 65
GHS: Classification