

Safety Data Sheet

Classified in accordance 29 CFR 1910.1200

1. Product Identification

Product Information: 1000010168

Product Identifier: CLAIRE BUG BUSTER INSECT KILLER- EPA 706-107

Recommended Use: Pesticide

Manufacturer/Importer/Distributor Information: PLZ CORP
2651 WARRENVILLE RD, STE 300
DOWNERS GROVE, IL 60515
US
800-332-9000

Emergency Telephone: 866-836-8855

2. Hazard(s) identification

Classification

Flammable Aerosol, category 1

Label elements

HAZARD PICTOGRAMS



SIGNAL WORD

Danger

GHS HAZARD STATEMENTS

H222 Extremely flammable aerosol.

GHS PRECAUTIONARY STATEMENTS

Prevention

P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.

P211 Do not spray on an open flame or other ignition source.

P251 Do not pierce or burn, even after use.

Response

None

Storage

P410+P412 Protect from sunlight. Do not expose to temperatures exceeding 50°C/ 122°F.

Disposal

None

Other Information

None

3. Composition/Information on Ingredients

Mixtures

<u>Chemical Identity</u>	<u>CAS Number</u>	<u>Content in Percent (%)*</u>
Propane	74-98-6	2.5-10
Butane	106-97-8	2.5-10
Distillates (Petroleum), Hydrotreated Light	64742-47-8	2.5-10
Piperonyl Butoxide	51-03-6	2.5-10
Pyrethrins	8003-34-7	0.1-1.0

* All concentrations are percent by weight unless ingredient is a gas. Gas concentrations are in percent by volume.

Composition Comments: Other components are not hazardous or are below required disclosure limits.

The exact concentration has been withheld as a trade secret.

4. First-aid Measures

SKIN CONTACT: Remove contaminated clothing and wash the skin thoroughly with soap and water after work.

EYE CONTACT: Rinse immediately with plenty of water.

INHALATION: Move to fresh air.

INGESTION: Rinse mouth.

IMPORTANT SYMPTOMS: No data available

INDICATION OF IMMEDIATE MEDICAL ATTENTION AND SPECIAL TREATMENT NEEDED: Get medical attention if symptoms occur.

5. Fire-fighting Measures

EXTINGUISHING MEDIA: Use fire-extinguishing media appropriate for surrounding materials.

UNSUITABLE EXTINGUISHING MEDIA: Do not use water jet as an extinguisher, as this will spread the fire.

UNUSUAL FIRE AND EXPLOSION HAZARDS: No data available

SPECIAL FIREFIGHTING PROCEDURES: No data available

6. Accidental Release Measures

PERSONAL PRECAUTIONS : Ventilate closed spaces before entering them. ELIMINATE all ignition sources (no smoking, flares, sparks or flames in immediate area). Keep upwind.

METHODS AND MATERIALS FOR CONTAINMENT AND CLEANUP: Stop the flow of material, if this is without risk. Absorb with sand or other inert absorbent.

ENVIRONMENTAL PRECAUTIONS: Avoid release to the environment. Prevent further leakage or spillage if safe to do so. Do not contaminate water sources or sewer. Environmental manager must be informed of all major spillages.

7. Handling and Storage

HANDLING: Keep away from sources of ignition - No smoking. Keep away from open flames, hot surfaces and sources of ignition. Do not spray on an open flame or other ignition source. Pressurized container: Do not pierce or burn, even after use.

SAFE HANDLING ADVICE: Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. Do not spray on an open flame or other ignition source. Pressurized container: Do not pierce or burn, even after use.

STORAGE: Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use.

NFPA 30B: Aerosol Level 1

8. Exposure Controls/Personal Protection

Ingredients with Occupational Exposure Limits

<u>Chemical Name</u>	<u>TLV-TWA</u>	<u>TLV-STEL</u>	<u>PEL-TWA</u>	<u>PEL-CEILING</u>
Propane	N.E.	N.E.	1000 ppm	N.E.
Butane	N.E.	1000 ppm	N.E.	N.E.
Distillates (Petroleum), Hydrotreated Light	200 mg/m ³	N.E.	N.E.	N.E.
Piperonyl Butoxide	N.E.	N.E.	N.E.	N.E.
Pyrethrins	5 mg/m ³	N.E.	5 mg/m ³	N.E.

Further Advice: MEL = Maximum Exposure Limit OES = Occupational Exposure Standard SUP = Supplier's Recommendation
Sk = Skin Sensitizer N.E. = Not Established

ENGINEERING CONTROLS: No data available.

Personal Protection

EYE/FACE PROTECTION: Wear goggles/face shield.

SKIN PROTECTION: No data available

RESPIRATORY PROTECTION: Seek advice from local supervisor. In case of inadequate ventilation use suitable respirator.

HYGIENIC PRACTICES: When using do not smoke. Observe good industrial hygiene practices.

9. Physical and Chemical Properties

Appearance:

Physical State:	Liquid
Form:	Spray Aerosol
Color:	White
Odor:	cherry
Odor Threshold:	No data available
pH:	No data available
Freeze Point, °C:	No data available
Boiling Point, °C:	174
Flash Point, °C:	-104
Flammability (solid, gas):	No data available
Evaporation Rate:	No data available
Combustibility:	Supports Combustion
Explosive Limits, %:	0.5 - 9.5
Vapor Pressure @20°C, PSI:	75-95 PSI
Vapor Density:	No data available
Relative Density:	0.894
Solubility in Water:	No data available
Partition Coefficient, n-octanol/water:	No data available
Auto-Ignition Temperature, °C:	No data available
Decomposition temperature, °C:	No data available
Kinematic Viscosity:	No data available

10. Stability and Reactivity

REACTIVITY: No data available.

STABILITY: Material is stable under normal conditions.

POSSIBILITY OF HAZARDOUS REACTIONS: No data available.

CONDITIONS TO AVOID: Avoid heat or contamination

INCOMPATIBILITY: No data available

HAZARDOUS DECOMPOSITION PRODUCTS: No data available.

11. Toxicological Information

Information on Likely Routes of Exposure

IMPORTANT SYMPTOMS: No data available

SKIN CONTACT EFFECTS: May cause irritation on prolonged or repeated contact.

EYE CONTACT EFFECTS: May cause slight irritation with tearing.

INHALATION EFFECTS: Inhalation of high concentrations of mists may cause irritation of the nose throat and upper respiratory tract.

INGESTION EFFECTS: Ingestion may cause irritation of the mucous membranes, esophagus and stomach.

CHRONIC HAZARDS: No data available

Carcinogenicity: No component of this product present at levels greater than or equal to 0.1% is identified as probable, possible, or confirmed human carcinogen by IARC, ACGIH, NTP or OSHA.

The following values are calculated based on chapter 3.1 of the GHS document. The product itself has not been tested.

<u>ATE ORAL</u>	29,215 mg/kg
<u>ATE DERMAL</u>	14,445 mg/kg
<u>ATE INHALATION</u>	Not classified for acute toxicity based on available data.

Acute Toxicity Values

The acute effects of this product have not been tested. Data on individual components are tabulated below

<u>CAS-No.</u>	<u>Chemical Name</u>	<u>Oral LD50</u>	<u>Dermal LD50</u>	<u>Vapor LC50</u>
74-98-6	Propane	5,000 mg/kg	5,000 mg/kg	100 mg/l
106-97-8	Butane	N.I.	N.I.	658 mg/L Rat
64742-47-8	Distillates (Petroleum), Hydrotreated Light	5,000 mg/kg	2,000 mg/kg	>100 mg/l
51-03-6	Piperonyl Butoxide	5,630 mg/kg	2,000 mg/kg	100 mg/l
8003-34-7	Pyrethrins	500 - 1,000 mg/kg	1,100 mg/kg	11 mg/L Rat

N.I. = No Information

Skin Corrosion & Irritation:

Product: No data available

Serious Eye Damage & Irritation:

Product: No data available

Respiratory or Skin Sensitization:

Product: No data available

STOT-Single Exposure:

Product: No data available

STOT-Repeated Exposure:

Product: No data available

Aspiration Hazard:

Product: No data available

Carcinogenicity:

Product: No data available

Reproductive Toxicity:

Product: No data available

Germ Cell Mutagenicity:

Product: No data available

12. Ecological Information

ECOLOGICAL INFORMATION: No data available

PERSISTENCE: No data available

BIOACCUMULATE: No data available

MOBILITY IN SOIL: No data available

OTHER ECOLOGICAL: No data available

13. Disposal Information

DISPOSAL INFORMATION: Consult with your local, regional and federal agencies for information on proper disposal.

CONTAMINATED PACKAGING : Consult with your local, regional and federal agencies for information on proper disposal.

14. Transport Information

SPECIAL TRANSPORT PRECAUTIONS: No data available

DOT

UN Number:	UN1950
Proper Shipping Name:	AEROSOLS, FLAMMABLE
Technical Name:	N/A
Hazard Class(es)	
Class:	2.1
Subsidiary Risk	N/A
Packing Group:	N/A

IATA

UN Number:	UN1950
Proper Shipping Name:	AEROSOLS, FLAMMABLE
Technical Name:	N/A
Hazard Class(es)	
Class:	2.1
Subsidiary Risk:	N/A
Packing Group:	N/A

IMDG

UN Number: UN1950
Proper Shipping Name: AEROSOLS, FLAMMABLE
Technical Name: N/A
Hazard Class(es)
Class: 2.1
Subsidiary Risk: N/A
Packing Group: N/A

The classification shown in this section may be eligible for use of an exception, such as 'Limited Quantity', per the dangerous goods regulations. The shipper of this product should consult the applicable mode's regulation for the UN number displayed above to determine if any exceptions are available and may be utilized, at the shipper's discretion.

15. Regulatory Information

CHEMICAL INVENTORY STATUS:

TSCA On or in compliance with the inventory
DSL On or in compliance with the inventory

CALIFORNIA PROPOSITION 65 CARCINOGENS AND REPRODUCTIVE TOXINS:

No Proposition 65 chemicals present or warning required.

Further Information: FIFRA: This chemical is a pesticide product registered by the United States Environmental Protection Agency and is subject to certain labeling requirements under federal pesticide law. These requirements differ from the classification criteria and hazard information required for safety data sheets (SDS), and for workplace labels of non-pesticide chemicals. The pesticide label also includes other important information, including directions for use.

16. Other Information

Revision Date: 8/9/2022
Datasheet produced by: Regulatory Department

Legend

N/A. - Not Applicable, N.E. - Not Established, N.D. - Not Determined, N.I. - No Information

TLV - Threshold Limit Values (TLVs®), as established by the American Conference of Governmental Industrial Hygienists (ACGIH®)

PEL - Permissible Exposure Limit, as established by the U.S. Occupational Safety and Health Administration (OSHA), as amended

TSCA - U.S. Toxic Substance Control Act

DSL - Canada Environmental Protection Act: Domestic Substance List

This information is provided without warranty. The information is believed to be correct. This information should be used to make an independent determination of the methods to safeguard workers and the environment.

