



SAFETY DATA SHEET

1. Identification

Product identifier: GELLED BASEBOARD STRIPPER

Other means of identification

SDS number: RE1000010691

Recommended restrictions

Product use: Cleaner

Restrictions on use: Not known.

Manufacturer/Importer/Distributor Information

Manufacturer

Company Name: CLAIRES MANUFACTURING COMPANY
Address: 1000 Integram Dr
Pacific, MO 63069
Telephone: 1-630-543-7600
Fax:

Emergency telephone number: 1-866-836-8855

2. Hazard(s) identification

Hazard Classification

Physical Hazards

Flammable aerosol Category 1

Health Hazards

Skin Corrosion/Irritation Category 2

Serious Eye Damage/Eye Irritation Category 2A

Label Elements

Hazard Symbol:



Signal Word: Danger

Hazard Statement: Extremely flammable aerosol.
Causes skin irritation.
Causes serious eye irritation.

Precautionary Statements



Prevention: Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. Do not spray on an open flame or other ignition source. Do not pierce or burn, even after use. Wash thoroughly after handling. Wear protective gloves/protective clothing/eye protection/face protection.

Response: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention. IF ON SKIN: Wash with plenty of water. If skin irritation occurs: Get medical advice/attention. Specific treatment (see on this label). Take off contaminated clothing.

Storage: Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F.

Hazard(s) not otherwise classified (HNOC): None.

3. Composition/information on ingredients

Mixtures

Chemical Identity	CAS number	Content in percent (%)*
Ethanol, 2-butoxy-	111-76-2	10 - <25%
Butane	106-97-8	5 - <10%
Propane	74-98-6	1 - <5%
Oils, pine	8002-09-3	0.1 - <1%
Sodium hydroxide (Na(OH))	1310-73-2	0.1 - <1%

* All concentrations are percent by weight unless ingredient is a gas. Gas concentrations are in percent by volume.

4. First-aid measures

Ingestion: Call a POISON CENTER/doctor if you feel unwell. Rinse mouth.

Inhalation: Move to fresh air.

Skin Contact: Immediately flush with plenty of water for at least 15 minutes while removing contaminated clothing and shoes. Wash contaminated clothing before reuse. Get medical attention.

Eye contact: Immediately flush with plenty of water for at least 15 minutes. If easy to do, remove contact lenses. Get medical attention.

Most important symptoms/effects, acute and delayed

Symptoms: No data available.

Hazards: No data available.

Indication of immediate medical attention and special treatment needed

Treatment: No data available.

5. Fire-fighting measures

General Fire Hazards: Use water spray to keep fire-exposed containers cool. Fight fire from a protected location. Move containers from fire area if you can do so without risk.

Suitable (and unsuitable) extinguishing media



Suitable extinguishing media: Use fire-extinguishing media appropriate for surrounding materials.
Unsuitable extinguishing media: Do not use water jet as an extinguisher, as this will spread the fire.

Specific hazards arising from the chemical: Vapors may travel considerable distance to a source of ignition and flash back.

Special protective equipment and precautions for firefighters

Special fire fighting procedures: No data available.

Special protective equipment for fire-fighters: Firefighters must use standard protective equipment including flame retardant coat, helmet with face shield, gloves, rubber boots, and in enclosed spaces, SCBA.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures: Ventilate closed spaces before entering them. ELIMINATE all ignition sources (no smoking, flares, sparks or flames in immediate area). Keep upwind. See Section 8 of the SDS for Personal Protective Equipment. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Keep unauthorized personnel away.

Methods and material for containment and cleaning up: Absorb spill with vermiculite or other inert material, then place in a container for chemical waste.

Notification Procedures: Prevent entry into waterways, sewer, basements or confined areas. Stop the flow of material, if this is without risk. ELIMINATE all ignition sources (no smoking, flares, sparks or flames in immediate area). Stop leak if you can do so without risk.

Environmental Precautions: Do not contaminate water sources or sewer. Prevent further leakage or spillage if safe to do so.

7. Handling and storage

Precautions for safe handling: Avoid contact with eyes. Wash hands thoroughly after handling. Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. Do not spray on an open flame or other ignition source. Do not pierce or burn, even after use. Avoid contact with skin.

Conditions for safe storage, including any incompatibilities: Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use. Aerosol Level 1

8. Exposure controls/personal protection

Control Parameters

Occupational Exposure Limits

Chemical Identity	Type	Exposure Limit Values	Source
Ethanol, 2-butoxy-	TWA	20 ppm	US. ACGIH Threshold Limit Values (2008)
	TWA	25 ppm 120 mg/m3	US. OSHA Table Z-1-A (29 CFR 1910.1000) (1989)
	REL	5 ppm 24 mg/m3	US. NIOSH: Pocket Guide to Chemical Hazards (2005)
	PEL	50 ppm 240 mg/m3	US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000) (02 2006)
	REL	800 ppm 1,900 mg/m3	US. NIOSH: Pocket Guide to Chemical Hazards (2005)
Butane	REL	800 ppm 1,900 mg/m3	US. NIOSH: Pocket Guide to Chemical Hazards (2005)



	STEL	1,000 ppm		US. ACGIH Threshold Limit Values (03 2018)
	TWA	800 ppm	1,900 mg/m3	US. OSHA Table Z-1-A (29 CFR 1910.1000) (1989)
Propane	REL	1,000 ppm	1,800 mg/m3	US. NIOSH: Pocket Guide to Chemical Hazards (2005)
	PEL	1,000 ppm	1,800 mg/m3	US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000) (02 2006)
	TWA	1,000 ppm	1,800 mg/m3	US. OSHA Table Z-1-A (29 CFR 1910.1000) (1989)
Sodium hydroxide (Na(OH))	Ceiling		2 mg/m3	US. ACGIH Threshold Limit Values (2008)
	Ceiling		2 mg/m3	US. OSHA Table Z-1-A (29 CFR 1910.1000) (1989)
	Ceil_Time		2 mg/m3	US. NIOSH: Pocket Guide to Chemical Hazards (2005)
	PEL		2 mg/m3	US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000) (02 2006)
Ammonium hydroxide ((NH4)(OH))	STEL	35 ppm		US. ACGIH Threshold Limit Values (2008)
	TWA	25 ppm		US. ACGIH Threshold Limit Values (2008)
	STEL	35 ppm	27 mg/m3	US. OSHA Table Z-1-A (29 CFR 1910.1000) (1989)
	STEL	35 ppm	27 mg/m3	US. NIOSH: Pocket Guide to Chemical Hazards (2005)
	REL	25 ppm	18 mg/m3	US. NIOSH: Pocket Guide to Chemical Hazards (2005)
	PEL	50 ppm	35 mg/m3	US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000) (02 2006)

Biological Limit Values

Chemical Identity	Exposure Limit Values	Source
Ethanol, 2-butoxy- (Butoxyacetic acid (BAA), with hydrolysis: Sampling time: End of shift.)	200 mg/g (Creatinine in urine)	ACGIH BEL (03 2013)

Appropriate Engineering Controls No data available.

Individual protection measures, such as personal protective equipment

General information: Provide easy access to water supply and eye wash facilities. Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level. If exposure limits have not been established, maintain airborne levels to an acceptable level.

Eye/face protection: Wear safety glasses with side shields (or goggles).

Skin Protection
Hand Protection: No data available.

Other: Wear suitable protective clothing. Wear chemical-resistant gloves, footwear, and protective clothing appropriate for the risk of exposure. Contact health and safety professional or manufacturer for specific information.

Respiratory Protection: In case of inadequate ventilation use suitable respirator. Seek advice from local supervisor.

Hygiene measures: Observe good industrial hygiene practices. Avoid contact with eyes. When using do not smoke. Wash contaminated clothing before reuse. Avoid contact with skin. Wash hands before breaks and immediately after handling the product.

9. Physical and chemical properties

Appearance

Physical state: liquid



Form:	Spray Aerosol
Color:	No data available.
Odor:	No data available.
Odor threshold:	No data available.
pH:	No data available.
Melting point/freezing point:	No data available.
Initial boiling point and boiling range:	No data available.
Flash Point:	-104.44 °C
Evaporation rate:	No data available.
Flammability (solid, gas):	No data available.
Upper/lower limit on flammability or explosive limits	
Flammability limit - upper (%):	No data available.
Flammability limit - lower (%):	No data available.
Explosive limit - upper (%):	No data available.
Explosive limit - lower (%):	No data available.
Vapor pressure:	No data available.
Vapor density:	No data available.
Density:	No data available.
Relative density:	No data available.
Solubility(ies)	
Solubility in water:	No data available.
Solubility (other):	No data available.
Partition coefficient (n-octanol/water):	No data available.
Auto-ignition temperature:	No data available.
Decomposition temperature:	No data available.
Viscosity:	No data available.

10. Stability and reactivity

Reactivity:	No data available.
Chemical Stability:	Material is stable under normal conditions.
Possibility of hazardous reactions:	No data available.
Conditions to avoid:	Avoid heat or contamination.
Incompatible Materials:	No data available.
Hazardous Decomposition Products:	No data available.

11. Toxicological information

Information on likely routes of exposure

Inhalation:	No data available.
Skin Contact:	No data available.
Eye contact:	No data available.



Ingestion: No data available.

Symptoms related to the physical, chemical and toxicological characteristics

Inhalation: No data available.

Skin Contact: No data available.

Eye contact: No data available.

Ingestion: No data available.

Information on toxicological effects

Acute toxicity (list all possible routes of exposure)

Oral

Product: ATEmix: 6,765.54 mg/kg

Dermal

Product: ATEmix: 2,579.34 mg/kg

Inhalation

Product: ATEmix: 90.91 mg/l
ATEmix : 22.73 mg/l

Repeated dose toxicity

Product: No data available.

Specified substance(s):

Ethanol, 2-butoxy-	NOAEL (Rabbit(Female, Male), Dermal, 90 d): > 150 mg/kg Dermal Experimental result, Key study NOAEL (Rat(Female), Oral, 90 d): < 82 mg/kg Oral Experimental result, Key study NOAEL (Rat(Female), Inhalation, 2 yr): < 31 ppm(m) Inhalation Experimental result, Key study
Butane	LOAEL (Rat(Female, Male), Inhalation, >= 28 d): 12,000 ppm(m) Inhalation Experimental result, Key study NOAEL (Rat(Female, Male), Inhalation, >= 28 d): 4,000 ppm(m) Inhalation Experimental result, Key study
Propane	NOAEL (Rat(Female, Male), Inhalation, >= 28 d): 4,000 ppm(m) Inhalation Experimental result, Key study LOAEL (Rat(Female, Male), Inhalation, >= 28 d): 12,000 ppm(m) Inhalation Experimental result, Key study

Skin Corrosion/Irritation

Product: No data available.

Specified substance(s):

Ethanol, 2-butoxy- in vivo (Rabbit): Irritating
Experimental result, Key study

Serious Eye Damage/Eye Irritation

Product: No data available.

Specified substance(s):

Ethanol, 2-butoxy-	Rabbit, 24 - 72 hrs: Irritating
Sodium hydroxide (Na(OH))	Corrosive Rabbit, 2 d: 10% Sodium Hydroxide- Category 1; 0.5% Sodium Hydroxide- Slightly irritating to eyes



Respiratory or Skin Sensitization

Product: No data available.

Specified substance(s):

Ethanol, 2-butoxy- Skin sensitization:, in vivo (Guinea pig): Non sensitising

Carcinogenicity

Product: No data available.

IARC Monographs on the Evaluation of Carcinogenic Risks to Humans:

No carcinogenic components identified

US. National Toxicology Program (NTP) Report on Carcinogens:

No carcinogenic components identified

US. OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050):

No carcinogenic components identified

Germ Cell Mutagenicity

In vitro

Product: No data available.

In vivo

Product: No data available.

Reproductive toxicity

Product: No data available.

Specific Target Organ Toxicity - Single Exposure

Product: No data available.

Specific Target Organ Toxicity - Repeated Exposure

Product: No data available.

Aspiration Hazard

Product: No data available.

Specified substance(s):

Oils, pine May be fatal if swallowed and enters airways.

Other effects: No data available.

12. Ecological information

Ecotoxicity:

Acute hazards to the aquatic environment:

Fish

Product: No data available.

Specified substance(s):

Ethanol, 2-butoxy- LC 50 (Oncorhynchus mykiss, 96 h): 1,474 mg/l Experimental result, Key study

Butane LC 50 (Various, 96 h): 147.54 mg/l QSAR QSAR, Key study

Propane LC 50 (Various, 96 h): 147.54 mg/l QSAR QSAR, Key study



Sodium hydroxide (Na(OH)) LC 50 (Western mosquitofish (*Gambusia affinis*), 96 h): 125 mg/l Mortality
LC 50 (*Gambusia affinis*, 96 h): < 180 mg/l Experimental result, Supporting study

Aquatic Invertebrates

Product: No data available.

Specified substance(s):

Ethanol, 2-butoxy- EC 50 (*Daphnia magna*, 48 h): 1,550 mg/l Experimental result, Key study

Butane LC 50 (*Daphnia* sp., 48 h): 69.43 mg/l QSAR QSAR, Key study

Oils, pine EC 50 (48 h): < 10 mg/l estimation

Sodium hydroxide (Na(OH)) EC 50 (Water flea (*Ceriodaphnia dubia*), 48 h): 34.59 - 47.13 mg/l Intoxication

Chronic hazards to the aquatic environment:

Fish

Product: No data available.

Specified substance(s):

Ethanol, 2-butoxy- NOAEL (*Danio rerio*): > 100 mg/l Experimental result, Key study

Aquatic Invertebrates

Product: No data available.

Specified substance(s):

Ethanol, 2-butoxy- EC 50 (*Daphnia magna*): 297 mg/l Experimental result, Key study

EC 10 (*Daphnia magna*): 134 mg/l Experimental result, Key study

Toxicity to Aquatic Plants

Product: No data available.

Persistence and Degradability

Biodegradation

Product: No data available.

Specified substance(s):

Ethanol, 2-butoxy- 90.4 % Detected in water. Experimental result, Key study

Butane 100 % (385.5 h) Detected in water. Experimental result, Key study

Propane 100 % (385.5 h) Detected in water. Experimental result, Key study
50 % (3.19 d) Detected in water. QSAR, Weight of Evidence study

Oils, pine Animal and vegetable fats and oils are biodegradable.

BOD/COD Ratio

Product: No data available.

Bioaccumulative potential

Bioconcentration Factor (BCF)

Product: No data available.

Partition Coefficient n-octanol / water (log Kow)



Product: No data available.

Mobility in soil: No data available.

Known or predicted distribution to environmental compartments

Ethanol, 2-butoxy-	No data available.
Butane	No data available.
Propane	No data available.
Oils, pine	No data available.
Sodium hydroxide (Na(OH))	No data available.

Other adverse effects: No data available.

13. Disposal considerations

Disposal instructions: Wash before disposal. Dispose to controlled facilities.

Contaminated Packaging: No data available.

14. Transport information

DOT

UN Number:	UN 1950
UN Proper Shipping Name:	Aerosols, flammable
Transport Hazard Class(es)	
Class:	2.1
Label(s):	–
Packing Group:	II
Marine Pollutant:	No
Environmental Hazards:	No
Marine Pollutant	No
Special precautions for user:	Not regulated.

IMDG

UN Number:	UN 1950
UN Proper Shipping Name:	Aerosols, flammable
Transport Hazard Class(es)	
Class:	2
Label(s):	–
EmS No.:	
Packing Group:	–
Environmental Hazards:	No
Marine Pollutant	No
Special precautions for user:	Not regulated.

IATA

UN Number:	UN 1950
Proper Shipping Name:	Aerosols, flammable
Transport Hazard Class(es):	
Class:	2.1
Label(s):	–
Packing Group:	–



Environmental Hazards: No
Marine Pollutant No

Special precautions for user: Not regulated.

15. Regulatory information

US Federal Regulations

Restrictions on use: Not known.

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)
US. OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)
None present or none present in regulated quantities.

CERCLA Hazardous Substance List (40 CFR 302.4):

<u>Chemical Identity</u>	<u>Reportable quantity</u>
Butane	lbs. 100
Propane	lbs. 100
Sodium hydroxide (Na(OH))	lbs. 1000
Ammonium hydroxide ((NH4)(OH))	lbs. 1000

Superfund Amendments and Reauthorization Act of 1986 (SARA)

Hazard categories

- Fire Hazard
- Immediate (Acute) Health Hazards
- Flammable aerosol
- Skin Corrosion/Irritation
- Serious Eye Damage/Eye Irritation

SARA 302 Extremely Hazardous Substance
None present or none present in regulated quantities.

SARA 304 Emergency Release Notification

<u>Chemical Identity</u>	<u>Reportable quantity</u>
Ethanol, 2-butoxy-	
Butane	lbs. 100
Propane	lbs. 100
Sodium hydroxide (Na(OH))	lbs. 1000
Ammonium hydroxide ((NH4)(OH))	lbs. 1000

SARA 311/312 Hazardous Chemical

<u>Chemical Identity</u>	<u>Threshold Planning Quantity</u>
Ethanol, 2-butoxy-	10000 lbs
Butane	10000 lbs
Propane	10000 lbs
Oils, pine	10000 lbs
Sodium hydroxide (Na(OH))	10000 lbs
Ammonium hydroxide ((NH4)(OH))	10000 lbs

SARA 313 (TRI Reporting)

<u>Chemical Identity</u>	<u>Reporting threshold for other users</u>	<u>Reporting threshold for manufacturing and processing</u>
Ethanol, 2-butoxy-	N230 lbs	N230 lbs.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130):

Clean Water Act Section 311 Hazardous Substances (40 CFR 117.3)

US State Regulations



US. California Proposition 65

No ingredient requiring a warning under CA Prop 65.

US. New Jersey Worker and Community Right-to-Know Act

Chemical Identity

Ethanol, 2-butoxy-
Butane
Propane

US. Massachusetts RTK - Substance List

Chemical Identity

Glycine, N,N-bis(carboxymethyl)-, sodium salt (1:3)

US. Pennsylvania RTK - Hazardous Substances

Chemical Identity

Ethanol, 2-butoxy-
Butane
Propane

US. Rhode Island RTK

No ingredient regulated by RI Right-to-Know Law present.

International regulations

Montreal protocol

Not applicable

Stockholm convention

Not applicable

Rotterdam convention

Not applicable

Kyoto protocol

Not applicable



Inventory Status:

EINECS, ELINCS or NLP:	Not in compliance with the inventory.
Japan (ENCS) List:	Not in compliance with the inventory.
Canada NDSL Inventory:	Not in compliance with the inventory.
Japan ISHL Listing:	Not in compliance with the inventory.
Japan Pharmacopoeia Listing:	Not in compliance with the inventory.
Mexico INSQ:	Not in compliance with the inventory.
Ontario Inventory:	Not in compliance with the inventory.
Taiwan Chemical Substance Inventory:	On or in compliance with the inventory
Australia AICS:	On or in compliance with the inventory
Canada DSL Inventory List:	On or in compliance with the inventory
China Inv. Existing Chemical Substances:	On or in compliance with the inventory
Korea Existing Chemicals Inv. (KECI):	On or in compliance with the inventory
Philippines PICCS:	On or in compliance with the inventory
US TSCA Inventory:	On or in compliance with the inventory
New Zealand Inventory of Chemicals:	On or in compliance with the inventory

16. Other information, including date of preparation or last revision

Issue Date:	11/11/2019
Revision Information:	No data available.
Version #:	1.0
Further Information:	No data available.
Disclaimer:	This information is provided without warranty. The information is believed to be correct. This information should be used to make an independent determination of the methods to safeguard workers and the environment.