



SAFETY DATA SHEET

1. Identification

Product identifier: Heat Stable Silicone Release Agent

Other means of identification

SDS number: RE1000007790

Recommended restrictions

Product use: Lubricant

Restrictions on use: Not known.

Manufacturer/Importer/Distributor Information

Manufacturer

Company Name: CLAIRES MANUFACTURING COMPANY
Address: 1000 Integram Dr
Pacific, MO 63069
Telephone: 1-630-543-7600
Fax:

Emergency telephone number: 1-866-836-8855

2. Hazard(s) identification

Hazard Classification

Physical Hazards

Flammable aerosol Category 1

Health Hazards

Aspiration Hazard Category 1

Label Elements

Hazard Symbol:



Signal Word: Danger

Hazard Statement: Extremely flammable aerosol.
May be fatal if swallowed and enters airways.

Precautionary Statements

Prevention: Keep away from heat, hot surfaces, sparks, open flames and other ignition



sources. No smoking. Do not spray on an open flame or other ignition source. Do not pierce or burn, even after use.

Response: IF SWALLOWED: Immediately call a POISON CENTER/doctor Do NOT induce vomiting.

Storage: Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F. Store locked up.

Disposal: Dispose of contents/container to an appropriate treatment and disposal facility in accordance with applicable laws and regulations, and product characteristics at time of disposal.

Hazard(s) not otherwise classified (HNOC): None.

3. Composition/information on ingredients

Mixtures

Chemical Identity	CAS number	Content in percent (%)*
Butane	106-97-8	50 - <100%
Propane	74-98-6	20 - <50%
Naphtha (petroleum), heavy alkylate	64741-65-7	10 - <20%
Siloxanes and Silicones, di-Me	63148-62-9	1 - <5%

* All concentrations are percent by weight unless ingredient is a gas. Gas concentrations are in percent by volume.

4. First-aid measures

Ingestion: Rinse mouth. Call a physician or poison control center immediately. Never give liquid to an unconscious person. If vomiting occurs, keep head low so that stomach content doesn't get into the lungs.

Inhalation: Move to fresh air.

Skin Contact: Wash skin thoroughly with soap and water. Get medical attention if symptoms occur.

Eye contact: Any material that contacts the eye should be washed out immediately with water. If easy to do, remove contact lenses. If eye irritation persists: Get medical advice/attention.

Most important symptoms/effects, acute and delayed

Symptoms: No data available.

Hazards: No data available.

Indication of immediate medical attention and special treatment needed

Treatment: No data available.

5. Fire-fighting measures



General Fire Hazards: Use water spray to keep fire-exposed containers cool. Fight fire from a protected location. Move containers from fire area if you can do so without risk.

Suitable (and unsuitable) extinguishing media

Suitable extinguishing media: Use fire-extinguishing media appropriate for surrounding materials.

Unsuitable extinguishing media: Do not use water jet as an extinguisher, as this will spread the fire.

Specific hazards arising from the chemical: Vapors may travel considerable distance to a source of ignition and flash back.

Special protective equipment and precautions for firefighters

Special fire fighting procedures: No data available.

Special protective equipment for fire-fighters: Firefighters must use standard protective equipment including flame retardant coat, helmet with face shield, gloves, rubber boots, and in enclosed spaces, SCBA.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures: Ventilate closed spaces before entering them. ELIMINATE all ignition sources (no smoking, flares, sparks or flames in immediate area). Keep upwind.

Methods and material for containment and cleaning up: Absorb spill with vermiculite or other inert material, then place in a container for chemical waste. Dike far ahead of larger spill for later recovery and disposal.

Notification Procedures: Dike for later disposal. Prevent entry into waterways, sewer, basements or confined areas. Stop the flow of material, if this is without risk. ELIMINATE all ignition sources (no smoking, flares, sparks or flames in immediate area). Stop leak if you can do so without risk.

Environmental Precautions: Do not contaminate water sources or sewer. Prevent further leakage or spillage if safe to do so.

7. Handling and storage

Precautions for safe handling: Wash hands thoroughly after handling. Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. Do not spray on an open flame or other ignition source. Do not pierce or burn, even after use.

Conditions for safe storage, including any incompatibilities: Store locked up. Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use. Aerosol Level 3

8. Exposure controls/personal protection

Control Parameters



Occupational Exposure Limits

Chemical Identity	Type	Exposure Limit Values	Source
Butane	REL	800 ppm 1,900 mg/m3	US. NIOSH: Pocket Guide to Chemical Hazards (2005)
	STEL	1,000 ppm	US. ACGIH Threshold Limit Values (03 2018)
	TWA	800 ppm 1,900 mg/m3	US. OSHA Table Z-1-A (29 CFR 1910.1000) (1989)
Propane	REL	1,000 ppm 1,800 mg/m3	US. NIOSH: Pocket Guide to Chemical Hazards (2005)
	PEL	1,000 ppm 1,800 mg/m3	US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000) (02 2006)
	TWA	1,000 ppm 1,800 mg/m3	US. OSHA Table Z-1-A (29 CFR 1910.1000) (1989)
Naphtha (petroleum), heavy alkylate	PEL	100 ppm 400 mg/m3	US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000) (02 2006)
	TWA	100 ppm 400 mg/m3	US. OSHA Table Z-1-A (29 CFR 1910.1000) (1989)
	REL	100 ppm 400 mg/m3	US. NIOSH: Pocket Guide to Chemical Hazards (2010)

Appropriate Engineering Controls No data available.

Individual protection measures, such as personal protective equipment

General information: Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. Supplementary local exhaust ventilation, closed systems, or respiratory and eye protection may be needed in special circumstances, such as poorly ventilated spaces, heating, evaporation of liquids from large surfaces, spraying of mists, mechanical generation of dusts, drying of solids, etc.

Eye/face protection: Wear safety glasses with side shields (or goggles).

Skin Protection
Hand Protection: No data available.

Other: Wear suitable protective clothing.

Respiratory Protection: In case of inadequate ventilation use suitable respirator. Seek advice from local supervisor.

Hygiene measures: Observe good industrial hygiene practices. When using do not smoke.

9. Physical and chemical properties

Appearance

Physical state: liquid
Form: Spray Aerosol
Color: No data available.
Odor: No data available.
Odor threshold: No data available.
pH: No data available.
Melting point/freezing point: No data available.
Initial boiling point and boiling range: No data available.
Flash Point: Estimated -104.4 °C
Evaporation rate: No data available.



Flammability (solid, gas):	No data available.
Upper/lower limit on flammability or explosive limits	
Flammability limit - upper (%):	Estimated 7 %(V)
Flammability limit - lower (%):	Estimated 1 %(V)
Explosive limit - upper (%):	No data available.
Explosive limit - lower (%):	No data available.
Vapor pressure:	No data available.
Vapor density:	No data available.
Density:	No data available.
Relative density:	No data available.
Solubility(ies)	
Solubility in water:	No data available.
Solubility (other):	No data available.
Partition coefficient (n-octanol/water):	No data available.
Auto-ignition temperature:	No data available.
Decomposition temperature:	No data available.
Viscosity:	No data available.

10. Stability and reactivity

Reactivity:	No data available.
Chemical Stability:	Material is stable under normal conditions.
Possibility of hazardous reactions:	No data available.
Conditions to avoid:	Avoid heat or contamination.
Incompatible Materials:	No data available.
Hazardous Decomposition Products:	No data available.

11. Toxicological information

Information on likely routes of exposure

Inhalation:	No data available.
Skin Contact:	No data available.
Eye contact:	No data available.
Ingestion:	No data available.

Symptoms related to the physical, chemical and toxicological characteristics

Inhalation:	No data available.
Skin Contact:	No data available.



Eye contact: No data available.

Ingestion: No data available.

Information on toxicological effects

Acute toxicity (list all possible routes of exposure)

Oral

Product: Not classified for acute toxicity based on available data.

Specified substance(s):
Naphtha (petroleum),
heavy alkylate LD 50: > 2,000 mg/kg

Dermal

Product: Not classified for acute toxicity based on available data.

Specified substance(s):
Naphtha (petroleum),
heavy alkylate LD 50: > 2,000 mg/kg

Inhalation

Product:

Specified substance(s):
Butane LC 50: > 100 mg/l
LC 50: > 100 mg/l

Propane LC 50: > 100 mg/l
LC 50: > 100 mg/l

Naphtha (petroleum),
heavy alkylate LD 50: > 5 mg/l

Repeated dose toxicity

Product: No data available.

Specified substance(s):
Butane LOAEL (Rat(Female, Male), Inhalation, >= 28 d): 12,000 ppm(m) Inhalation
Experimental result, Key study
NOAEL (Rat(Female, Male), Inhalation, >= 28 d): 4,000 ppm(m) Inhalation
Experimental result, Key study
Propane NOAEL (Rat(Female, Male), Inhalation, >= 28 d): 4,000 ppm(m) Inhalation
Experimental result, Key study
LOAEL (Rat(Female, Male), Inhalation, >= 28 d): 12,000 ppm(m) Inhalation
Experimental result, Key study

Skin Corrosion/Irritation

Product: No data available.

Serious Eye Damage/Eye Irritation

Product: No data available.



Respiratory or Skin Sensitization

Product: No data available.

Carcinogenicity

Product: No data available.

IARC Monographs on the Evaluation of Carcinogenic Risks to Humans:

No carcinogenic components identified

US. National Toxicology Program (NTP) Report on Carcinogens:

No carcinogenic components identified

US. OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050):

No carcinogenic components identified

Germ Cell Mutagenicity

In vitro

Product: No data available.

In vivo

Product: No data available.

Reproductive toxicity

Product: No data available.

Specific Target Organ Toxicity - Single Exposure

Product: No data available.

Specific Target Organ Toxicity - Repeated Exposure

Product: No data available.

Aspiration Hazard

Product: No data available.

Specified substance(s):

Naphtha (petroleum),
heavy alkylate

May be fatal if swallowed and enters airways.

Other effects: No data available.

12. Ecological information

Ecotoxicity:

Acute hazards to the aquatic environment:

Fish



Product:	No data available.
Specified substance(s):	
Butane	LC 50 (Various, 96 h): 147.54 mg/l QSAR QSAR, Key study
Propane	LC 50 (Various, 96 h): 147.54 mg/l QSAR QSAR, Key study
Siloxanes and Silicones, di-Me	LC 50 (Redear sunfish (Lepomis microlophus), 96 h): 26.27 - 56.73 mg/l Mortality

Aquatic Invertebrates

Product:	No data available.
Specified substance(s):	
Butane	LC 50 (Daphnia sp., 48 h): 69.43 mg/l QSAR QSAR, Key study
Siloxanes and Silicones, di-Me	LC 50 (Water flea (Daphnia magna), 48 h): 44.5 mg/l Mortality

Chronic hazards to the aquatic environment:

Fish

Product: No data available.

Aquatic Invertebrates

Product: No data available.

Toxicity to Aquatic Plants

Product: No data available.

Persistence and Degradability

Biodegradation

Product: No data available.

Specified substance(s):

Butane	100 % (385.5 h) Detected in water. Experimental result, Key study
Propane	100 % (385.5 h) Detected in water. Experimental result, Key study 50 % (3.19 d) Detected in water. QSAR, Weight of Evidence study

BOD/COD Ratio

Product: No data available.

Bioaccumulative potential

Bioconcentration Factor (BCF)

Product: No data available.

Partition Coefficient n-octanol / water (log Kow)

Product: No data available.

Mobility in soil: No data available.

Known or predicted distribution to environmental compartments

Butane	No data available.
Propane	No data available.



Naphtha (petroleum), heavy alkylate No data available.
Siloxanes and Silicones, di-Me No data available.

Other adverse effects: No data available.

13. Disposal considerations

Disposal instructions: Discharge, treatment, or disposal may be subject to national, state, or local laws.

Contaminated Packaging: No data available.

14. Transport information

DOT

UN Number: UN 1950
UN Proper Shipping Name: Aerosols, flammable
Transport Hazard Class(es)
Class: 2.1
Label(s): –
Packing Group: II
Marine Pollutant: No

Environmental Hazards: No
Marine Pollutant: No

Special precautions for user: Not regulated.

IMDG

UN Number: UN 1950
UN Proper Shipping Name: Aerosols, flammable
Transport Hazard Class(es)
Class: 2
Label(s): –
EmS No.: –
Packing Group: –

Environmental Hazards: No
Marine Pollutant: No

Special precautions for user: Not regulated.

IATA

UN Number: UN 1950
Proper Shipping Name: Aerosols, flammable
Transport Hazard Class(es):
Class: 2.1
Label(s): –
Packing Group: –

Environmental Hazards: No
Marine Pollutant: No

Special precautions for user: Not regulated.



15. Regulatory information

US Federal Regulations

Restrictions on use: Not known.

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)
US. OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)
None present or none present in regulated quantities.

CERCLA Hazardous Substance List (40 CFR 302.4):

<u>Chemical Identity</u>	<u>Reportable quantity</u>
Butane	lbs. 100
Propane	lbs. 100

Superfund Amendments and Reauthorization Act of 1986 (SARA)

Hazard categories

Fire Hazard
Immediate (Acute) Health Hazards
Flammable aerosol
Aspiration Hazard

SARA 302 Extremely Hazardous Substance

None present or none present in regulated quantities.

SARA 304 Emergency Release Notification

<u>Chemical Identity</u>	<u>Reportable quantity</u>
Butane	lbs. 100
Propane	lbs. 100

SARA 311/312 Hazardous Chemical

<u>Chemical Identity</u>	<u>Threshold Planning Quantity</u>
Butane	10000 lbs
Propane	10000 lbs
Naphtha (petroleum), heavy alkylate	10000 lbs
Siloxanes and Silicones, di-Me	10000 lbs

SARA 313 (TRI Reporting)

None present or none present in regulated quantities.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130):

Clean Water Act Section 311 Hazardous Substances (40 CFR 117.3)

US State Regulations

US. California Proposition 65

No ingredient requiring a warning under CA Prop 65.

US. New Jersey Worker and Community Right-to-Know Act

Chemical Identity
Butane
Propane
Naphtha (petroleum), heavy alkylate

US. Massachusetts RTK - Substance List

No ingredient regulated by MA Right-to-Know Law present.



US. Pennsylvania RTK - Hazardous Substances

Chemical Identity

Butane
Propane
Naphtha (petroleum), heavy alkylate

US. Rhode Island RTK

No ingredient regulated by RI Right-to-Know Law present.

International regulations

Montreal protocol

Not applicable

Stockholm convention

Not applicable

Rotterdam convention

Not applicable

Kyoto protocol

Not applicable



Inventory Status:

Australia AICS:	On or in compliance with the inventory
Canada DSL Inventory List:	On or in compliance with the inventory
EINECS, ELINCS or NLP:	Not in compliance with the inventory.
Japan (ENCS) List:	Not in compliance with the inventory.
China Inv. Existing Chemical Substances:	On or in compliance with the inventory
Korea Existing Chemicals Inv. (KECI):	On or in compliance with the inventory
Canada NDSL Inventory:	Not in compliance with the inventory.
Philippines PICCS:	On or in compliance with the inventory
US TSCA Inventory:	On or in compliance with the inventory
New Zealand Inventory of Chemicals:	On or in compliance with the inventory
Japan ISHL Listing:	Not in compliance with the inventory.
Japan Pharmacopoeia Listing:	Not in compliance with the inventory.
Mexico INSQ:	On or in compliance with the inventory
Ontario Inventory:	On or in compliance with the inventory
Taiwan Chemical Substance Inventory:	On or in compliance with the inventory

16. Other information, including date of preparation or last revision

Issue Date:	12/18/2019
Revision Information:	No data available.
Version #:	1.0
Further Information:	No data available.
Disclaimer:	This information is provided without warranty. The information is believed to be correct. This information should be used to make an independent determination of the methods to safeguard workers and the environment.