

Product Description

D-A AutoTrans[™] Super LV is a low viscosity, fully synthetic, automatic transmission fluid that supports performance requirements of today's newer automatic transmissions, including General Motors, Honda, Hyundai, Ford, Kia, Mitsubishi, Nissan, Saab, Toyota, Volkswagen and others. D-A AutoTrans Super LV is suitable for severe service applications (up to 50,000 miles) and for extended drain intervals in normal service applications (up to 100,000 miles). It offers excellent corrosion resistance to all types of metals used in transmissions, plus provides superior friction retention and thermal and oxidation stability. D-A AutoTrans Super LV can be used in a broad variety of multi-vehicle applications found in on- and off-highway service as well as marine and industrial applications.

Product Features and Benefits

Friction modifiers control lock-up rates of clutch packs for proper transmission shifting characteristics and efficient power transfer.

Controls seal deterioration to limit fluid leakage.

Specially formulated for extra wear control and rust protection for longer equipment life.

Special detergent/dispersant additives limit formation of sludge and varnish deposits which interfere with proper transmission operation.

Multigrade for optimum performance during cold starts and high temperature operations, including start/stop severe service.

Formulated to be compatible with metallurgy used in most modern transmissions.

Provides efficient heat removal from clutch surfaces to extend clutch life and reduce clutch shudder in modulated torque converters.

Full synthetic for longer fluid life and faster oil flow in low temperature operation.



PRODUCT AT A GLANCE

- Low Viscosity
- Automatic Transmission Fluid
- Full Synthetic
- Multi-Vehicle Use



D-A Lubricant Company, Inc.

801 Edwards Drive, Lebanon, IN 46052 • TEL: 317.923.5321 • FAX: 765.482.3065 • EMAIL: dalube@dalube.com
www.dalube.com

Supports the Performance Requirements of:

Aisin Warner AW-1	JASO 1-A-LV	VW G-055-540
Dexron VI	JWS 3324	
Ford Mercon LV	Kia NWS-9638	
Ford Mercon SP	Mitsubishi ATF J-2	
GM	Mitsubishi SP-IV	
Honda DW-1	Nissan Matic-S	
Hyundai/Kia NWS-9638	Saab 93 165 147	
Hyundai/Kia SP-IV	Toyota WS (JWS 3324)	
Hyundai/Kia SPH-IV	Volvo AT102 (P/N 97342)	
Hyundai/Kia SP-IVRR	Volvo 97342	

NOTE: ATF recommendations may vary between models from a manufacturer.
Please consult the owners manual for the correct fluid recommendations.

Dexron is a trademark of General Motors Inc.
Mercon is a trademark of the Ford Motor Company.

Typical Properties

Viscosity		
@ 100°C, cSt	ASTM D445	5.80
@ 40°C, cSt	ASTM D445	28.4
Viscosity Index	ASTM D2270	155
Brookfield Viscosity, cPs		
@ -40°C	ASTM D2983	9,900
Flash Point,		
°F (°C)	ASTM D92	380 (193)
Pour Point,		
°F (°C)	ASTM D97	-52 (-46)
API Gravity @ 60°F	ASTM D287	33.9
Order D-A Part #	Drum, 55 Gal	54582
	Pail, 5 Gal	54588
	12-1 Qt Case, net 3 Gal	54586

To Order D-A Products, Call 1-800-OIL-LUBE (1-800-645-5823) or Fax orders to 765-482-3065

D-A Lubricant Company, Inc.

801 Edwards Drive, Lebanon, IN 46052 • TEL: 317.923.5321 • FAX: 765.482.3065

Email: dalube@dalube.com • www.dalube.com

