

HydraTrans[™] \100

Product Description

D-A HydraTrans™ 100 is a transmission and hydraulic fluid providing excellent performance for severe service agricultural equipment applications. It is formulated from high-quality base stocks fortified with a high-performance additive system to extend component life and improve performance characteristics. D-A HydraTrans 100 supports the performance requirements of most major agricultural equipment manufacturers, allowing users to stock one fluid to meet transmission, hydraulic and wet-brake system needs.

Product Features and Benefits

Improves hydraulic pump and gear train life to help reduce maintenance costs.

Improved oxidation stability extends oil life.

Improved frictional properties prevent grabbing or chattering of wet brakes and PTO clutches.

Excellent water tolerance and low temperature fluidity provides protection in all working environments.

Provides rust and corrosion protection for all types of metal surfaces, increasing component life.

Supports the performance requirements of both hydraulic and transmission field service of major agricultural equipment manufacturers reducing the need to inventory separate lubricants.

PRODUCT AT A GLANCE

- Premium Grade Tractor Fluid
- Transmission and Hydraulic Fluid
- Designed for use in Severe Service
- Supports the performance requirements of major agricultural manufacturers
- Prevents grabbing or chattering of wet brakes and PTO clutches











HydraTrans[™] \100

Others

API GL-4

Allison C-3, C-4

Sauer Danfoss (Sundstrand)

M-2950-S

Sperry-Vickers, I-286-S

Typical Applications - Supports the Performance Requirements of:

ACGO

ACGO Power Fluid 821XL Allis Power Fluid 821 Deutz-Allis 272843, 25741, 246634 Massey Ferguson M1135, M1141, M1143, M1145 Massey Ferguson M1110, 1127A/B, M1129A

CNH

ESN-M2C134-A, B, C ESN-M2C86B, C ESN-M2C43 ESN-M2C41-B JIC 145, 143/144 MAT 3505/MS 1209 (Ultra) MAT 3525/FNHA-2-C-201/Ford ESN M2C134-A/B/C/D MAT 3526/FNHA-2-C-200A MS-1206, 1207, 1209, 1210, 1204 John Deere

J14B, J14C JDM J20A JDM J21A JDM J20C JDT 303

<u>Kubota</u>

Kubota UDT

White Farm/MM/Oliver

Q1826, Q1766, Q1722, Q1766B Q1705, Q1802 Type 55

Typical Properties

isco	

@ 100°C, cSt	ASTM D445	9.6
@ 40°C, cSt	ASTM D445	56.2
@ -20°C, cP	ASTM D5293	3,400
@ -35°C, cP	ASTM D2983	40,000
Viscosity Index	ASTM D2270	145
Flash Point,		
°F	ASTM D92	425
°C	ASTM D92	218
Pour Point, °C	ASTM D6749	-39
APIGravity	ASTM D287	28.2
D-A Part Numbers:	Bulk	57511
	Drum, 55 Gal	57512
	4-1 Gal Case, net 4 Gal	57514
	Plastic Pail, 5 Gal	57518
	Metal Pail	57519

A CTA A D 4 4 F

To Order D-A Products, Call 1-800-OIL-LUBE (1-800-645-5823) or Fax orders to 765-482-3065

D-A Lubricant Company, Inc.

801 Edwards Drive, Lebanon, IN 46052 • TEL: 317.923.5321 • FAX: 765.482.3065

Email: dalube@dalube.com • www.dalube.com

© 2016. D-A Lubricant Company. Inc.