

Taper Shank Drills, Shanks Larger

HIGH SPEED STEEL
Fractional / Black Oxide



PACKAGING:
All sizes are individually packaged.

Series 1475

118° POINT / TAPER SHANK

For general purpose use in a wide range of materials.

1400 – American Standard Taper Shanks

1450 – Smaller than normal Taper Shanks

1475 – Larger than normal Taper Shanks



1475

Size	Morse Taper	Flute Length	Overall Length	1475 EDP No.
3/8"	2	3-1/2"	7-3/8"	1475A124
25/64"	2	3-5/8"	7-1/2"	1475A125
13/32"	2	3-5/8"	7-1/2"	1475A126
27/64"	2	3-7/8"	7-3/4"	1475A127
7/16"	2	3-7/8"	7-3/4"	1475A128
29/64"	2	4-1/8"	8"	1475A129
15/32"	2	4-1/8"	8"	1475A130
41/64"	3	5-1/8"	9-3/4"	1475A141
21/32"	3	5-1/8"	9-3/4"	1475A142
43/64"	3	5-3/8"	10"	1475A143

Size	Morse Taper	Flute Length	Overall Length	1475 EDP No.
11/16"	3	5-3/8"	10"	1475A144
45/64"	3	5-3/8"	10-1/4"	1475A145
23/32"	3	5-7/8"	10-1/4"	1475A146
47/64"	3	5-7/8"	10-1/2"	1475A147
3/4"	3	6"	10-1/2"	1475A148
49/64"	3	6"	10-5/8"	1475A149
25/32"	3	6-3/8"	10-5/8"	1475A150
1"	4	6-3/8"	12"	1475A164
1-1/32"	4	6-1/2"	12-1/8"	1475A202
1-1/16"	4	6-5/8"	12-1/4"	1475A204

