

Construction Reamers

HIGH SPEED STEEL
Fractional / Black Oxide

PACKAGING:
All sizes are individually packaged.

4275  **/4275E Construction Reamers**

SPIRAL FLUTE / 3-FLATS REDUCED SHANK

Construction or Car Reamers are especially adapted for heavy duty reaming as encountered in the fabrication of structural steel assemblies. They are tapered at the point to facilitate entering of holes which are out of alignment. Available in Spiral Flute and High Spiral Flute designs with 3-Flat Straight Shanks, or with Hex Nut Shanks.



4275

Size	Shank Dia.	Flute Length	Overall Length	4275 EDP No.	4275E EDP No.
1/4"	1/4"	2-1/2"	4-3/8"	427A116	-
5/16"	5/16"	2-3/4"	4-5/8"	427A120	427E120
3/8"	3/8"	2-3/4"	4-5/8"	427A124	427E124
13/32"	13/32"	3-1/2"	5-3/8"	427A126	-
7/16"	7/16"	3-1/2"	5-3/8"	427A128	427E128
1/2"	1/2"	4"	5-7/8"	427A132	427E132
17/32"	1/2"	3-3/4"	5-7/8"	427A134	-
9/16"	1/2"	4"	5-7/8"	427A136	427E136
19/32"	1/2"	4-1/4"	6-3/8"	427A138	-
39/64"	1/2"	4-1/4"	6-3/8"	427A139	-
5/8"	1/2"	4-1/2"	6-3/8"	427A140	427E140
.652	1/2"	4-1/2"	6-3/8"	427A141	-
21/32"	1/2"	4-1/2"	6-3/8"	427A142	-
11/16"	1/2"	4-1/2"	6-3/8"	427A144	427E144
23/32"	1/2"	4-1/2"	6-3/8"	427A146	-
3/4"	1/2"	5"	6-7/8"	427A148	427E148

Size	Shank Dia.	Flute Length	Overall Length	4275 EDP No.	4275E EDP No.
.776"	1/2"	5"	6-7/8"	427A149	-
25/32"	1/2"	5"	6-7/8"	427A150	-
13/16"	1/2"	5"	6-7/8"	427A152	427E152
7/8"	1/2"	5"	6-7/8"	427A156	427E156
15/16"	1/2"	5"	6-7/8"	427A160	427E160
1"	1/2"	5"	6-7/8"	427A164	427E164
1-027	1/2"	5"	6-7/8"	427A201	-
1-1/16"	1/2"	5"	6-7/8"	427A204	427E204
1-3/32"	1/2"	5"	6-7/8"	427A206	-
1-1/8"	3/4"	5"	6-7/8"	427A208	-
1-3/16"	3/4"	5"	6-7/8"	427A212	-
1-1/4"	3/4"	5"	6-7/8"	427A216	-
1-5/16"	3/4"	5"	6-7/8"	427A220	-
1-3/8"	3/4"	5"	6-7/8"	427A224	-
1-7/16"	3/4"	5"	6-7/8"	427A228	-
1-1/2"	3/4"	5"	6-7/8"	427A232	-

Sizes 1-1/8" and above also available with 1/2" shank. Please call for price and availability.