



SAFETY DATA SHEET

1. Identification

Product number 1000009286
Product identifier **SW508 FABRIC CLEANR PLUS LB 12PK**
Company information Sprayway, Inc.
1000 INTEGRAM DR
Pacific, MO 63069 United States
Company phone 1-630-628-3000
Emergency telephone US 1-866-836-8855
Emergency telephone outside US 1-952-852-4646
Version # 01
Recommended use Cleaner
Recommended restrictions None known.

2. Hazard(s) identification

Physical hazards Flammable aerosols Category 1
Health hazards Serious eye damage/eye irritation Category 2
OSHA defined hazards Not classified.

Label elements



Signal word Danger
Hazard statement Extremely flammable aerosol. Causes serious eye irritation.
Precautionary statement
Prevention Keep away from heat/sparks/open flames/hot surfaces. - No smoking. Do not spray on an open flame or other ignition source. Pressurized container: Do not pierce or burn, even after use. Wash thoroughly after handling. Wear eye protection/face protection.
Response If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.
Storage Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F.
Disposal Dispose of contents/container in accordance with local/regional/national/international regulations.
Environmental hazards Hazardous to the aquatic environment, acute Category 3 hazard
Hazard(s) not otherwise classified (HNOC) None known.
Supplemental information None.

3. Composition/information on ingredients

Mixtures

Chemical name	Common name and synonyms	CAS number	%
Butane		106-97-8	2.5 - 10
Diethylene Glycol Monobutyl Ether		112-34-5	2.5 - 10
Alcohols C9-11 Ethoxylated		68439-46-3	1 - 2.5
Propane		74-98-6	1 - 2.5
EDTA Tetrasodium Salt		64-02-8	0.1 - 1
Other components below reportable levels			80 - 90

*Designates that a specific chemical identity and/or percentage of composition has been withheld as a trade secret.

4. First-aid measures

Inhalation	Move to fresh air. Call a physician if symptoms develop or persist.
Skin contact	Wash off with soap and water. Get medical attention if irritation develops and persists.
Eye contact	Immediately flush eyes with plenty of water for at least 15 minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.
Ingestion	In the unlikely event of swallowing contact a physician or poison control center. Rinse mouth.
Most important symptoms/effects, acute and delayed	Severe eye irritation. Symptoms may include stinging, tearing, redness, swelling, and blurred vision.
Indication of immediate medical attention and special treatment needed	Provide general supportive measures and treat symptomatically. Keep victim under observation. Symptoms may be delayed.
General information	Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves.

5. Fire-fighting measures

Suitable extinguishing media	Not available.
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.
Specific hazards arising from the chemical	Contents under pressure. Pressurized container may explode when exposed to heat or flame. During fire, gases hazardous to health may be formed.
Special protective equipment and precautions for firefighters	Firefighters must use standard protective equipment including flame retardant coat, helmet with face shield, gloves, rubber boots, and in enclosed spaces, SCBA.
Fire fighting equipment/instructions	Move containers from fire area if you can do so without risk. Containers should be cooled with water to prevent vapor pressure build up. For massive fire in cargo area, use unmanned hose holder or monitor nozzles, if possible. If not, withdraw and let fire burn out.
Specific methods	Use standard firefighting procedures and consider the hazards of other involved materials. Move containers from fire area if you can do so without risk. In the event of fire and/or explosion do not breathe fumes.
General fire hazards	Extremely flammable aerosol.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures	Keep unnecessary personnel away. Keep people away from and upwind of spill/leak. Wear appropriate protective equipment and clothing during clean-up. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Ventilate closed spaces before entering them. Local authorities should be advised if significant spillages cannot be contained. For personal protection, see section 8 of the SDS.
Methods and materials for containment and cleaning up	Refer to attached safety data sheets and/or instructions for use. Stop leak if you can do so without risk. Move the cylinder to a safe and open area if the leak is irreparable. Isolate area until gas has dispersed. Eliminate all ignition sources (no smoking, flares, sparks, or flames in immediate area). Keep combustibles (wood, paper, oil, etc.) away from spilled material. Prevent product from entering drains. Cover with plastic sheet to prevent spreading. Absorb in vermiculite, dry sand or earth and place into containers. Following product recovery, flush area with water. Small Spills: Wipe up with absorbent material (e.g. cloth, fleece). Clean surface thoroughly to remove residual contamination. For waste disposal, see section 13 of the SDS.
Environmental precautions	Avoid release to the environment. Inform appropriate managerial or supervisory personnel of all environmental releases. Prevent further leakage or spillage if safe to do so. Avoid discharge into drains, water courses or onto the ground.

7. Handling and storage

Precautions for safe handling	Pressurized container: Do not pierce or burn, even after use. Do not use if spray button is missing or defective. Do not spray on a naked flame or any other incandescent material. Do not smoke while using or until sprayed surface is thoroughly dry. Do not cut, weld, solder, drill, grind, or expose containers to heat, flame, sparks, or other sources of ignition. All equipment used when handling the product must be grounded. Do not re-use empty containers. Avoid contact with eyes. Use only in well-ventilated areas. Wear appropriate personal protective equipment. Avoid release to the environment. Observe good industrial hygiene practices.
--------------------------------------	---

Conditions for safe storage, including any incompatibilities

Level 1 Aerosol.

Pressurized container. Protect from sunlight and do not expose to temperatures exceeding 50°C/122 °F. Do not puncture, incinerate or crush. Do not handle or store near an open flame, heat or other sources of ignition. This material can accumulate static charge which may cause spark and become an ignition source. Store away from incompatible materials (see Section 10 of the SDS).

8. Exposure controls/personal protection**Occupational exposure limits****US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)**

Components	Type	Value
Propane (CAS 74-98-6)	PEL	1800 mg/m3 1000 ppm

US. ACGIH Threshold Limit Values

Components	Type	Value	Form
Butane (CAS 106-97-8)	STEL	1000 ppm	Inhalable fraction and vapor.
Diethylene Glycol	TWA	10 ppm	
Monobutyl Ether (CAS 112-34-5)			

US. NIOSH: Pocket Guide to Chemical Hazards

Components	Type	Value
Butane (CAS 106-97-8)	TWA	1900 mg/m3 800 ppm
Propane (CAS 74-98-6)	TWA	1800 mg/m3 1000 ppm

Biological limit values

No biological exposure limits noted for the ingredient(s).

Appropriate engineering controls

Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level. Provide eyewash station.

Individual protection measures, such as personal protective equipment

Eye/face protection Wear safety glasses with side shields (or goggles).

Skin protection

Hand protection Wear appropriate chemical resistant gloves. Suitable gloves can be recommended by the glove supplier.

Other Wear suitable protective clothing.

Respiratory protection If permissible levels are exceeded use NIOSH mechanical filter / organic vapor cartridge or an air-supplied respirator.

Thermal hazards Wear appropriate thermal protective clothing, when necessary.

General hygiene considerations

When using do not smoke. Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants.

9. Physical and chemical properties**Appearance**

Physical state Gas.

Form Aerosol.

Color Not available.

Odor Not available.

Odor threshold Not available.

pH Not available.

Melting point/freezing point Not available.

Initial boiling point and boiling range 212 °F (100 °C) estimated

Flash point	-154.0 °F (-103.3 °C) Propellant estimated
Evaporation rate	Not available.
Flammability (solid, gas)	Not available.
Upper/lower flammability or explosive limits	
Flammability limit - lower (%)	0.9 % estimated
Flammability limit - upper (%)	24.6 % estimated
Explosive limit - lower (%)	Not available.
Explosive limit - upper (%)	Not available.
Vapor pressure	21.81 psig @70F estimated
Vapor density	Not available.
Relative density	Not available.
Solubility(ies)	
Solubility (water)	Not available.
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	442.4 °F (228 °C) estimated
Decomposition temperature	Not available.
Viscosity	Not available.
Other information	
Explosive properties	Not explosive.
Heat of combustion (NFPA 30B)	3.78 kJ/g estimated
Oxidizing properties	Not oxidizing.
Percent volatile	95.85 % estimated
Specific gravity	0.966 estimated

10. Stability and reactivity

Reactivity	The product is stable and non-reactive under normal conditions of use, storage and transport.
Chemical stability	Material is stable under normal conditions.
Possibility of hazardous reactions	Hazardous polymerization does not occur.
Conditions to avoid	Avoid temperatures exceeding the flash point. Contact with incompatible materials.
Incompatible materials	Strong oxidizing agents.
Hazardous decomposition products	No hazardous decomposition products are known.

11. Toxicological information

Information on likely routes of exposure

Inhalation	No adverse effects due to inhalation are expected.
Skin contact	No adverse effects due to skin contact are expected.
Eye contact	Causes serious eye irritation.
Ingestion	Expected to be a low ingestion hazard.

Symptoms related to the physical, chemical and toxicological characteristics Severe eye irritation. Symptoms may include stinging, tearing, redness, swelling, and blurred vision.

Information on toxicological effects

Acute toxicity

Components	Species	Test Results
Alcohols C9-11 Ethoxylated (CAS 68439-46-3)		
<u>Acute</u>		
Dermal		
LD50	Rabbit	2000 mg/kg, 24 Hours
	Rat	> 2000 mg/kg, 24 Hours
Inhalation		
<i>Aerosol</i>		
LC50	Rat	> 1600 mg/m3, 4 Hours
<i>Vapor</i>		
LC50	Rat	> 100 mg/m3, 6 Hours
<i>Aerosol</i>		
LC50	Rat	> 1.6 mg/l, 4 Hours
Oral		
LD50	Rat	3488 mg/kg
Butane (CAS 106-97-8)		
<u>Acute</u>		
Inhalation		
LC50	Mouse	1237 mg/l, 120 Minutes 52 %, 120 Minutes
	Rat	1355 mg/l
Diethylene Glycol Monobutyl Ether (CAS 112-34-5)		
<u>Acute</u>		
Dermal		
LD50	Rabbit	2764 mg/kg, 24 Hours
	Rat	2021 mg/kg
Inhalation		
LC50	Rat	74 mg/l/4h
Oral		
LD100	Rabbit	4000 mg/kg
LD50	Guinea pig	2000 mg/kg
	Mouse	2410 mg/kg
	Rabbit	2500 - 3000 mg/kg
	Rat	7291 mg/kg
EDTA Tetrasodium Salt (CAS 64-02-8)		
<u>Acute</u>		
Oral		
LD50	Rat	1658 mg/kg
Propane (CAS 74-98-6)		
<u>Acute</u>		
Inhalation		
LC50	Mouse	1237 mg/l, 120 Minutes 52 %, 120 Minutes
	Rat	1355 mg/l 658 mg/l/4h

* Estimates for product may be based on additional component data not shown.

Skin corrosion/irritation Prolonged skin contact may cause temporary irritation.
Serious eye damage/eye irritation Causes serious eye irritation.

Respiratory or skin sensitization

Respiratory sensitization Not a respiratory sensitizer.

Skin sensitization This product is not expected to cause skin sensitization.

Germ cell mutagenicity No data available to indicate product or any components present at greater than 0.1% are mutagenic or genotoxic.

Carcinogenicity This product is not considered to be a carcinogen by IARC, ACGIH, NTP, or OSHA.

IARC Monographs. Overall Evaluation of Carcinogenicity

Not listed.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)

Not regulated.

US. National Toxicology Program (NTP) Report on Carcinogens

Not listed.

Reproductive toxicity This product is not expected to cause reproductive or developmental effects.

Specific target organ toxicity - single exposure Not classified.

Specific target organ toxicity - repeated exposure Not classified.

Aspiration hazard Not an aspiration hazard.

12. Ecological information

Ecotoxicity Harmful to aquatic life.

Components		Species	Test Results
Alcohols C9-11 Ethoxylated (CAS 68439-46-3)			
Aquatic			
Crustacea	EC50	Water flea (Daphnia magna)	2.9 - 8.5 mg/l, 48 hours
Fish	LC50	Fathead minnow (Pimephales promelas)	6 - 12 mg/l, 96 hours
Diethylene Glycol Monobutyl Ether (CAS 112-34-5)			
Aquatic			
Crustacea	EC50	Daphnia	2803 mg/L, 48 Hours
Fish	LC50	Bluegill (Lepomis macrochirus)	1300 mg/l, 96 hours
		Fish	1304 mg/L, 96 Hours
EDTA Tetrasodium Salt (CAS 64-02-8)			
Aquatic			
Algae	IC50	Algae	1.01 mg/L, 72 Hours
Fish	LC50	Bluegill (Lepomis macrochirus)	472 - 500 mg/l, 96 hours

* Estimates for product may be based on additional component data not shown.

Persistence and degradability No data is available on the degradability of this product.

Bioaccumulative potential

Partition coefficient n-octanol / water (log Kow)

Butane	2.89
Diethylene Glycol Monobutyl Ether	0.56
Propane	2.36

Mobility in soil No data available.

Other adverse effects No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.

13. Disposal considerations

Disposal instructions Collect and reclaim or dispose in sealed containers at licensed waste disposal site. Contents under pressure. Do not puncture, incinerate or crush. Do not allow this material to drain into sewers/water supplies. Do not contaminate ponds, waterways or ditches with chemical or used container. Dispose of contents/container in accordance with local/regional/national/international regulations.

Local disposal regulations Dispose in accordance with all applicable regulations.

Hazardous waste code	The waste code should be assigned in discussion between the user, the producer and the waste disposal company.
Waste from residues / unused products	Dispose of in accordance with local regulations. Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe manner (see: Disposal instructions).
Contaminated packaging	Since emptied containers may retain product residue, follow label warnings even after container is emptied. Empty containers should be taken to an approved waste handling site for recycling or disposal. Do not re-use empty containers.

14. Transport information

DOT

UN number	UN1950
UN proper shipping name	Aerosols, flammable, (each not exceeding 1 L capacity)
Transport hazard class(es)	
Class	2.1
Subsidiary risk	-
Label(s)	2.1
Packing group	Not applicable.
Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.
Special provisions	N82
Packaging exceptions	306
Packaging non bulk	None
Packaging bulk	None

This product meets the exception requirements of section 173.306 as a limited quantity and may be shipped as a limited quantity. Until 12/31/2020, the "Consumer Commodity - ORM-D" marking may still be used in place of the new limited quantity diamond mark for packages of UN 1950 Aerosols. Limited quantities require the limited quantity diamond mark on cartons after 12/31/20 and may be used now in place of the "Consumer Commodity ORM-D" marking.

IATA

UN number	UN1950
UN proper shipping name	Aerosols, flammable
Transport hazard class(es)	
Class	2.1
Subsidiary risk	-
Label(s)	2.1
Packing group	Not applicable.
Environmental hazards	No.
ERG Code	10L
Special precautions for user	Read safety instructions, SDS and emergency procedures before handling. Read safety instructions, SDS and emergency procedures before handling.
Other information	
Passenger and cargo aircraft	Allowed with restrictions.
Cargo aircraft only	Allowed with restrictions.
Packaging Exceptions	LTD QTY

IMDG

UN number	UN1950
UN proper shipping name	AEROSOLS
Transport hazard class(es)	
Class	2.1
Subsidiary risk	-
Label(s)	2.1
Packing group	Not applicable.
Environmental hazards	
Marine pollutant	No.
EmS	F-D, S-U
Special precautions for user	Read safety instructions, SDS and emergency procedures before handling. Read safety instructions, SDS and emergency procedures before handling.
Packaging Exceptions	LTD QTY
Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code	Not applicable.

DOT



IATA; IMDG



15. Regulatory information

US federal regulations This product is a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200.

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

CERCLA Hazardous Substance List (40 CFR 302.4)

Not listed.

SARA 304 Emergency release notification

Not regulated.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)

Not regulated.

Superfund Amendments and Reauthorization Act of 1986 (SARA)

Hazard categories Immediate Hazard - Yes
Delayed Hazard - No
Fire Hazard - Yes
Pressure Hazard - No
Reactivity Hazard - No

SARA 302 Extremely hazardous substance

Not listed.

SARA 311/312 Hazardous chemical No

SARA 313 (TRI reporting)

Not regulated.

Other federal regulations

Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List

Not regulated.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Butane (CAS 106-97-8)

Propane (CAS 74-98-6)

Safe Drinking Water Act (SDWA) Not regulated.

US state regulations

US. California Controlled Substances. CA Department of Justice (California Health and Safety Code Section 11100)

Not listed.

US. California. Candidate Chemicals List. Safer Consumer Products Regulations (Cal. Code Regs, tit. 22, 69502.3, subd. (a))

Butane (CAS 106-97-8)

US. Massachusetts RTK - Substance List

Butane (CAS 106-97-8)

Propane (CAS 74-98-6)

US. New Jersey Worker and Community Right-to-Know Act

Butane (CAS 106-97-8)

Propane (CAS 74-98-6)

US. Pennsylvania Worker and Community Right-to-Know Law

Butane (CAS 106-97-8)

Propane (CAS 74-98-6)

US. Rhode Island RTK

Butane (CAS 106-97-8)

Propane (CAS 74-98-6)

US. California Proposition 65

California Safe Drinking Water and Toxic Enforcement Act of 1986 (Proposition 65): This material is not known to contain any chemicals currently listed as carcinogens or reproductive toxins.

International Inventories

Country(s) or region	Inventory name	On inventory (yes/no)*
Australia	Australian Inventory of Chemical Substances (AICS)	Yes
Canada	Domestic Substances List (DSL)	Yes
Canada	Non-Domestic Substances List (NDSL)	No
China	Inventory of Existing Chemical Substances in China (IECSC)	Yes
Europe	European Inventory of Existing Commercial Chemical Substances (EINECS)	No
Europe	European List of Notified Chemical Substances (ELINCS)	No
Japan	Inventory of Existing and New Chemical Substances (ENCS)	No
Korea	Existing Chemicals List (ECL)	No
New Zealand	New Zealand Inventory	No
Philippines	Philippine Inventory of Chemicals and Chemical Substances (PICCS)	No
United States & Puerto Rico	Toxic Substances Control Act (TSCA) Inventory	Yes

*A "Yes" indicates that all components of this product comply with the inventory requirements administered by the governing country(s)

A "No" indicates that one or more components of the product are not listed or exempt from listing on the inventory administered by the governing country(s).

16. Other information, including date of preparation or last revision

Issue date 06-13-2018

Version # 01

Disclaimer We cannot anticipate all conditions under which this information and its product, or the products of other manufacturers in combination with its product, may be used. It is the user's responsibility to ensure safe conditions for handling, storage and disposal of the product, and to assume liability for loss, injury, damage or expense due to improper use. The information in the sheet was written based on the best knowledge and experience currently available.

Revision information Product and Company Identification: Alternate Trade Names