



DEFENDER
CABLE 

12/3 CONTRACTOR GRADE 3-POWER BLOCK CORDS SPECIFICATION SHEET

PRODUCT FEATURES:

- 3-Receptacle
- 12/3 Contractor grade
- Ultra flexible from -40°F to 140°F
- Abrasion and sun resistant
- Cold weather resistant
- Lighted ends w/ red indicator light
- Flame retardant
- Water resistant
- Welded hook and loop wrap for easy cord management
- Made from virgin copper for ultimate performance & quality
- 5-15 Plug and receptacle



TECHNICAL DATA:

- Made from virgin copper
- 12 Gauge wire diameter
- 3 Conductor
- Max amps
 - 20A (25' & 50')
 - 15A (100')
- Max power:
 - 2500W (25' & 50')
 - 1875W (100')
- Receptacle:
 - 3 Outlet (powerblock)
- Operating temperature range
 - -40°F-140°F
- Length: 25', 50', 100'
- Water resistant
- Flame retardant
- Lighted ends
- COO: China

STANDARDS & COMPLIANCE:

- OSHA compliant
- UL and ETL listed

APPLICATIONS & CARE:

The 3-Conductor Power Block extension cord is SJTW rated and can be used in outdoor/construction settings. It is weather resistant and can operate between -40°F to 140°F. Before using, carefully observe to see if any damage is found on the wires. During use, always look to see if the red indicator light is on. When storing, keep cables in a dry cool place away from liquid or direct sunlight.



DEFENDER
CABLE 

12/3 CONTRACTOR GRADE 3-POWER BLOCK CORDS SPECIFICATION SHEET

Packaging and Logistics Information

SKU	CORD LENGTH	JACKET COLOR	AMPS (MAX)	POWER (MAX)	CASE QTY	CASE WT	UPC
DCE-311-22	25 ft.	Yellow	20 A	2500 W	12	51 lbs.	069165847974
DCE-311-42	50 ft.	Yellow	20 A	2500 W	6	36 lbs.	069165847981
DCE-311-62	100 ft.	Yellow	15 A	1875 W	2	16 lbs.	069165847998