

# RELATIVE HUMIDITY/TEMPERATURE TRANSMITTERS

Dual Channel Design for Simultaneous 4-20 mA Output Signals

## CALIBRATION SERVICES AVAILABLE





The Series 657 Relative Humidity/Temperature Transmitters provide two 4-20 mA channels to produce separate output signals for both relative humidity and temperature. These devices deliver ±2% accuracy for humidity and ±1°F for temperature measurements. Stainless steel probe can be easily mounted to most ductwork using either of the two optional kits below.

#### BENEFITS/FEATURES

- Polymer film humidity and thin film RTD temperature sensors offer highly reliable and stable measurements.
- Remote mount housing offers installation flexibility (657-1)
- Rugged die-cast aluminum housing is great for industrial applications (657C-1)

#### **APPLICATIONS**

- · Cleanroom monitoring
- HVAC/building control monitoring

MODEL CHART		
Model	Description	
657-1 657C-	RH/temperature transmitter RH/temperature transmitter - conduit housing	

OPTIONS		
To order add suffix:	Description	
-NIST	NIST traceable humidity calibration certificate	
Example: 657C-1-NIST		

### **SPECIFICATIONS**

Service: Dry clean air.

Range: Relative humidity: 0 to 100%; Temperature: 32 to 212°F (0 to 100°C).

Accuracy: Relative humidity: ±2% (10 to 90% RH), ±3% (0 to 10% and 90 to 100%

RH); Temperature ±1°F (0.5°C).

Temperature Limits: 32 to 140°F (0 to 60°C).

Pressure Limits: 1 psi (.07 bar).

Compensated Temperature Range: 32 to 140°F (0 to 60°C).

Power Requirements: 10-35 VDC

Output Signal: 2 channels each 4-20 mA. Loop powered on the RH channel.

Electrical Connections: 4 screw type terminals. Mounting Orientation: Mount in any position.

Probe: 657-1: SS 5/16" x 10" (0.8 x 25.4 cm): 657C-1: 5/16" x 9-1/10" (0.8 x 23.1

Weight: 657-1: 5.5 oz (156 g); 657C-1: 10 oz (284 g).

ACCESSORIES			
Model	Description		
A-158 A-159	Split flange Mounting gland		



A-158

A-159