
GAS MASS FLOW METERS

Flow Range Up to 1000 L/min, Pressures Up to 1000 psi, NIST Traceable



Series GFM Gas Mass Flow Meters combine a straight tube sensor with a restrictor flow element to provide high accuracy and repeatability. Flow rates are virtually unaffected by temperature and pressure variations. Actual gas flow is displayed in engineering units on a 3-digit, 90° tiltable LCD readout. Units can be used with Series GFT Flow Totalizer for applications requiring totalization. Series GFM includes a NIST traceable certificate.

SPECIFICATIONS

Service: Clean gases compatible with wetted parts.

Wetted Materials: GFM-1XXX Wetted Materials: GFM-1XXX: Anodized aluminum, brass, 316 SS and fluoroelastomer O-rings; GFM-2XXX: 316 SS and fluoroelastomer O-rings. Accuracy: ±1% FS including linearity over 59 to 77°F (5 to 25°C) and 5 to 60 psia (0.34 to 4 bar); Series X143, X144, X145, ±1.5% FS.

Repeatability: ±0.25% of FS.
Response Time: 2 s to within ±2% of actual flow.

actual flow.

Output: Linear 0-5 VDC and

Max. Particulate Size: 5 microns. Temperature Limits: 32 to 122°F (0 to

Power Supply: ±12 VDC.

Process Connections: 1/4"

compression fitting for flow rates ≤50

L/m; 3/8" for 100 and 200 L/m; 1/2" for 500 L/min; 3/4" for 1000 L/min. **Pressure Limits:** 1000 psig (68.9 bar);

Series GFM-X143, X144, X145, 500 psig (34 5 bar)

Leak Integrity: 1 x 10-9 sccs of He. Display: 90° tiltable, 3-1/2 digit.

l 4-20 mA.	Comp	liance:	CE

MODEL CHART							
Model*	Material	Flow Range	Process Connector Compression Fitting	Model*	Material	Flow Range	Process Connector Compression Fitting
GFM-1101 GFM-1102		0 to 10 mL/m	1/4″ 1/4″	GFM-2101 GFM-2102	SS	0 to 10 mL/m	1/4″ 1/4″
GFM-1102 GFM-1103		0 to 20 mL/m 0 to 50 mL/m	1/4"		SS SS	0 to 20 mL/m 0 to 50 mL/m	1/4"
GFM-1104 GFM-1105		0 to 100 mL/m 0 to 200 mL/m	1/4" 1/4"	GFM-2104 GFM-2105	SS	0 to 100 mL/m 0 to 200 mL/m	1/4" 1/4"
GFM-1106	Aluminum	0 to 500 mL/m	1/4"	GFM-2106	SS	0 to 500 mL/m	1/4"
GFM-1107 GFM-1108		0 to 1000 mL/m 0 to 2 L/min	1/4″ 1/4″	GFM-2107 GFM-2108	SS SS	0 to 1000 mL/m 0 to 2 L/min	1/4" 1/4"
GFM-1109	Aluminum	0 to 5 L/min	1/4" 1/4"	GFM-2109	SS	0 to 5 L/min	1/4″ 1/4″
GFM-1131		0 to 15 L/min 0 to 30 L/min	1/4"		SS SS	0 to 15 L/min 0 to 30 L/min	1/4"
GFM-1133 GFM-1142		0 to 50 L/min 0 to 100 L/min	1/4" 3/8"		SS SS	0 to 50 L/min 0 to 100 L/min	1/4" 3/8"
GFM-1143	Aluminum	0 to 200 L/min	3/8"	GFM-2143	SS	0 to 200 L/min	3/8"
GFM-1144 GFM-1145		0 to 500 L/min 0 to 1000 L/min	1/2″ 3/4″	GFM-2144 GFM-2145	SS SS	0 to 500 L/min 0 to 1000 L/min	1/2" 3/4"
*Specified f	*Specified flow ranges are for an equivalent flow of nitrogen at 70°F (21°C) @ 760 mm Hg.						

ACCESSORIES		
Model	Description	
GFM-220PE GFM-CBL4	110 V power supply 220 V power supply 3' cable for 4-20 mA output 3' cable for 0-5 VDC output	

USA: California Proposition 65
WARNING: This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

Mass Flowmeters/ Controllers