




Series
SC4

Iso Verter® II Signal Conditioning Modules

Accepts Virtually All Standard Process Signals



Linearized and isolated RTD and Thermocouple transmitters are part of the Series SC4000 Iso Verter® II Signal Conditioning Modules. These modules completely isolate the input from the output and from ground. Compatible with industry standard 35 mm DIN Rail mount transmitters and isolators, these modules are easily applied in new or existing installations.

The **SC4380 Process Signal Converter/Isolator** accepts virtually all standard process signals as an input, and isolates and retransmits the signal in either the same units or virtually any other standard process signal. The SC4380 can be field programmed for reverse or direct action and can receive and transmit single sided or bipolar* signals. Low Voltage units (SCL) are also available.

The **SC4151 RTD Transmitters** each offer a fixed scale range input (selected when ordered) and a linearized, isolated, field selectable 4 to 20 mA or 0 to 10 VDC output. Output is selected by simple switch settings. Low Voltage units (SCL) are also available.

The **SC4130 Thermocouple Transmitter** offers a fixed scale range input (selected when ordered) and a linearized, isolated, field selectable 4 to 20 mA or 0 to 10 VDC output. Output is selected by simple switch settings. Low Voltage units (SCL) are also available.

Note: The term "bipolar" refers to an input or output that crosses zero volts. Certain devices have ranges that run from minus to plus voltages (eg. -1 to +5 VDC, -10 to +10 VDC, etc.). The SC4380 Iso Verter® II can be set up to accept a bipolar signal input or provide a bipolar output.

ACCESSORY

A-360, Aluminum DIN Rail 1 m

SPECIFICATIONS

Isolation: 1500 VAC RMS.

Linearity: 0.1% of full-scale.

Drift: ±0.02%/°C typical, ±0.05%/ °C maximum.

Power Supply: SC: 85 to 265 VDC/VAC 50 to 400 Hz; SCL: 12 to 24 VDC/VAC 50 to 400 Hz.

Output Loads: Current: 600 Ω max voltage: 500 Ω min (20 mA maximum).

Input Characteristics: SC4380: Voltage: 1 M Ω impedance; Current: 10 Ω; SC4151: RTD Search current < 500 μA; SC4130: 3 M Ω impedance.

Case Size: 0.866" W (22.5 mm) x 2.950" H (75.0 mm) x 3.880" D (98.5 mm).

Mounting: Mounts on industry standard 35 mm DIN Rail (DIN EN50022-35).

To Order Use Range Code as Suffix:

SC4130 & SCL4130

Model SC4130 Range Codes	Model SCL4130 Range Codes
A = J, -100 to 200°C	A = J, -100 to 200°C
C = J, 0 to 100°C	C = J, 0 to 100°C
D = J, 0 to 500°F	D = J, 0 to 500°F
E = J, 0 to 250°C	E = J, 0 to 250°C
F = J, 0 to 750°C	F = J, 0 to 750°C
G = J, 0 to 1000°F	G = J, 0 to 1000°F
H = K, -150 to 350°F	H = K, -150 to 350°F
J = K, -100 to 200°C	J = K, -100 to 200°C
K = K, 0 to 500°F	K = K, 0 to 500°F
L = K, 0 to 250°C	L = K, 0 to 250°C
M = K, 0 to 1000°F	M = K, 0 to 1000°F
N = K, 0 to 500°C	N = K, 0 to 500°C
P = K, 0 to 2000°F	P = K, 0 to 2000°F
R = K, 0 to 1000°C	R = K, 0 to 1000°C
S = T, -300 to 250°F	S = T, -300 to 250°F
T = T, -200 to 200°C	T = T, -200 to 200°C

SC4151 & SCL4151

Model SC4151 Range Codes	Model SCL4151 Range Codes
A = DIN, -100 to 200°C	A = DIN, -100 to 200°C
B = DIN, 0 to 100°C	B = DIN, 0 to 100°C
C = DIN, 0 to 150°C	C = DIN, 0 to 150°C
D = DIN, 0 to 200°F	D = DIN, 0 to 200°F
E = DIN, 0 to 200°C	E = DIN, 0 to 200°C
F = DIN, 0 to 400°F	F = DIN, 0 to 400°F
G = DIN, 0 to 250°C	G = DIN, 0 to 250°C
H = DIN, 0 to 500°F	H = DIN, 0 to 500°F
J = DIN, 0 to 500°C	J = DIN, 0 to 500°C
K = DIN, 0 to 1000°F	K = DIN, 0 to 1000°F

SC4380 & SCL4380 Operating Ranges

Inputs		Outputs	
Current	Voltage	Current	Voltage
0 to 5 mA	0 to 100 mV	0 to 1 mA	0 to 1 V
0 to 10 mA	0 to 200 mV	0 to 5 mA	0 to 5 V
0 to 10 mA	0 to 500 mV	0 to 20 mA	0 to 10 V
0 to 20 mA	0 to 1 V	1 to 5 mA	1 to 5 V
0 to 50 mA	0 to 5 V	4 to 20 mA	2 to 10 V
0 to 100 mA	0 to 10 V		
1 to 5 mA	1 to 5 V		
4 to 20 mA	2 to 10 V		
10 to 50 mA			