

# HCC3250E-IR/28

5MP HDCVI IR Dome Camera

# **HDCVI**



- · Max. 20fps@5MP
- · HD and SD output switchable
- · 3.6mm fixed lens (2.8mm optional)
- · Max. IR length 30m, Smart IR
- · IP67, IK10, DC12V















#### **System Overview**

Experience superior 5MP video and the simplicity of reusing existing coaxial infrastructure with HDCVI. The Lite series 5MP HDCVI camera features a compact design and offers a high quality image with rich details at a friendly price. It offers various vari-focal/fixed lens models with a multi-language OSD and HD/SD switchable output. Its structural flexibility and high cost-performance makes the camera an ideal choice for SMB solutions.

#### **Functions**

#### 4 Signals over 1 Coaxial Cable

HDCVI technology supports 4 signals to be transmitted over 1 coaxial cable simultaneously, i.e. video, audio\*, data and power. Dual-way data transmission allows the HDCVI camera to interact with the HCVR, such as sending control signal or triggering alarm. Moreover, HDCVI technology supports PoC for construction flexibility.

\* Audio input is available for some models of HDCVI cameras.

#### **Long Distance Transmission**

HDCVI technology guarantees long-distance and real-time transmission without any loss. It supports up to 700m for 5MP HD video via coaxial cable, and up to 300m via UTP cable.\*

\*Actual results verified by real-scene testing in Dahua's test laboratory.

#### **Simplicity**

HDCVI technology inherits the born feature of simplicity from traditional analog surveillance system, making itself a best choice for investment protection. HDCVI system can seamlessly upgrade the traditional analog system without replacing existing coaxial cabling. The plug and play approach enables full HD video surveillance without the hassle of configuring a network.

#### Smart IR

The camera is designed with microcrystalline LED IR illumination for best lowlight performance. Smart IR is a technology to ensure brightness uniformity in B/W image under low illumination. Dahua's unique Smart IR adjusts to the intensity of camera's infrared LEDs to compensate for the distance of an object, and prevents IR LEDs from overexposing images as the object come closer to the camera.

#### **HD/SD Switchable**

The camera supports switchable HDCVI high definition video output and CVBS standard definition video output. The two formats can be switched over through OSD menu or by PFM820(UTC controller). This feature makes the camera to be compatible with both HCVRs and existing analog DVRs and also facilitates debugging through analog testers.

#### Multi-language OSD

OSD menu provides multiple image adjustments and function settings to meet the requirements of different monitoring scenes. The OSD menu includes configurations such as backlight mode, day/night, white balance, privacy mask and motion detect. The camera supports 11 languages for OSD menu, namely, Chinese, English, French, German, Spanish, Portuguese, Italian, Japanese, Korean, Russian and Polish.

#### Protection

The camera's outstanding reliability is unsurpassed due to its rugged design. The camera is protected against water and dust with IP67 ranking, making it suitable for indoor or outdoor environments.

The camera complies with an IK10 vandal resistance rating making it capable of withstanding the equivalent of 5 kg (11.02 lbs) of force dropped from a height of 40 cm (15.75 in).

With working temperature range of-40 °C to +60 °C (-40 °F to +140 °F), the camera is designed for extreme temperature environments.

Supporting  $\pm 25\%$  input voltage tolerance, this camera suits even the most unstable power supply conditions. Its 4KV lightning rating provides protection against the camera and its structure from the effects of lightning.

# Lite Series | HCC3250E-IR/28

Technical Specification	1					
Camera						
Image Sensor	1/2.7" CMOS	1/2.7" CMOS				
Effective Pixels	2592(H)×1944(V), 5MP	2592(H)×1944(V), 5MP				
Scanning System	Progressive					
Electronic Shutter Speed	PAL: 1/25~1/100000s NTSC: 1/30~1/100000s					
Minimum Illumination	0.02Lux/F1.85, 30IRE, 0L	ux IR on				
S/N Ratio	More than 65dB					
IR Distance	Up to 30m (98feet)					
IR On/Off Control	Auto / Manual	Auto / Manual				
IR LEDs	12					
Lens						
Lens Type	Fixed lens / Fixed iris					
Mount Type	Board-in	Board-in				
Focal Length	3.6mm (2.8mm optional	3.6mm (2.8mm optional)				
Max Aperture	F1.85					
Angle of View	H: 77.5° (98°)					
Focus Control	N/A					
Close Focus Distance	1400mm (900mm) 55" (35")					
DORI Distance						
Note: The DORI distance is a "ge pinpoint the right camera for you sensor specification and lab test criteria for Detect, Observe, Rec	ur needs. The DORI distance i result according to EN 62676	s calculated based on i-4 which defines the				
	DORI					

	DORI Definition	Distance
Detect	25px/m (8px/ft)	2.8mm: 63m(207ft) 3.6mm: 80m(262ft)
Observe	63px/m (19px/ft)	2.8mm: 25m(82ft) 3.6mm: 32m(105ft)
Recognize	125px/m (38px/ft)	2.8mm: 13m(43ft) 3.6mm: 16m(53ft)
Identify	250ppm (76px/ft)	2.8mm: 6m(21ft) 3.6mm: 8m(26ft)

# Pan / Tilt / Rotation

	Pan: 0° ~ 355°
Pan/Tilt/Rotation	Tilt: 0° ~ 65°
	Rotation: 0° ~ 355°

# Video

Resolution	5MP (2592×1944)
Frame Rate	20fps@5MP, 25/30fps@4MP, 25/30fps@1080P
Video Output	1-channel BNC high definition video output / CVBS video output (Can switch)

Day/Night	Auto (ICR) / Manual
OSD Menu	Multi-language
BLC Mode	BLC / HLC / DWDR
WDR	DWDR
Gain Control	AGC
Noise Reduction	2D
White Balance	Auto / Manual
Smart IR	Auto / Manual

### Certifications

Certifications FCC (CFR 47 FCC Part 15 subpartB, ANSI C63.4-20.3   UL (UL60950-1+CAN/CSA C22.2 No.60950-1)
--

# Interface

Audio Interface	N/A
Eelectrical	

Power Supply	12V DC ±30%
Power Consumption	Max. 4.2W (12V DC, IR on)

### Environmental

Operating Conditions	-40°C $^{\sim}$ +60°C (-40°F $^{\sim}$ +140°F) / Less than 95% RH * Start up should be done at above-40°C (-40°F)
Storage Conditions	-40°C ~ +60°C (-40°F ~ +140°F) / Less than 95% RH
Ingress Protection & Vandal Resistance	IP67, IK10

### Construction

Casing	Aluminium
Dimensions	Ф109.9mm×81.0mm (Ф4.33"×3.19")
Net Weight	0.31kg (0.68lb)
Gross Weight	0.45kg (0.99lb)

Ordering Information				
Туре	Part Number Description			
	HCC3250E-IR/28	EMPLIDOWID David Carrers DAI		
5140.0	HCC3250E-IR/36	5MP HDCVI IR Dome Camera, PAL		
5MP Camera	HCC3250E-IR/28	SMOUDOWID D. C. NITCO		
	HCC3250E-IR/36	5MP HDCVI IR Dome Camera, NTSC		
	PFA136	Junction box (For use alone)		
Accessories	PFB203W	Wall mount (For use alone or with PFA152 pole mount)		
	PFA152-E	Pole mount (For use with PFB203W wall mount)		
	PFA200W	Rain Shade (For use with PFB203W wall mount or with PFB203W wall mount and PFA152-E pole mount)		
	PFM800-E	Passive HDCVI Balun		
	PFM800-4K	Passive Video Balun		
	PFM800B-4K	Passive Video Balun		
	PFM321	12V 1A Power Adapter		
	PFM320D-015	12V 1.5A Power Adapter		
	PFM300	12V 2A Power Adapter		
	PFM820	UTC Controller		

_							
Α	rr	00	: C	n	rı	Δ	c
$\overline{}$		-	, ,	v		c	-

### Optional:



PFA136 Junction box



PFA200W Rain shade



PFM800B-4K Passive Video Balun



PFM300 12V 2A Power Adapter



PFA152-E

Pole mount

PFM800-4K

PFM320D-015

12V 1.5A Power Adapter

Passive Video Balun

PFB203W Wall mount



PFM800-E Passive HDCVI Balun



PFM321 12V 1A Power Adapter



PFM820 UTC Controller





