

SN3208/8P-K SN3216/16P-K



Features and Functions

Professional and Reliable

Dual-OS design to ensure high reliability of system running

ANR technology to enhance the storage reliability when the network is disconnected

HD Input

H.265/H.265+/H.264/H.264+/MPEG4 video formats

Connectable to the third-party network cameras

Up to 32 IP cameras can be connected

Recording at up to 8 MP resolution

Supports live view, storage, and playback of the connected camera at up to 8 MP resolution

HD Output

HDMI and VGA independent outputs provided

HDMI Video output at up to 4K (3840 × 2160) resolution

HD Storage

Up to 2 SATA interfaces connectable for recording and backup

Storage space effectively saved by 50% to 70% with the use of H.264+ decoding format

HD Transmission

1 self-adaptive 10M/100M/1000 Mbps network interface

8/16 independent PoE network interfaces are provided

Various Applications

Centralized management of IP cameras, including configuration, information import/export, real-time information display, two-way audio, upgrade, etc.

Connectable to smart IP cameras from Hikvision and the recording, playing back, and backing up of VCA alarms can be realized

VCA detection alarm is supported

Instant playback for assigned channel during multi-channel display mode

Smart search for the selected area in the video; and smart playback to improve the playback efficiency


Supports HDD quota and group modes; different capacity can be assigned to different channels

Hik-Connect for easy network management

Specifications

Model		SN3208/8P-K	SN3216/16P-K		
Video/ Audio input	IP video input	16-ch	32-ch		
	Incoming bandwidth	160 Mbps	256 Mbps		
	Outgoing bandwidth	160 Mbps			
Video/ Audio output	HDMI output resolution	4K (3840 × 2160)/30Hz, 2K (2560 × 1440)/60Hz, 1920 × 1080/60Hz, 1600 × 1200/60Hz, 1280 × 1024/60Hz, 1280 × 720/60Hz, 1024 × 768/60Hz			
	VGA output resolution	1920 × 1080/60Hz, 1280 × 1024/60Hz, 1280 × 720/60Hz, 1024 × 768/60Hz			
	Audio output	1-ch, RCA (Linear, 1 KΩ)			
Decoding	Decoding format	H.265/H.265+/H.264/H.264+/MPEG4			
	Recording resolution	8MP/6MP/5MP/4MP/3MP/1080p/UXGA/720p/VGA/4CIF/DCIF/2CIF/CIF/QCIF			
	Synchronous playback	16-ch			
	Capability	2-ch @ 8 MP (25fps) / 4-ch @ 4MP (30fps) / 8-ch @ 1080p (30fps)			
Network management	Network protocols	TCP/IP, DHCP, Hik-Connect, DNS, DDNS, NTP, SADP, SMTP, NFS, iSCSI, UPnP™, HTTPS			
Hard disk	SATA	2 SATA interfaces			
	Capacity	Up to 6TB capacity for each HDD			
External interface	Two-way audio	1-ch, RCA (2.0 Vp-p, 1kΩ)			
	Network interface	1 RJ-45 10/100/1000 Mbps self-adaptive Ethernet interface			
	USB interface	Front panel: 1 × USB 2.0; Rear panel: 1 × USB 3.0			
	Alarm in/out	4/1			
POE interface	Interface	16, RJ-45 10/100 Mbps self-adaptive Ethernet interface			
	Power	≤ 200 W			
	Supported standard	IEEE 802.3 af/at			
General	Power supply	100 to 240 VAC			
	Power	≤ 280 W			
	Consumption (without hard disk)	≤ 15 W (without enabling PoE)			
	Working temperature	-10 to +55° C (14 to 131° F)			
	Working humidity	10 to 90 %			
	Chassis	385 mm chassis			
	Dimensions $(W \times D \times H)$	385 × 315× 52 mm (15.2" × 12.4" × 2.0")			
	Weight (without hard disk)	≤ 3 kg (6.6 lb)			

Physical Interfaces



Index	Description	Index	Description
1	AUDIO IN	7	USB 3.0 Interface.
2	AUDIO OUT	8	GND
3	VGA Interface	9	100 to 240 VAC power supply
4	HDMI Interface	10	Power Switch
5	Controller Port, Alarm In/Alarm Out	11	Network Interfaces with PoE function
6	LAN Network Interface		