

**LEVER BODY**

Glass-fibre reinforced polyamide based (PA) technopolymer, black colour, matte finish.

**PUSH BUTTON**

Technopolymer, black colour, matte finish.

**STANDARD EXECUTIONS**

Glass-fibre reinforced technopolymer clamping element with retaining pin, black colour, with knurling on the protruding part to make initial tightening easier. AISI 302 stainless steel return spring.

- **MRX-B:** brass boss, threaded blind hole.
- **MRX-SST:** AISI 303 stainless steel boss, threaded blind hole.
- **MRX-p:** zinc-plated steel threaded stud, chamfered flat end ISO 4753 (see Technical Data on page A-11).
- **MRX-SST-p:** AISI 303 stainless steel threaded stud, chamfered flat end ISO 4753 (see Technical Data on page A-11).

**FEATURES AND APPLICATIONS**

Particularly suitable when the lever turning angle is limited owing to lack of space.

Compared to other types of adjustable handles with metal retaining screw this solution offers:

- absolute electric insulation for the operator
- more comfortable lever release.

**STRESS RESISTANCE**

See ERX. on page 264.

**OTHER EXECUTIONS AVAILABLE**


Lever body in orange (C2) with black push button (C1).  
Example: code 941131-C2-C1 description MRX.40-C2-B-10-C1

**SPECIAL EXECUTIONS ON REQUEST**

Lever body in RAL 7031 grey.

**INSTRUCTIONS OF USE**

For clamping, lift the lever to disengage the clamping device teeth and bring it back to start position. By releasing the lever, the return spring automatically engages the teeth.




**MRX-B**

Code	Description	R	d2B	L	D	H	H1	h	h1	h2	h3	d1	Teeth no.	⚖
941131	MRX.40 B-10-24	1.65	10-24	1.97	0.71	1.26	1.4	0.39	1.14	0.24	0.55	0.47	18	0.02
941133	MRX.40 B-10-32	1.65	10-32	1.97	0.71	1.26	1.4	0.39	1.14	0.24	0.55	0.47	18	0.02
941141	MRX.40 B-1/4-20	1.65	1/4-20	1.97	0.71	1.26	1.4	0.39	1.14	0.24	0.55	0.47	18	0.03
941411	MRX.63 B-1/4-20	2.48	1/4-20	2.87	0.91	1.69	1.83	0.47	1.46	0.31	0.67	0.59	20	0.05
941421	MRX.63 B-5/16-18	2.48	5/16-18	2.87	0.91	1.69	1.83	0.51	1.46	0.31	0.67	0.59	20	0.05
942111	MRX.80 B-5/16-18	3.15	5/16-18	3.62	1.1	2.13	2.3	0.71	1.85	0.39	0.87	0.75	24	0.1
942121	MRX.80 B-3/8-16	3.15	3/8-16	3.62	1.1	2.13	2.3	0.67	1.85	0.39	0.87	0.75	24	0.11
942131	MRX.80 B-1/2-13	3.15	1/2-13	3.62	1.1	2.13	2.3	0.67	1.85	0.39	0.87	0.75	24	0.11
942501	MRX.100 B-3/8-16	3.94	3/8-16	4.49	1.3	2.56	2.74	0.79	2.13	0.47	0.98	0.98	28	0.17
942511	MRX.100 B-1/2-13	3.94	1/2-13	4.49	1.3	2.56	2.74	0.79	2.13	0.47	0.98	0.98	28	0.18

**MRX-SST**

Code	Description	R	d2B	L	D	H	H1	h	h1	h2	h3	d1	Teeth no.	⚖
941191	MRX.40-SST-1/4-20	1.65	1/4-20	1.97	0.71	1.26	1.4	0.39	1.14	0.24	0.55	0.47	18	0.03
941431	MRX.63-SST-5/16-18	2.48	5/16-18	2.87	0.91	1.69	1.83	0.51	1.46	0.31	0.67	0.59	20	0.05
942151	MRX.80-SST-3/8-16	3.15	3/8-16	3.62	1.1	2.13	2.3	0.67	1.85	0.39	0.87	0.75	24	0.1





INCH

MRX-p

Code	Description	R	d2A	L	D	H	H1	h1	h2	h3	d1	l	Teeth no.	Δ
941221	MRX.40 p-10-24x3/4	1.65	10-24	1.97	0.71	1.26	1.4	1.14	0.24	0.55	0.47	0.750	18	0.03
941241	MRX.40 p-10-32x1/2	1.65	10-32	1.97	0.71	1.26	1.4	1.14	0.24	0.55	0.47	0.500	18	0.02
941243	MRX.40 p-10-32x3/4	1.65	10-32	1.97	0.71	1.26	1.4	1.14	0.24	0.55	0.47	0.750	18	0.02
941301	MRX.40 p-1/4-20x1/2	1.65	1/4-20	1.97	0.71	1.26	1.4	1.14	0.24	0.55	0.47	0.500	18	0.03
941321	MRX.40 p-1/4-20x3/4	1.65	1/4-20	1.97	0.71	1.26	1.4	1.14	0.24	0.55	0.47	0.750	18	0.03
941331	MRX.40 p-1/4-20x1	1.65	1/4-20	1.97	0.71	1.26	1.4	1.14	0.24	0.55	0.47	1.000	18	0.04
941341	MRX.40 p-1/4-20x1½	1.65	1/4-20	1.97	0.71	1.26	1.4	1.14	0.24	0.55	0.47	1.500	18	0.04
941441	MRX.63 p-1/4-20x1/2	2.48	1/4-20	2.87	0.91	1.69	1.83	1.46	0.31	0.67	0.59	0.500	20	0.06
941451	MRX.63 p-1/4-20x3/4	2.48	1/4-20	2.87	0.91	1.69	1.83	1.46	0.31	0.67	0.59	0.750	20	0.06
941461	MRX.63 p-1/4-20x1	2.48	1/4-20	2.87	0.91	1.69	1.83	1.46	0.31	0.67	0.59	1.000	20	0.07
941471	MRX.63 p-1/4-20x1½	2.48	1/4-20	2.87	0.91	1.69	1.83	1.46	0.31	0.67	0.59	1.500	20	0.07
941501	MRX.63 p-5/16-18x1/2	2.48	5/16-18	2.87	0.91	1.69	1.83	1.46	0.31	0.67	0.59	0.500	20	0.06
941511	MRX.63 p-5/16-18x3/4	2.48	5/16-18	2.87	0.91	1.69	1.83	1.46	0.31	0.67	0.59	0.750	20	0.07
941521	MRX.63 p-5/16-18x1	2.48	5/16-18	2.87	0.91	1.69	1.83	1.46	0.31	0.67	0.59	1.000	20	0.07
941531	MRX.63 p-5/16-18x1¼	2.48	5/16-18	2.87	0.91	1.69	1.83	1.46	0.31	0.67	0.59	1.250	20	0.08
941541	MRX.63 p-5/16-18x1½	2.48	5/16-18	2.87	0.91	1.69	1.83	1.46	0.31	0.67	0.59	1.500	20	0.09
941561	MRX.63 p-5/16-18x2	2.48	5/16-18	2.87	0.91	1.69	1.83	1.46	0.31	0.67	0.59	2.000	20	0.09
942201	MRX.80 p-3/8-16x3/4	3.15	3/8-16	3.62	1.1	2.13	2.3	1.85	0.39	0.87	0.75	0.750	24	0.13
942211	MRX.80 p-3/8-16x1	3.15	3/8-16	3.62	1.1	2.13	2.3	1.85	0.39	0.87	0.75	1.000	24	0.14
942221	MRX.80 p-3/8-16x1¼	3.15	3/8-16	3.62	1.1	2.13	2.3	1.85	0.39	0.87	0.75	1.250	24	0.15
942231	MRX.80 p-3/8-16x1½	3.15	3/8-16	3.62	1.1	2.13	2.3	1.85	0.39	0.87	0.75	1.500	24	0.15
942241	MRX.80 p-3/8-16x2	3.15	3/8-16	3.62	1.1	2.13	2.3	1.85	0.39	0.87	0.75	2.000	24	0.17
942321	MRX.80 p-1/2-13x1¼	3.15	1/2-13	3.62	1.1	2.13	2.3	1.85	0.39	0.87	0.75	1.250	24	0.18
942331	MRX.80 p-1/2-13x1½	3.15	1/2-13	3.62	1.1	2.13	2.3	1.85	0.39	0.87	0.75	1.500	24	0.18
942341	MRX.80 p-1/2-13x2	3.15	1/2-13	3.62	1.1	2.13	2.3	1.85	0.39	0.87	0.75	2.000	24	0.21
942601	MRX.100 p-1/2-13x1¼	3.94	1/2-13	4.49	1.3	2.56	2.74	2.13	0.47	0.98	0.98	1.250	28	0.24
942631	MRX.100 p-1/2-13x1½	3.94	1/2-13	4.49	1.3	2.56	2.74	2.13	0.47	0.98	0.98	1.500	28	0.26
942651	MRX.100 p-1/2-13x2	3.94	1/2-13	4.49	1.3	2.56	2.74	2.13	0.47	0.98	0.98	2.000	28	0.29

MRX-SST-p

INOX STAINLESS STEEL

INCH

Code	Description	R	d2A	L	D	H	H1	h1	h2	h3	d1	l	Teeth no.	Δ
941361	MRX.40-SST-p-1/4-20x1/2	1.65	1/4-20	1.97	0.71	1.26	1.4	1.14	0.24	0.55	0.47	0.500	18	0.03
941365	MRX.40-SST-p-1/4-20x3/4	1.65	1/4-20	1.97	0.71	1.26	1.4	1.14	0.24	0.55	0.47	0.750	18	0.04
941371	MRX.40-SST-p-1/4-20x1	1.65	1/4-20	1.97	0.71	1.26	1.4	1.14	0.24	0.55	0.47	1.000	18	0.04
941611	MRX.63-SST-p-5/16-18x3/4	2.48	5/16-18	2.87	0.91	1.69	1.83	1.46	0.31	0.67	0.59	0.750	20	0.07
941615	MRX.63-SST-p-5/16-18x1	2.48	5/16-18	2.87	0.91	1.69	1.83	1.46	0.31	0.67	0.59	1.000	20	0.07
941621	MRX.63-SST-p-5/16-18x1¼	2.48	5/16-18	2.87	0.91	1.69	1.83	1.46	0.31	0.67	0.59	1.250	20	0.08
942381	MRX.80-SST-p-3/8-16x1	3.15	3/8-16	3.62	1.1	2.13	2.3	1.85	0.39	0.87	0.75	1.000	24	0.14
942385	MRX.80-SST-p-3/8-16x1¼	3.15	3/8-16	3.62	1.1	2.13	2.3	1.85	0.39	0.87	0.75	1.250	24	0.15
942391	MRX.80-SST-p-3/8-16x1½	3.15	3/8-16	3.62	1.1	2.13	2.3	1.85	0.39	0.87	0.75	1.500	24	0.15
942401	MRX.80-SST-p-3/8-16x2	3.15	3/8-16	3.62	1.1	2.13	2.3	1.85	0.39	0.87	0.75	2.000	24	0.17