

WE MAKE THE CUT™



Kett Tool PS-526 Panel Saw

Features:

- 90 PSI pistol grip, variable speed, 2200 rpm motor
- Replaceable high-speed steel saw blades
- Cuts cold-rolled mild steel up to 16 gauge, aluminum to 0.100", plastic, and other rigid materials
- Adjustable depth of cut up to $\frac{3}{8}$ "
- Plunge cuts for smooth, safe cutting
- Lightweight and easily maneuverable

Specifications:

CFM 16	Rigid Materials 5/16"
RPM 0 to 2,200	Cold-rolled Mild Steel 16 gauge
Power Source 90 PSI compressed air	Aluminum 0.100 inches
Saw Unit KS-26	Length 13.5 inches
Maximum Depth of Cut $\frac{3}{8}$ "	Weight 5 pounds
	Other Configurations 120V Electric pistol grip

Kett Tool Company
5055 Madison Road
Cincinnati, OH 45227
(513) 271-0333

www.kett-tool.com
info@kett-tool.com

