

WE MAKE THE CUT™



Kett Tool P-2042 16 Gauge Double Cut Shear

Features:

- 90 PSI straight handle, variable speed, 2500 rpm motor
- Replaceable A-2 tool steel shear blades
- Cuts cold-rolled mild steel up to 16 gauge, most grades of stainless steel to 18 gauge
- Cuts up to 170 inches per minute
- With the 7/32" waste strip, you get a clean, burr free cut
- Lightweight and easily maneuverable - can cut a 7" radius

Specifications:

| | |
|--|---|
| CFM 16 | Minimum Cutting Radius 7 inches |
| RPM 0 to 2,500 | Cold-rolled Mild Steel 16 gauge |
| Power Source 90 PSI compressed air | Stainless Steel 18 gauge |
| Shear Head 42-20 Aluminum | Length 10.5 inches |
| Cutting Speed 170 inches per minute | Weight 3.5 pounds |
| | Other Configurations 90 PSI pistol grip 120V Electric pistol grip |

Kett Tool Company
5055 Madison Road
Cincinnati, OH 45227
(513) 271-0333

www.kett-tool.com
info@kett-tool.com

KETT
TOOL COMPANY

