# Digital position indicators

direct drive, 4-digit counter, technopolymer











































# BASE AND CASE

High-resistance polyamide based (PA) technopolymer.

Case in the following colours:

- C2: RAL 2004 orange, glossy finish.
- C3: RAL 7035 grey, glossy finish.
- C1: RAL 7021 grey-black, glossy finish.

The ultrasonically welding between the base and the case prevents separation and avoids dust penetration.

#### WINDOW

Transparent polyamide based (PA-T) technopolymer, moulded over the case and with a perfect seal (avoid contact with alcohol during cleaning operations).

#### **DISPLAY**

It indicates the displacement of the mechanism controlled by the spindle from the start position (0).

Four-digit roller counter (three black rolls and one red roll or two black rolls and two red rolls). The digits of red rolls show the decimal values. An additional graduated scale next to the last decimal digit offers further accuracy of reading.

The display can be in different positions (see "Table of the possible combinations").

- AN: inclined display, counter in upper position.
- AR: inclined display, counter in lower position.
- FN: front display, counter in upper position.
- FR: front display, counter in lower position.

#### INTERNAL GASKET

O-ring front sealing in NBR synthetic rubber, between the case and the boss.

#### REAR GASKET

Foam polyethylene, supplied.

# STANDARD EXECUTION

Boss with DIA 0.500 (Ø 12.7 mm) standard reamed hole, fitting to shaft by means of a supplied grub screw with hexagon socket and cup end.

- DD51: black-oxide steel boss.
- DD51-SST: AISI 303 stainless steel boss.

# DIRECTION OF ROTATION

- D: clockwise. Increasing values with clockwise rotation of the boss.
- S: anti-clockwise. Increasing values with anti-clockwise rotation of the boss.

#### WEIGHT

0.152 lbs.

#### FEATURES AND APPLICATIONS

Direct drive digital position indicators can be assembled on passing through spindles in any position to give direct reading of the positioning of a machine component. They are suitable also for motor driven applications (see "Table of the possible combinations").

## **ERGONOMY AND DESIGN**


Compact roller counter, ergonomically designed digits for rapid reading. The readability of the counter is increased by the magnifying window.


# ASSEMBLY INSTRUCTIONS


- 1. Drill a DIA 0.24 by 0.39 (Ø 6 mm by Ø 10 mm) hole in the body of the machine with a 0.87 (22 mm) centre distance from the spindle to fit the rear referring pin.
- 2. Set the spindle to the start or referring position.
- 3. Fit the indicator with the zeroed roller counter onto the spindle and make sure that the referring pin fit the hole.
- 4. Clamp the boss to the spindle by tightening the grub screw with hexagon socket and cup end.



ELESA Original design


























# Position indicators

# Example of description for ordering



Rotational speed tests have been performed in our laboratory under standard operating conditions. It is recommended not to subject the product to sudden acceleration and / or sudden stop.

00.57

00.60

00.65(5)

00.75

00.80

00.83(3)

01.00

01.20

01.25

01.57

02.00

0.057

0.060

0.065(5)

0.075

0.080

0.083(3)

0.100

0.120

0.125

0.157

0.200

5.7

6.0

6.55

7.5

8.0

8.33

10.0

12.0

12.5

15.7

20.0

1.25

10

8

5

435

415

370

330 315

300

250

205

200

150

125

005.7

006.0

006.5(5)

007.5

0.800

008.3(3)

010.0

012.0

012.5

015.7

020.0

0057

0060

0065(5)

0075

0080

0100

0120

0125 0157

0200

<sup>\*</sup> The maximum rotation speed (rpm) of the spindle reported in the table corresponds to a maximum rotation of 2500 units of the last roll on the right of the counter.


























#### SPECIAL EXECUTIONS ON REQUEST

- Special readings after one revolution.
- Case in different colours.
- Completely sealed digital position indicators with IP 67 protection class, see IEC 529 table (see page A-19) obtained by means of a brass bushing with double seal ring inside the rear cavity of the base.

## LB - LOCKING DEVICE


The DD51-LB position indicators are designed to lock the spindle on which they are mounted to avoid the risk of accidental adjustment alterations due to vibrations. To lock or unlock the spindle rotation, simply move the lever, in pos. A equivalent to unlocked spindle, in pos. B equivalent to locked spindle. Following repeated locking cycles, the special device is highly wear resistant and functions perfectly over time. To order the indicator with spindle locking add the –LB index after the code and description (e.g. CE.84101-LB DD51-AN-00.50-D-C3-LB).





# ACCESSORIES ON REQUEST (TO BE ORDERED SEPARATELY)


 BS51: glass-fibre reinforced polyamide based (PA) technopolymer spacer plate (code CE.85900).



 MD51 (see page 615): polyamide based (PA) technopolymer fluted grip control knob.



- RB51: black-oxide steel reduction sleeves.
- RB51-SST: AISI 304 stainless steel reduction sleeves.



RB51	INCH	
Code	Description	d
CE985940	RB51-1/2-1/4	0.250+.0006
CE985950	RB51-1/2-3/8	0.375+.0008

RB51-SST			INOX STAINLESS STEEL INCH	
	Code	Description		d
	CE995941	RB51 1/2-1/4 SST-304	(	0.250+.0006
	CE995956	RB51 1/2-3/8-SST-304	(	0.375+.0008