



# Combo Burnishing

## ultra high speed burnishing pad

### PRODUCT SPECIFICATIONS

#### 1.0 Description

The Combo floor maintenance UHS burnishing pad is constructed of blended polyester and natural fibers in a textured nonwoven fabrication.

#### 2.0 Properties

Property	Value
Thickness	1 in 26 mm
Weight	31 osy 1051 gsm
Fiber Type	Recycled Polyester and Natural Hair
Binder System	Cross-linkable water based
Binder Application	Spray/Dip
Abrasive Application	N/A
Abrasive	N/A
Color	White/Black Blend
Pack	5 per case*

\*27" and 28" also available in 2 per case



Full Cycle® Products are certified by Green Seal™ for Environmental Innovation based on faster biodegradation in landfill conditions and 100% recycled content/natural fiber. Green Seal.orgGS20

*Note: Due to the intrinsic properties of the material and variable conditions of use, there may be slight variations in the specifications and results. Please contact Americo with any questions or concerns.*

#### 3.0 Use

This pad is used to burnish/polish floor finish to a high gloss. Recommended for use on soft to medium finishes. Ideal for use on machines speeds up to 3000 rpm.

#### 4.0 Construction

The Combo Ultra High Speed Burnishing Pad is made of 100% recycled polyester and natural fibers with water based resins. This pad has been designed for use on both sides.

#### 5.0 Labeling

Labeling is to clearly identify product, size, and quantity. Americo brand or private label is available for this product.

#### 6.0 Environmental Initiatives

- Polyester fiber used in our pads come from 100% post consumer and industrial recycled waste product.
- Full Cycle™**, formulated to biodegrade\* in a fraction of the time that it takes conventional floor pads once discarded into an active landfill.
- Water Based Latex Resins are used in the manufacturing process. No phenol-formaldehyde resins are used in our binding process.
- Shipping cartons contain at least 45% recycled material.
- Plant is operating under EPA approved Clean Air Permit.

\* For complete details or to view ASTM D5511 test results visit [www.AmericoFullCycle.com](http://www.AmericoFullCycle.com)

#### 7.0 Directions for Use

Dust mop floors prior to burnishing. Use pad until finish gives high gloss. Dust mop again to remove dust from burnishing.

#### 8.0 Product Care

To prolong the life of this product it may be washed using a hose with a pressure spray nozzle to remove soil. Allow pad to dry completely before using again.

#### 9.0 Sizes

Disc Size (Diameter) (O.D. ± 0.06 inch)	Center Hole
12 inch	3.25 inch
13 inch	3.25 inch
14 inch	3.25 inch
15 inch	3.25 inch
16 inch	3.25 inch
17 inch	3.25 inch
18 inch	3.25 inch
19 inch	3.25 inch
20 inch	3.25 inch
21 inch	3.25 inch
22 inch	3.25 inch
23 inch	3.25 inch
24 inch	3.25 inch
27 inch	3.25 inch
28 inch	3.25 inch

*Additional sizes available.*

*Check for availability on additional center hole dimensions.*

**Americo Manufacturing Company, Inc.**

1-800-849-6287  
[www.americomfg.com](http://www.americomfg.com)

© 2017

Rev. 06/01/17  
Combo Burnishing Product Specifications