

A00142 MST PAINLESS STAINLESS 20net18

Version 3.0

Revision Date 10/05/2015

Print Date 10/14/2015

SECTION 1. PRODUCT AND COMPANY IDENTIFICATION

Material name : A00142 MST PAINLESS STAINLESS 20net18

Material number : 00000000001001557

Manufacturer or supplier's details

Company : Zep Inc.

Address : 1310 Seaboard Industrial Blvd., NW
Atlanta, GA 30318

Telephone : 404-352-1680

Emergency telephone numbers
For SDS Information : Compliance Services 1-877-428-9937

For a Medical Emergency : 877-541-2016 Toll Free - All Calls Recorded

**For a Transportation
Emergency** : CHEMTREC: 800-424-9300 - All Calls Recorded.
In the District of Columbia 202-483-7616

SECTION 2. HAZARDS IDENTIFICATION
Emergency Overview

Appearance	Aerosol containing a liquefied gas
Colour	light cream
Odour	characteristic

GHS Classification

Gases under pressure : Liquefied gas

Skin sensitisation : Category 1

GHS Label element

Hazard pictograms :



Signal word : Warning

Hazard statements : H280 Contains gas under pressure; may explode if heated.
H317 May cause an allergic skin reaction.
 Precautionary statements : **Prevention:**
 P261 Avoid breathing dust/ fume/ gas/ mist/ vapours/ spray.
 P272 Contaminated work clothing should not be allowed out of the workplace.
 P280 Wear protective gloves.
 P251 Pressurized container: Do not pierce or burn, even after use.
Response:
 P302 + P352 IF ON SKIN: Wash with plenty of soap and water.
 P333 + P313 If skin irritation or rash occurs: Get medical

A00142 MST PAINLESS STAINLESS 20net18

Version 3.0

Revision Date 10/05/2015

Print Date 10/14/2015

advice/ attention.

P363 Wash contaminated clothing before reuse.

Storage:

P410 + P403 Protect from sunlight. Store in a well-ventilated place.

P412 Do not expose to temperatures exceeding 50 °C/ 122 °F.

Disposal:

Dispose of contents/container in accordance with local regulation.

Potential Health Effects**Carcinogenicity:****IARC**

No component of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.

ACGIH

No component of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.

OSHA

No component of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.

NTP

No component of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS**Hazardous components**

Chemical Name	CAS-No.	Concentration [%]
Distillates (petroleum), hydrotreated light	64742-47-8	>= 10 - < 20
Petroleum Distillates	64742-96-7	>= 10 - < 20
propane	74-98-6	>= 5 - < 10
butane	106-97-8	>= 1 - < 5
Naphtha (petroleum), hydrotreated light	64742-49-0	>= 1 - < 5
citral	5392-40-5	>= 0.1 - < 1

SECTION 4. FIRST AID MEASURES

- General advice : Move out of dangerous area.
Show this safety data sheet to the doctor in attendance.
Do not leave the victim unattended.
- If inhaled : If unconscious place in recovery position and seek medical advice.
If symptoms persist, call a physician.
- In case of skin contact : If skin irritation persists, call a physician.
Wash off immediately with plenty of water for at least 15 minutes.
If on clothes, remove clothes.

A00142 MST PAINLESS STAINLESS 20net18

Version 3.0

Revision Date 10/05/2015

Print Date 10/14/2015

- In case of eye contact : Rinse immediately with plenty of water for at least 15 minutes.
Remove contact lenses.
Protect unharmed eye.
Keep eye wide open while rinsing.
If eye irritation persists, consult a specialist.
- If swallowed : Keep respiratory tract clear.
DO NOT induce vomiting unless directed to do so by a physician or poison control center.
Never give anything by mouth to an unconscious person.
If symptoms persist, call a physician.
-

SECTION 5. FIREFIGHTING MEASURES

- Suitable extinguishing media : Alcohol-resistant foam
Carbon dioxide (CO₂)
Dry chemical
Water spray jet
- Unsuitable extinguishing media : High volume water jet
- Specific hazards during firefighting : Do not allow run-off from fire fighting to enter drains or water courses.
- Hazardous combustion products : Carbon dioxide (CO₂)
Carbon monoxide
Smoke
- Specific extinguishing methods : Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
- Further information : Collect contaminated fire extinguishing water separately. This must not be discharged into drains.
Fire residues and contaminated fire extinguishing water must be disposed of in accordance with local regulations.
- Special protective equipment for firefighters : Wear self-contained breathing apparatus for firefighting if necessary.
-

SECTION 6. ACCIDENTAL RELEASE MEASURES

- Personal precautions, protective equipment and emergency procedures : Use personal protective equipment.
Evacuate personnel to safe areas.
Beware of vapours accumulating to form explosive concentrations. Vapours can accumulate in low areas.
Ensure adequate ventilation.
Remove all sources of ignition.
- Environmental precautions : Prevent product from entering drains.
Prevent further leakage or spillage if safe to do so.
If the product contaminates rivers and lakes or drains inform respective authorities.

A00142 MST PAINLESS STAINLESS 20net18

Version 3.0

Revision Date 10/05/2015

Print Date 10/14/2015

Methods and materials for containment and cleaning up : Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust).
Keep in suitable, closed containers for disposal.

SECTION 7. HANDLING AND STORAGE

Advice on safe handling : Do not breathe vapours or spray mist.
Avoid exposure - obtain special instructions before use.
Avoid contact with skin and eyes.
For personal protection see section 8.
Smoking, eating and drinking should be prohibited in the application area.
Dispose of rinse water in accordance with local and national regulations.
Always replace cap after use.

Conditions for safe storage : BEWARE: Aerosol is pressurized. Keep away from direct sun exposure and temperatures over 50 °C. Do not open by force or throw into fire even after use. Do not spray on flames or red-hot objects.
No smoking.
Keep in a dry, cool and well-ventilated place.
Containers which are opened must be carefully resealed and kept upright to prevent leakage.
Observe label precautions.
Electrical installations / working materials must comply with the technological safety standards.

Materials to avoid : Oxidizing agents

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION
Components with workplace control parameters

Components	CAS-No.	Value type (Form of exposure)	Control parameters / Permissible concentration	Basis
Distillates (petroleum), hydrotreated light	64742-47-8	TWA	500 ppm 2,000 mg/m ³	OSHA Z-1
		TWA	400 ppm 1,600 mg/m ³	OSHA P0
propane	74-98-6	TWA	1,000 ppm	ACGIH
		TWA	1,000 ppm 1,800 mg/m ³	NIOSH REL
		TWA	1,000 ppm 1,800 mg/m ³	OSHA Z-1
		TWA	1,000 ppm 1,800 mg/m ³	OSHA P0
butane	106-97-8	TWA	800 ppm 1,900 mg/m ³	NIOSH REL
		TWA	800 ppm 1,900 mg/m ³	OSHA P0

A00142 MST PAINLESS STAINLESS 20net18

Version 3.0

Revision Date 10/05/2015

Print Date 10/14/2015

Personal protective equipment

- Respiratory protection : Use respiratory protection unless adequate local exhaust ventilation is provided or exposure assessment demonstrates that exposures are within recommended exposure guidelines.
- Hand protection
Remarks : The suitability for a specific workplace should be discussed with the producers of the protective gloves.
- Eye protection : Safety glasses
Ensure that eyewash stations and safety showers are close to the workstation location.
- Skin and body protection : Impervious clothing
Choose body protection according to the amount and concentration of the dangerous substance at the work place.
- Hygiene measures : When using do not eat or drink.
When using do not smoke.
Wash hands before breaks and at the end of workday.
-

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

- Appearance : Aerosol containing a liquefied gas
- Colour : light cream
- Odour : characteristic
- Odour Threshold : No data available
- pH : No data available
- Melting point/freezing point : No data available
- Boiling point : No data available
- Flash point :
No data available
- Evaporation rate : No data available
- Flammability (solid, gas) : The product is not flammable.
- Upper explosion limit : No data available
- Lower explosion limit : No data available
- Vapour pressure : No data available
- Relative vapour density : No data available
- Density : 0.938 g/cm³
- Solubility(ies)
- Water solubility : partly soluble
- Solubility in other solvents : not determined
-

A00142 MST PAINLESS STAINLESS 20net18

Version 3.0

Revision Date 10/05/2015

Print Date 10/14/2015

Partition coefficient: n-octanol/water	:	No data available
Auto-ignition temperature	:	not determined
Thermal decomposition	:	No data available
Viscosity	:	
Viscosity, kinematic	:	No data available
Heat of combustion	:	15.00 kJ/g

SECTION 10. STABILITY AND REACTIVITY

Reactivity	:	Stable
Chemical stability	:	Stable under normal conditions.
Possibility of hazardous reactions	:	No decomposition if stored and applied as directed.
Conditions to avoid	:	Heat, flames and sparks. Extremes of temperature and direct sunlight.
Incompatible materials	:	Oxidizing agents
Hazardous decomposition products	:	Carbon oxides

SECTION 11. TOXICOLOGICAL INFORMATION**Acute toxicity****Components:****Distillates (petroleum), hydrotreated light:**

Acute oral toxicity	:	LD50 Rat: > 5,000 mg/kg
Acute inhalation toxicity	:	LC50 Rat: > 4.6 mg/l Exposure time: 6 h
Acute dermal toxicity	:	LD50 Rat: > 2,000 mg/kg

propane:

Acute inhalation toxicity	:	LC50 Mouse: 1,237 mg/l Exposure time: 2 h
	:	LC50 Rat: 658 mg/l Exposure time: 4 h

A00142 MST PAINLESS STAINLESS 20net18

Version 3.0

Revision Date 10/05/2015

Print Date 10/14/2015

LC50 Rat: 1,355 mg/l

butane:

Acute inhalation toxicity : LC50 Mouse: 1,237 mg/l
Exposure time: 2 h

LC50 Rat: 1,355 mg/l

Skin corrosion/irritation

Product:

Remarks: May cause skin irritation and/or dermatitis.

Serious eye damage/eye irritation

Product:

Remarks: May irritate eyes.

Respiratory or skin sensitisation

Product:

Remarks: Causes sensitisation.

Germ cell mutagenicity

No data available

Carcinogenicity

No data available

Reproductive toxicity

No data available

Distillates (petroleum), hydrotreated light:

Petroleum Distillates:

propane:

butane:

Naphtha (petroleum), hydrotreated light:

citral:

STOT - single exposure

No data available

STOT - repeated exposure

No data available

Aspiration toxicity

No data available

Further information

Product:

Remarks: No data available

A00142 MST PAINLESS STAINLESS 20net18

Version 3.0

Revision Date 10/05/2015

Print Date 10/14/2015

Components:

Distillates (petroleum), hydrotreated light:

Remarks: No data available

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity

No data available

Persistence and degradability

No data available

Bioaccumulative potential**Product:**

Partition coefficient: n-octanol/water : Remarks: No data available

Components:**butane :**

Partition coefficient: n-octanol/water : Pow: 2.89

citral :

Partition coefficient: n-octanol/water : Pow: 2.76

Mobility in soil

No data available

Other adverse effects

No data available

Product:

Regulation 40 CFR Protection of Environment; Part 82 Protection of Stratospheric Ozone - CAA Section 602 Class I Substances

Remarks This product neither contains, nor was manufactured with a Class I or Class II ODS as defined by the U.S. Clean Air Act Section 602 (40 CFR 82, Subpt. A, App.A + B).

Additional ecological information : An environmental hazard cannot be excluded in the event of unprofessional handling or disposal., Harmful to aquatic life with long lasting effects.

Components:

Distillates (petroleum), hydrotreated light :

Additional ecological information : No data available

SECTION 13. DISPOSAL CONSIDERATIONS

SAFETY DATA SHEET



A00142 MST PAINLESS STAINLESS 20net18

Version 3.0

Revision Date 10/05/2015

Print Date 10/14/2015

Disposal methods

- Waste from residues : The product should not be allowed to enter drains, water courses or the soil.
Do not contaminate ponds, waterways or ditches with chemical or used container.
Dispose of in accordance with local regulations.
- Contaminated packaging : Empty remaining contents.
Dispose of as unused product.
Do not re-use empty containers.
Do not burn, or use a cutting torch on, the empty drum.

SECTION 14. TRANSPORT INFORMATION

Transportation Regulation: 49 CFR (USA):
ORM-D, CONSUMER COMMODITY

Transportation Regulation: IMDG (Vessel):
UN1950, AEROSOLS, NON-FLAMMABLE, 2.2, - Limited quantity

Transportation Regulation: IATA (Cargo Air):
UN1950, AEROSOLS, NON-FLAMMABLE, 2.2, - Limited quantity

Transportation Regulation: IATA (Passenger Air):
UN1950, AEROSOLS, NON-FLAMMABLE, 2.2, - Limited quantity

Transportation Regulation: TDG (Canada):
UN1950, AEROSOLS, NON-FLAMMABLE, 2.2, - Limited quantity

SECTION 15. REGULATORY INFORMATION

EPCRA - Emergency Planning and Community Right-to-Know Act

CERCLA Reportable Quantity

Components	CAS-No.	Component RQ (lbs)	Calculated product RQ (lbs)
xylenes	1330-20-7	100	*

*: Calculated RQ exceeds reasonably attainable upper limit.

SARA 304 Extremely Hazardous Substances Reportable Quantity

This material does not contain any components with a section 304 EHS RQ.

SARA 311/312 Hazards : Sudden Release of Pressure Hazard
Acute Health Hazard

SARA 302 : No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

SAFETY DATA SHEET



A00142 MST PAINLESS STAINLESS 20net18

Version 3.0

Revision Date 10/05/2015

Print Date 10/14/2015

SARA 313 : This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

California Prop 65 WARNING! This product contains a chemical known to the State of California to cause cancer.

ethylbenzene 100-41-4
benzene 71-43-2
naphthalene 91-20-3

WARNING: This product contains a chemical known to the State of California to cause birth defects or other reproductive harm.

toluene 108-88-3
benzene 71-43-2

The components of this product are reported in the following inventories:

TSCA On TSCA Inventory
DSL This product contains one or several components that are not on the Canadian DSL nor NDSL.
AICS Not in compliance with the inventory
NZIoC Not in compliance with the inventory
PICCS Not in compliance with the inventory
IECSC Not in compliance with the inventory


Inventory Acronym and Validity Area Legend:

AICS (Australia), DSL (Canada), IECSC (China), REACH (European Union), ENCS (Japan), ISHL (Japan), KECI (Korea), NZIoC (New Zealand), PICCS (Philippines), TCSI (Taiwan), TSCA (USA)

SECTION 16. OTHER INFORMATION

Further information

NFPA:



HMIS III:

HEALTH	3
FLAMMABILITY	1
PHYSICAL HAZARD	2

0 = not significant, 1 =Slight,
2 = Moderate, 3 = High
4 = Extreme, * = Chronic

OSHA GHS Label Information:

SAFETY DATA SHEET



A00142 MST PAINLESS STAINLESS 20net18

Version 3.0

Revision Date 10/05/2015

Print Date 10/14/2015

Hazard pictograms



Signal word

: **Warning:**

Hazard statements

: Contains gas under pressure; may explode if heated. May cause an allergic skin reaction.

Precautionary statements

: **Prevention:** Avoid breathing dust/ fume/ gas/ mist/ vapours/ spray. Contaminated work clothing should not be allowed out of the workplace. Wear protective gloves.

Pressurized container: Do not pierce or burn, even after use.

Response: IF ON SKIN: Wash with plenty of soap and water. If skin irritation or rash occurs: Get medical advice/ attention. Wash contaminated clothing before reuse.

Storage: Protect from sunlight. Store in a well-ventilated place. Do not expose to temperatures exceeding 50 °C/ 122 °F.

Disposal: Dispose of contents/container in accordance with local regulation.

Version:	3.0
Revision Date:	10/05/2015
Print Date:	10/14/2015

We believe the statements, technical information and recommendations contained herein are reliable, but they are given without warranty or guarantee of any kind. The information in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. Users should make their own investigations to determine the suitability and applicability of the information for their particular purposes. This SDS has been prepared by the Compliance Services organization supporting this manufacturer, supplier or distributor.

Zep Inc. markets products under well recognized and established brand names such as Zep®, Zep Commercial®, Zep Professional®, Enforcer®, National Chemical™, Selig™, Misty®, Next Dimension™, Petro®, i-Chem®, TimeMist®, TimeWick™, MicrobeMax®, Country Vet®, Konk®, Original Bike Spirits®, Blue Coral®, Black Magic®, Rain-X®, Niagara National™, FC Forward Chemicals®, Rexodan®, Mykal™, and a number of private labeled brands.