

# Safety Data Sheet

Classified in accordance 29 CFR 1910.1200

## 1. Product Identification

**Product Information:** 1000011192

**Product Identifier:** CLAIRE HEAVY DUTY FOAMING OVEN CLEANER

**Recommended Use:** Cleaner

**Manufacturer/Importer/Distributor Information:** PLZ CORP  
2651 WARRENVILLE RD, STE 300  
DOWNERS GROVE, IL 60515  
US  
800-332-9000

**Emergency Telephone:** 866-836-8855

## 2. Hazard(s) identification

### Classification

Compressed Gas  
Skin Corrosion, category 1A

### Label elements

#### HAZARD PICTOGRAMS



### SIGNAL WORD

Danger

### GHS HAZARD STATEMENTS

H280 Contains gas under pressure; may explode if heated.  
H314 Causes severe skin burns and eye damage.

### GHS PRECAUTIONARY STATEMENTS

#### Prevention

P260 Do not breathe fumes, mists, vapours or spray.  
P264 Wash thoroughly after handling.  
P280 Wear protective gloves, protective clothing, eye protection, and face protection

#### Response

P301+P330+P331+P310 IF SWALLOWED: rinse mouth. Do NOT induce vomiting. Immediately call a POISON CENTER or doctor/physician.  
P303+P361+P353 IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse affected areas with water [or shower].  
P304+P340 IF INHALED: Remove person to fresh air and keep comfortable for breathing.

P305+P351+P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P363	Wash contaminated clothing before reuse.
<b>Storage</b>	
P405	Store locked up.
P410+P403	Protect from sunlight. Store in a well-ventilated place.
<b>Disposal</b>	
P501	Dispose of contents/container to an appropriate treatment and disposal facility in accordance with applicable laws and regulations, and product characteristics at time of disposal.

**Other Information**

None

### 3. Composition/Information on Ingredients

**Mixtures**

<u>Chemical Identity</u>	<u>CAS Number</u>	<u>Content in Percent (%)*</u>
Sodium Hydroxide	1310-73-2	2.5-10
Butane	106-97-8	2.5-10
Diethylene Glycol Monobutyl Ether	112-34-5	2.5-10
Propane	74-98-6	1.0-2.5

\* All concentrations are percent by weight unless ingredient is a gas. Gas concentrations are in percent by volume.

**Composition Comments:** Other components are not hazardous or are below required disclosure limits.

The exact concentration has been withheld as a trade secret.

### 4. First-aid Measures

**SKIN CONTACT:** Wash skin thoroughly with soap and water. If skin irritation occurs: Get medical advice/attention.

**EYE CONTACT:** Any material that contacts the eye should be washed out immediately with water. If easy to do, remove contact lenses. If eye irritation persists: Get medical advice/attention. Immediately flush eyes thoroughly with large quantities of water for at least 20 minutes, while holding the eye lids open to be sure the material is washed out. Remove contact lenses if present and easy to do. Get immediate medical attention.

**INHALATION:** Move to fresh air.

**INGESTION:** Call a POISON CENTER/doctor if you feel unwell. Rinse mouth.

**IMPORTANT SYMPTOMS:** May cause severe eye irritation and burns with possible eye damage.

**INDICATION OF IMMEDIATE MEDICAL ATTENTION AND SPECIAL TREATMENT NEEDED:** Get medical attention if symptoms occur.

### 5. Fire-fighting Measures

**EXTINGUISHING MEDIA:** Use fire-extinguishing media appropriate for surrounding materials.

**UNSUITABLE EXTINGUISHING MEDIA:** Do not use water jet as an extinguisher, as this will spread the fire.

**UNUSUAL FIRE AND EXPLOSION HAZARDS:** Pressurized container may explode when exposed to heat or flame.

**SPECIAL FIREFIGHTING PROCEDURES:** No data available

### 6. Accidental Release Measures

**PERSONAL PRECAUTIONS :** No data available

**METHODS AND MATERIALS FOR CONTAINMENT AND CLEANUP:** Stop the flow of material, if this is without risk. Absorb with sand or other inert absorbent.

**ENVIRONMENTAL PRECAUTIONS:** Avoid release to the environment. Prevent further leakage or spillage if safe to do so. Do not contaminate water sources or sewer. Environmental manager must be informed of all major spillages.

## 7. Handling and Storage

**HANDLING:** Wear personal protective equipment.

**SAFE HANDLING ADVICE:** Observe good industrial hygiene practices.

**STORAGE:** No data available

**NFPA 30B:** Aerosol Level 1

## 8. Exposure Controls/Personal Protection

### Ingredients with Occupational Exposure Limits

<u>Chemical Name</u>	<u>TLV-TWA</u>	<u>TLV-STEL</u>	<u>PEL-TWA</u>	<u>PEL-CEILING</u>
Sodium Hydroxide	N.E.	N.E.	2 mg/m3	2 mg/m3
Butane	N.E.	1000 ppm	N.E.	N.E.
Diethylene Glycol Monobutyl Ether	10 ppm	N.E.	N.E.	N.E.
Propane	N.E.	N.E.	1000 ppm	N.E.

**Further Advice:** MEL = Maximum Exposure Limit OES = Occupational Exposure Standard SUP = Supplier's Recommendation  
 Sk = Skin Sensitizer N.E. = Not Established

**ENGINEERING CONTROLS:** Provide adequate ventilation.

### Personal Protection

**EYE/FACE PROTECTION:** Wear goggles/face shield. Chemical safety goggles and faceshield should be worn where splashing is possible.

**SKIN PROTECTION:** No data available

**RESPIRATORY PROTECTION:** Seek advice from local supervisor. In case of inadequate ventilation use suitable respirator.

**HYGIENIC PRACTICES:** General industrial hygiene practice.

## 9. Physical and Chemical Properties

### Appearance:

Physical State:	Liquid
Form:	Spray Aerosol
Color:	Colorless
Odor:	Glycol
Odor Threshold:	No data available
pH:	12.6 - 13.6
Freeze Point, °C:	No data available
Boiling Point, °C:	105
Flash Point, °C:	No data available
Flammability (solid, gas):	No data available
Evaporation Rate:	No data available
Combustibility:	Supports Combustion
Explosive Limits, %:	No data available
Vapor Pressure @20°C, PSI:	50 - 70
Vapor Density:	No data available
Relative Density:	1.030
Solubility in Water:	No data available
Partition Coefficient, n-octanol/water:	No data available
Auto-Ignition Temperature, °C:	No data available
Decomposition temperature, °C:	No data available
Kinematic Viscosity:	No data available

## 10. Stability and Reactivity

**REACTIVITY:** Not reactive under normal conditions of use.

**STABILITY:** Material is stable under normal conditions.

**POSSIBILITY OF HAZARDOUS REACTIONS:** No data available

**CONDITIONS TO AVOID:** Avoid heat or contamination

**INCOMPATIBILITY:** No data available

**HAZARDOUS DECOMPOSITION PRODUCTS:** No data available

## 11. Toxicological Information

### Information on Likely Routes of Exposure

**SKIN CONTACT EFFECTS:** May cause irritation on prolonged or repeated contact.

**EYE CONTACT EFFECTS:** Exposure to the liquid causes severe eye burns and irreversible damage. Exposure to vapors may cause eye irritation, burning sensation, pain, watering, and vision changes.

**INHALATION EFFECTS:** Inhalation of high concentrations of mists may cause irritation of the nose throat and upper respiratory tract.

**INGESTION EFFECTS:** Ingestion may cause irritation of the mucous membranes, esophagus and stomach.

**Carcinogenicity:** No component of this product present at levels greater than or equal to 0.1% is identified as probable, possible, or confirmed human carcinogen by IARC, ACGIH, NTP or OSHA.

The following values are calculated based on chapter 3.1 of the GHS document. The product itself has not been tested.

<b><u>ATE ORAL</u></b>	29,868 mg/kg
<b><u>ATE DERMAL</u></b>	31,249 mg/kg
<b><u>ATE INHALATION</u></b>	Not classified for acute toxicity based on available data.

#### Acute Toxicity Values

The acute effects of this product have not been tested. Data on individual components are tabulated below

<u>CAS-No.</u>	<u>Chemical Name</u>	<u>Oral LD50</u>	<u>Dermal LD50</u>	<u>Vapor LC50</u>
1310-73-2	Sodium Hydroxide	5000 mg/kg	5000 mg/kg	100 mg/l
106-97-8	Butane	5000 mg/kg	5000 mg/kg	658 mg/L Rat
112-34-5	Diethylene Glycol Monobutyl Ether	2,410 mg/kg	2,764 mg/kg	100 mg/l
74-98-6	Propane	5,000 mg/kg	5,000 mg/kg	100 mg/l

N.I. = No Information

#### Skin Corrosion & Irritation:

<b>Product:</b>	No data available
<b>Components:</b>	
Sodium Hydroxide	1310-73-2 Causes severe skin burns and eye damage.

#### Serious Eye Damage & Irritation:

<b>Product:</b>	No data available
-----------------	-------------------

#### Respiratory or Skin Sensitization:

<b>Product:</b>	No data available
-----------------	-------------------

#### STOT-Single Exposure:

<b>Product:</b>	No data available
-----------------	-------------------

#### STOT-Repeated Exposure:

<b>Product:</b>	No data available
-----------------	-------------------

#### Aspiration Hazard:

<b>Product:</b>	No data available
-----------------	-------------------

#### Carcinogenicity:

<b>Product:</b>	No data available
-----------------	-------------------

#### Reproductive Toxicity:

<b>Product:</b>	No data available
-----------------	-------------------

#### Germ Cell Mutagenicity:

<b>Product:</b>	No data available
-----------------	-------------------

## 12. Ecological Information

**ECOLOGICAL INFORMATION:** No data available

**PERSISTENCE:** No data available

**BIOACCUMULATE:** No data available

**MOBILITY IN SOIL:** No data available

**OTHER ECOLOGICAL:** No data available

### 13. Disposal Information

**DISPOSAL INFORMATION:** Consult with your local, regional and federal agencies for information on proper disposal.

**CONTAMINATED PACKAGING :** Consult with your local, regional and federal agencies for information on proper disposal.

### 14. Transport Information

**SPECIAL TRANSPORT PRECAUTIONS:** No data available

#### DOT

<b>UN Number:</b>	UN1950
<b>Proper Shipping Name:</b>	Aerosols, corrosive, Packing Group II or III
<b>Technical Name:</b>	N/A
<b>Hazard Class(es)</b>	
<b>Class:</b>	2.2
<b>Subsidiary Risk</b>	8
<b>Packing Group:</b>	N/A

#### IATA

<b>UN Number:</b>	UN1950
<b>Proper Shipping Name:</b>	Aerosols, non-flammable, containing substances in Class 8, Packing Group III
<b>Technical Name:</b>	N/A
<b>Hazard Class(es)</b>	
<b>Class:</b>	2.2
<b>Subsidiary Risk:</b>	8
<b>Packing Group:</b>	N/A

#### IMDG

<b>UN Number:</b>	UN1950
<b>Proper Shipping Name:</b>	AEROSOLS, class 8 packing groups II or III
<b>Technical Name:</b>	N/A
<b>Hazard Class(es)</b>	
<b>Class:</b>	2.2
<b>Subsidiary Risk:</b>	8
<b>Packing Group:</b>	N/A

The classification shown in this section may be eligible for use of an exception, such as 'Limited Quantity', per the dangerous goods regulations. The shipper of this product should consult the applicable mode's regulation for the UN number displayed above to determine if any exceptions are available and may be utilized, at the shipper's discretion.

### 15. Regulatory Information

#### CHEMICAL INVENTORY STATUS:

<b>TSCA</b>	On or in compliance with the inventory
<b>DSL</b>	All ingredients in this product are listed on the DSL or are exempt.

#### CALIFORNIA PROPOSITION 65 CARCINOGENS AND REPRODUCTIVE TOXINS:



## WARNING

Warning: This product may contain ingredients known to the state of California to cause Cancer or Reproductive Harm.

<u>Chemical Name</u>	<u>CAS-No.</u>
Ethylene Oxide	75-21-8
Propylene Oxide	75-56-9
1,4-Dioxane	123-91-1

## 16. Other Information

**Revision Date:** 3/1/2023

**Datasheet produced by:** Regulatory Department

### Legend

N/A. - Not Applicable, N.E. - Not Established, N.D. - Not Determined, N.I. - No Information

TLV - Threshold Limit Values (TLVs®), as established by the American Conference of Governmental Industrial Hygienists (ACGIH®)

PEL - Permissible Exposure Limit, as established by the U.S. Occupational Safety and Health Administration (OSHA), as amended

TSCA - U.S. Toxic Substance Control Act

DSL - Canada Environmental Protection Act: Domestic Substance List

This information is provided without warranty. The information is believed to be correct. This information should be used to make an independent determination of the methods to safeguard workers and the environment.

