



Suma Mineral Oil Lubricant

Version Number: 1

Preparation date: 2014-11-19

1. IDENTIFICATION

Product name: Suma Mineral Oil Lubricant
Product Code: 48048
SDS #: MS0800568
Recommended use:

- Industrial/Institutional
- This product is intended to be used neat.

Uses advised against: Uses other than those identified are not recommended

Manufacturer, importer, supplier:

US Headquarters Diversey, Inc. 8310 16th St. Sturtevant, Wisconsin 53177-1964 Phone: 1-888-352-2249 MSDS Internet Address: www.diversey.com	Canadian Headquarters Diversey, Inc. - Canada 3755 Laird Road Mississauga, Ontario L5L 0B3 Phone: 1-800-668-3131
--	--

Emergency telephone number: 1-800-851-7145 (U.S.); 1-651-917-6133 (Int'l)

2. HAZARDS IDENTIFICATION

Classification for the undiluted product

This product is not classified as hazardous according to OSHA 29CFR 1910.1200 (HazCom 2012-GHS) and current Canadian Controlled Products Regulations (CPR).

Precautionary Statements

May be mildly irritating to eyes and skin. In case of contact, immediately flush with plenty of water. If irritation occurs and persists, get medical attention.

Health hazards not otherwise classified (HHNOC) - Not applicable

Physical hazards not otherwise classified (PHNOC) - Not applicable

Classification for the diluted product @ RTU

This product is intended to be used neat.

Precautionary Statements

See undiluted product information above.

3. COMPOSITION/INFORMATION ON INGREDIENTS

Classified Ingredients

None of the components of this product are classified as hazardous according to OSHA 29CFR 1910.1200 (HazCom 2012-GHS) and current Canadian Controlled Products Regulations (CPR)

4. FIRST AID MEASURES

Undiluted Product:

Eyes: In case of contact, immediately flush with plenty of water. If irritation occurs and persists, get medical attention.

Skin: In case of contact, immediately flush with plenty of water. If irritation occurs and persists, get medical attention.

Inhalation: No specific first aid measures are required.

Ingestion: Rinse mouth with water.

Most Important Symptoms/Effects: No information available.

Immediate medical attention and special treatment needed Not applicable.

Diluted Product:

This product is intended to be used neat.

Eyes: See undiluted product information above.

Skin: See undiluted product information above.

Inhalation: See undiluted product information above.

Ingestion: See undiluted product information above.

5. FIRE-FIGHTING MEASURES

Specific methods: No special methods required

Suitable extinguishing media: The product is not flammable. Extinguish fire using agent suitable for surrounding fire.

Specific hazards: Not applicable.

Special protective equipment for firefighters: As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

Extinguishing media which must not be used for safety reasons: No information available.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions: No special measures required.

Environmental precautions and clean-up methods: Clean-up methods - large spillage. Absorb spill with inert material (e.g. dry sand or earth), then place in a chemical waste container. Use a water rinse for final clean-up.

7. HANDLING AND STORAGE

Handling: Wash thoroughly after handling. Do not taste or swallow. Product residue may remain on/in empty containers. All precautions for handling the product must be used in handling the empty container and residue. FOR COMMERCIAL AND INDUSTRIAL USE ONLY.

Storage:

Keep tightly closed in a dry, cool and well-ventilated place.

Aerosol Level (if applicable) : Not applicable

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Exposure Guidelines: This product, as supplied, does not contain any hazardous materials with occupational exposure limits established by the region specific regulatory bodies.

Undiluted Product:

Engineering measures to reduce exposure:

No special ventilation requirements

Personal Protective Equipment

Eye protection: No personal protective equipment required under normal use conditions.

Hand protection: No personal protective equipment required under normal use conditions.

Skin and body protection: No personal protective equipment required under normal use conditions.

Respiratory protection: No personal protective equipment required under normal use conditions.

Hygiene measures: Handle in accordance with good industrial hygiene and safety practice.

Diluted Product:

This product is intended to be used neat.

Personal Protective Equipment

Eye protection:	No personal protective equipment required under normal use conditions.
Hand protection:	No personal protective equipment required under normal use conditions.
Skin and body protection:	No personal protective equipment required under normal use conditions.
Respiratory protection:	No personal protective equipment required under normal use conditions.
Hygiene measures:	Handle in accordance with good industrial hygiene and safety practice.

9. PHYSICAL AND CHEMICAL PROPERTIES:

Physical State: Liquid	Color: Clear Colorless
Evaporation Rate: No information available	Odor: Hydrocarbon
Odor threshold: No information available.	Boiling point/range: Not determined
Melting point/range: Not determined	Decomposition temperature: Not determined
Autoignition temperature: No information available	Solubility: Insoluble
Solubility in other solvents: No information available	Relative Density (relative to water): 0.858
Density: 7.16 lbs/gal 0.858 Kg/L	Vapor density: No information available
Bulk density: No information available	Vapor pressure: No information available.
Flash point: > 200 °F > 93.3 °C	Partition coefficient (n-octanol/water): No information available
Dilution Flash Point: > 200 °F > 93.3 °C	Viscosity: No information available
Elemental Phosphorus: 0.00 % by wt.	VOC: 0 %
pH: No information available	VOC % by wt. at use dilution 0 %
Dilution pH: No information available. @ RTU	Flammability (Solid or Gas): Not applicable
Metal Corrosion: Not determined	
Explosion limits: - upper: Not determined - lower: Not determined	

* - Title 17, California Code of Regulations, Division 3, Chapter 1, Subchapter 8.5, Article 2, Consumer Products, Sections 94508

10. STABILITY AND REACTIVITY

Reactivity:	Not Applicable
Stability:	The product is stable
Hazardous decomposition products:	None reasonably foreseeable.
Materials to avoid:	Do not mix with any other product or chemical unless specified in the use directions.
Conditions to avoid:	No information available.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure:

Skin contact, Inhalation, Eye contact

Delayed, immediate, or chronic effects and symptoms from short and long-term exposure

Skin contact: May be mildly irritating to skin. Symptoms may include redness and/or transient discomfort.

Eye contact: May be mildly irritating to eyes. Symptoms may include redness, watering and/or transient discomfort.

Ingestion: No information available.

Inhalation: No information available.

Sensitization: No known effects.

Numerical measures of toxicity

12. ECOLOGICAL INFORMATION

Ecotoxicity: No information available.

Persistence and Degradability: No information available.

Bioaccumulation: No information available.

13. DISPOSAL CONSIDERATIONS

Waste from residues / unused products: This product, as sold, if discarded or disposed, is not a hazardous waste according to Federal regulations (40 CFR 261.4 (b)(4)). Dispose in compliance with all Federal, state, provincial, and local laws and regulations.

Contaminated Packaging: Do not re-use empty containers.

RCRA Hazard Class (undiluted product): Not Regulated

14. TRANSPORT INFORMATION

DOT/TDG/IMDG: Please refer to the Diversey HazMat Library, only available through Internet Explorer, <http://naextranet.diversey.com/dot/>, for up to date shipping information.

DOT (Ground) Bill of Lading Description: OIL, LUBRICANT, OTHER THAN PETROLEUM

IMDG (Ocean) Bill of Lading Description: OIL, LUBRICANT, OTHER THAN PETROLEUM

15. REGULATORY INFORMATION

International Inventories at CAS# Level

All components of this product are listed on the following inventories: U.S.A. (TSCA), Canada (DSL/NDSL).

U.S. Regulations

California Proposition 65: This product is not subject to the reporting requirements under California's Proposition 65.

RIGHT TO KNOW (RTK)

Ingredient(s)	CAS #	MARTK:	NJRTK:	PARTK:	RIRTK:
White mineral oil	8042-47-5	X	X	-	-

CERCLA/ SARA

SARA 311/312 Hazard Categories

Immediate: -
Delayed: -
Fire: -
Reactivity: -
Sudden Release of Pressure: -

Canadian Regulations

WHMIS hazard class: Non-controlled.

16. OTHER INFORMATION

NFPA (National Fire Protection Association)

Rating Scale: (Low Hazard) 0 - 4 (Extreme Hazard)

Version Number: 1

Preparation date: 2014-11-19

Reason for revision: Not applicable

Prepared by: NAPRAC

Additional advice:

- Does not contain an added fragrance
- This product has been classified in accordance with hazard criteria of the Controlled Products Regulations and the MSDS contains all the information required by the Controlled Products Regulations

Notice to Reader: This document has been prepared using data from sources considered technically reliable. It does not constitute a warranty, express or implied, as to the accuracy of the information contained within. Actual conditions of use and handling are beyond seller's control. User is

responsible to evaluate all available information when using product for any particular use and to comply with all Federal, State, Provincial and Local laws and regulations.