

# INSL-X

## SAFETY DATA SHEET

Revision Date: 24-Mar-2020

Revision Number: 1

### 1. PRODUCT AND COMPANY IDENTIFICATION

**Product Name** INSL-X ALL-PURPOSE CITRUS CLEANER  
**Product Code** CL02-00  
**Alternate Product Code** UA3300  
**Product Class** SURFACE PREPARATION PRODUCT  
**Color** Clear  
**Recommended use** Paint  
**Restrictions on use** No information available

**Manufacturer**  
Benjamin Moore & Co.  
101 Paragon Drive  
Montvale, NJ 07645  
Phone: 1-866-708-9180  
insl-x.com

**Emergency Telephone**  
CHEMTREC (US): 800-424-9300  
CHEMTREC (outside US): (703)-527-3887

### 2. HAZARDS IDENTIFICATION

#### Classification

This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Skin corrosion/irritation	Category 2
Serious eye damage/eye irritation	Category 2A
Skin sensitization	Category 1
Carcinogenicity	Category 1B
Reproductive toxicity	Category 1B
Specific target organ toxicity (repeated exposure)	Category 2
Aspiration toxicity	Category 1

#### Label elements

##### **Danger**

##### **Hazard statements**

Causes skin irritation  
Causes serious eye irritation  
May cause an allergic skin reaction  
May cause cancer  
May damage fertility or the unborn child  
May cause damage to organs through prolonged or repeated exposure  
May be fatal if swallowed and enters airways

**Appearance** liquid**Odor** little or no odor**Precautionary Statements - Prevention**

Obtain special instructions before use  
 Do not handle until all safety precautions have been read and understood  
 Use personal protective equipment as required  
 Wash face, hands and any exposed skin thoroughly after handling  
 Contaminated work clothing should not be allowed out of the workplace  
 Do not breathe dust/fume/gas/mist/vapors/spray  
 Wear protective gloves/protective clothing/eye protection/face protection

**Precautionary Statements - Response**

IF exposed or concerned: Get medical advice/attention

**Eyes**

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do.  
 Continue rinsing

If eye irritation persists: Get medical advice/attention

**Skin**

IF ON SKIN: Wash with plenty of soap and water  
 Take off contaminated clothing and wash before reuse  
 If skin irritation or rash occurs: Get medical advice/attention

**Ingestion**

IF SWALLOWED: Immediately call a POISON CENTER or doctor/physician  
 Do NOT induce vomiting

**Precautionary Statements - Storage**

Store locked up

**Precautionary Statements - Disposal**

Dispose of contents/container to an approved waste disposal plant

**Hazards not otherwise classified (HNOC)**

Not applicable

**Other information**

No information available

### 3. COMPOSITION INFORMATION ON COMPONENTS

Chemical name	CAS No.	Weight-%
D-Limonene	5989-27-5	10 - 15
1-Methyl-2-pyrrolidinone	872-50-4	5 - 10
Diethanolamine	111-42-2	1 - 5

#### 4. FIRST AID MEASURES

<b>General Advice</b>	If symptoms persist, call a physician. Show this safety data sheet to the doctor in attendance.
<b>Eye Contact</b>	Rinse thoroughly with plenty of water for at least 15 minutes and consult a physician.
<b>Skin Contact</b>	Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes. If skin irritation persists, call a physician. Wash clothing before reuse. Destroy contaminated articles such as shoes.
<b>Inhalation</b>	Move to fresh air. If symptoms persist, call a physician.
<b>Ingestion</b>	Clean mouth with water and afterwards drink plenty of water. Consult a physician if necessary.
<b>Most Important Symptoms/Effects</b>	May cause allergic skin reaction.
<b>Notes To Physician</b>	Treat symptomatically.

#### 5. FIRE-FIGHTING MEASURES

<b>Suitable Extinguishing Media</b>	Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
<b>Protective equipment and precautions for firefighters</b>	As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.
<b>Specific Hazards Arising From The Chemical</b>	Closed containers may rupture if exposed to fire or extreme heat.
<b>Sensitivity to mechanical impact</b>	No
<b>Sensitivity to static discharge</b>	No
<b>Flash Point Data</b>	
Flash point (°F)	Not applicable
Flash Point (°C)	Not applicable
Method	Not applicable
<b>Flammability Limits In Air</b>	
Lower flammability limit:	Not applicable
Upper flammability limit:	Not applicable
<b>NFPA</b>	Health: 2      Flammability: 0      Instability: 0      Special: Not Applicable

**NFPA Legend**

- 0 - Not Hazardous
- 1 - Slightly
- 2 - Moderate
- 3 - High
- 4 - Severe

*The ratings assigned are only suggested ratings, the contractor/employer has ultimate responsibilities for NFPA ratings where this system is used.*

*Additional information regarding the NFPA rating system is available from the National Fire Protection Agency (NFPA) at [www.nfpa.org](http://www.nfpa.org).*

**6. ACCIDENTAL RELEASE MEASURES**

<b>Personal Precautions</b>	Avoid contact with skin, eyes and clothing. Ensure adequate ventilation.
<b>Other Information</b>	Prevent further leakage or spillage if safe to do so.
<b>Environmental precautions</b>	See Section 12 for additional Ecological Information.
<b>Methods for Cleaning Up</b>	Soak up with inert absorbent material. Sweep up and shovel into suitable containers for disposal.

**7. HANDLING AND STORAGE**

<b>Handling</b>	Avoid contact with skin, eyes and clothing. Avoid breathing vapors, spray mists or sanding dust. In case of insufficient ventilation, wear suitable respiratory equipment.
<b>Storage</b>	Keep container tightly closed. Keep out of the reach of children.
<b>Incompatible Materials</b>	No information available

**8. EXPOSURE CONTROLS/PERSONAL PROTECTION****Exposure Limits**

Chemical name	ACGIH TLV	OSHA PEL
Diethanolamine	TWA: 1 mg/m <sup>3</sup> inhalable fraction and vapor S*	N/E

**Legend**

ACGIH - American Conference of Governmental Industrial Hygienists Exposure Limits

OSHA - Occupational Safety & Health Administration Exposure Limits

N/E - Not Established

**Engineering Measures**                      Ensure adequate ventilation, especially in confined areas.

**Personal Protective Equipment****Eye/Face Protection**

Safety glasses with side-shields. If splashes are likely to occur, wear: Tightly fitting safety goggles.

**Skin Protection**

Protective gloves and impervious clothing.

**Respiratory Protection**

In operations where exposure limits are exceeded, use a NIOSH approved respirator that has been selected by a technically qualified person for the specific work conditions. When spraying the product or applying in confined areas, wear a

NIOSH approved respirator specified for paint spray or organic vapors.

**Hygiene Measures**

Avoid contact with skin, eyes and clothing. Remove and wash contaminated clothing before re-use. Wash thoroughly after handling.

## 9. PHYSICAL AND CHEMICAL PROPERTIES

<b>Appearance</b>	liquid
<b>Odor</b>	little or no odor
<b>Odor Threshold</b>	No information available
<b>Density (lbs/gal)</b>	8.1 - 8.2
<b>Specific Gravity</b>	0.97 - 0.99
<b>pH</b>	No information available
<b>Viscosity (cps)</b>	No information available
<b>Solubility(ies)</b>	No information available
<b>Water solubility</b>	No information available
<b>Evaporation Rate</b>	No information available
<b>Vapor pressure</b>	No information available
<b>Vapor density</b>	No information available
<b>Wt. % Solids</b>	10 - 20
<b>Vol. % Solids</b>	10 - 20
<b>Wt. % Volatiles</b>	80 - 90
<b>Vol. % Volatiles</b>	80 - 90
<b>VOC Regulatory Limit (g/L)</b>	< 575
<b>VOC Content (% by weight)</b>	< 4.0
<b>Boiling Point (°F)</b>	212
<b>Boiling Point (°C)</b>	100
<b>Freezing point (°F)</b>	32
<b>Freezing Point (°C)</b>	0
<b>Flash point (°F)</b>	Not applicable
<b>Flash Point (°C)</b>	Not applicable
<b>Method</b>	Not applicable
<b>Flammability (solid, gas)</b>	Not applicable
<b>Upper flammability limit:</b>	Not applicable
<b>Lower flammability limit:</b>	Not applicable
<b>Autoignition Temperature (°F)</b>	No information available
<b>Autoignition Temperature (°C)</b>	No information available
<b>Decomposition Temperature (°F)</b>	No information available
<b>Decomposition Temperature (°C)</b>	No information available
<b>Partition coefficient</b>	No information available

## 10. STABILITY AND REACTIVITY

<b>Reactivity</b>	Not Applicable
<b>Chemical Stability</b>	Stable under normal conditions.
<b>Conditions to avoid</b>	Prevent from freezing.
<b>Incompatible Materials</b>	No materials to be especially mentioned.
<b>Hazardous Decomposition Products</b>	None under normal use.

**Possibility of hazardous reactions** None under normal conditions of use.

## 11. TOXICOLOGICAL INFORMATION

### Product Information

#### Information on likely routes of exposure

**Principal Routes of Exposure** Eye contact, skin contact and inhalation.

#### Acute Toxicity

**Product Information** No information available

#### Symptoms related to the physical, chemical and toxicological characteristics

**Symptoms** No information available

#### Delayed and immediate effects as well as chronic effects from short and long-term exposure

<b>Eye contact</b>	May cause slight irritation.
<b>Skin contact</b>	Substance may cause slight skin irritation. Prolonged or repeated contact may dry skin and cause irritation.
<b>Inhalation</b>	May cause irritation of respiratory tract.
<b>Ingestion</b>	Ingestion may cause gastrointestinal irritation, nausea, vomiting and diarrhea.
<b>Sensitization</b>	May cause an allergic skin reaction
<b>Neurological Effects</b>	No information available.
<b>Mutagenic Effects</b>	No information available.
<b>Reproductive Effects</b>	May damage fertility or the unborn child.
<b>Developmental Effects</b>	No information available.
<b>Target organ effects</b>	No information available.
<b>STOT - single exposure</b>	No information available.
<b>STOT - repeated exposure</b>	No information available.
<b>Other adverse effects</b>	No information available.
<b>Aspiration Hazard</b>	No information available

#### Numerical measures of toxicity

The following values are calculated based on chapter 3.1 of the GHS document

<b>ATEmix (oral)</b>	19969 mg/kg
<b>ATEmix (inhalation-dust/mist)</b>	87.1 mg/L

#### Component Information

Chemical name	Oral LD50	Dermal LD50	Inhalation LC50
D-Limonene 5989-27-5	= 5200 mg/kg ( Rat ) = 4400 mg/kg ( Rat )	> 5 g/kg ( Rabbit )	-
1-Methyl-2-pyrrolidinone 872-50-4	= 3914 mg/kg ( Rat )	= 8 g/kg ( Rabbit )	> 5.1 mg/L ( Rat ) 4 h
Diethanolamine 111-42-2	= 780 mg/kg ( Rat ) = 620 µL/kg ( Rat )	= 11.9 mL/kg ( Rabbit ) = 7640 µL/kg ( Rabbit )	-

#### Chronic Toxicity

**Carcinogenicity**

The information below indicates whether each agency has listed any ingredient as a carcinogen..

Chemical name	IARC	NTP	OSHA
D-Limonene	2A - Probable Human Carcinogen		Listed
Diethanolamine	2B - Possible Human Carcinogen		Listed

**Legend**

IARC - International Agency for Research on Cancer

NTP - National Toxicity Program

OSHA - Occupational Safety & Health Administration

## 12. ECOLOGICAL INFORMATION

**Ecotoxicity Effects**

The environmental impact of this product has not been fully investigated.

**Product Information****Acute Toxicity to Fish**

No information available

**Acute Toxicity to Aquatic Invertebrates**

No information available

**Acute Toxicity to Aquatic Plants**

No information available

**Persistence / Degradability**

No information available.

**Bioaccumulation**

There is no data for this product.

**Mobility in Environmental Media**

No information available.

**Ozone**

No information available

**Component Information****Acute Toxicity to Fish**

No information available

**Acute Toxicity to Aquatic Invertebrates**

No information available

**Acute Toxicity to Aquatic Plants**

No information available

### 13. DISPOSAL CONSIDERATIONS

**Waste Disposal Method** Dispose of in accordance with federal, state, and local regulations. Local requirements may vary, consult your sanitation department or state-designated environmental protection agency for more disposal options.

### 14. TRANSPORT INFORMATION

**DOT** Not regulated

**ICAO / IATA** Not regulated

**IMDG / IMO** Not regulated

### 15. REGULATORY INFORMATION

#### International Inventories

**TSCA: United States** Yes - All components are listed or exempt.  
**DSL: Canada** Yes - All components are listed or exempt.

#### Federal Regulations

##### SARA 311/312 hazardous categorization

Acute health hazard	Yes
Chronic Health Hazard	Yes
Fire hazard	No
Sudden release of pressure hazard	No
Reactive Hazard	No

##### SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product contains a chemical or chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372:

<u>Chemical name</u>	<u>CAS No.</u>	<u>Weight-%</u>	<u>CERCLA/SARA 313 (de minimis concentration)</u>
1-Methyl-2-pyrrolidinone	872-50-4	5 - 10	1.0
Diethanolamine	111-42-2	1 - 5	1.0

##### Clean Air Act, Section 112 Hazardous Air Pollutants (HAPs) (see 40 CFR 61)

This product contains the following HAPs:

<u>Chemical name</u>	<u>CAS No.</u>	<u>Weight-%</u>	<u>Hazardous Air Pollutant (HAP)</u>
Diethanolamine	111-42-2	1 - 5	Listed

#### US State Regulations





**Disclaimer**

The information contained herein is presented in good faith and believed to be accurate as of the effective date shown above. This information is furnished without warranty of any kind. Employers should use this information only as a supplement to other information gathered by them and must make independent determination of suitability and completeness of information from all sources to assure proper use of these materials and the safety and health of employees. Any use of this data and information must be determined by the user to be in accordance with applicable federal, provincial, and local laws and regulations.

**End of Safety Data Sheet**