

Revision Date: 14-Aug-2020 Revision Number: 10

1. PRODUCT AND COMPANY IDENTIFICATION

Product Name STIX WATERBORNE BONDING PRIMER WHITE

Product Code SXA-1100

Alternate Product Code XA0501

Product Class Water thinned paint

Color White **Recommended use** Primers

Restrictions on use No information available

Manufacturer

Benjamin Moore & Co. 101 Paragon Drive Montvale, NJ 07645

Phone: 1-866-708-9180 www.benjaminmoore.com/INSLX

Emergency Telephone

CHEMTREC (US): 800-424-9300

CHEMTREC (outside US): (703)-527-3887

2. HAZARDS IDENTIFICATION

Classification

This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Carcinogenicity	Category 1A
Reproductive toxicity	Category 2

Label elements

Danger

Hazard statements

May cause cancer

Suspected of damaging fertility or the unborn child



Appearance liquid Odor little or no odor

Precautionary Statements - Prevention

····-

Revision Date: 14-Aug-2020

Obtain special instructions before use

Do not handle until all safety precautions have been read and understood

Use personal protective equipment as required

Precautionary Statements - Response

IF exposed or concerned: Get medical advice/attention

Precautionary Statements - Storage

Store locked up

Precautionary Statements - Disposal

Dispose of contents/container to an approved waste disposal plant

Hazards not otherwise classified (HNOC)

Not applicable

Other information

No information available

WARNING: This product contains isothiazolinone compounds at levels of <0.1%. These substances are biocides commonly found in most paints and a variety of personal care products as a preservative. Certain individuals may be sensitive or allergic to these substances, even at low levels.

3. COMPOSITION INFORMATION ON COMPONENTS

Chemical name	CAS No.	Weight-%
Talc	14807-96-6	15 - 20
Titanium dioxide	13463-67-7	10 - 15
Dipropylene glycol monomethyl ether	34590-94-8	1 - 5
2,2,4-trimethyl-1,3-pentanediol diisobutyrate	6846-50-0	1 - 5
Silica, crystalline	14808-60-7	0.1 - 0.5

4. FIRST AID MEASURES

General Advice If symptoms persist, call a physician. Show this safety data sheet to the doctor in

attendance.

Eye Contact Rinse thoroughly with plenty of water for at least 15 minutes and consult a

physician.

Skin Contact Wash off immediately with soap and plenty of water while removing all

contaminated clothes and shoes.

Inhalation Move to fresh air. If symptoms persist, call a physician.

Ingestion Clean mouth with water and afterwards drink plenty of water. Consult a physician

if necessary.

Most Important Symptoms/Effects None known.

SXA-1100 - STIX WATERBORNE BONDING PRIMER

WHITE

Notes To Physician Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media

Use extinguishing measures that are appropriate to local

circumstances and the surrounding environment.

Protective equipment and precautions for firefighters As in any fire, wear self-contained breathing apparatus

pressure-demand, MSHA/NIOSH (approved or equivalent)

Revision Date: 14-Aug-2020

and full protective gear.

Specific Hazards Arising From The Chemical Closed containers may rupture if exposed to fire or

extreme heat.

Sensitivity to mechanical impact No

Sensitivity to static discharge No

Flash Point Data

Flash point (°F) Not applicable
Flash Point (°C) Not applicable
Method Not applicable

Flammability Limits In Air

Lower flammability limit:Not applicableUpper flammability limit:Not applicable

NFPA Health: 2 Flammability: 0 Instability: 0 Special: Not Applicable

NFPA Legend

- 0 Not Hazardous
- 1 Slightly
- 2 Moderate
- 3 High
- 4 Severe

The ratings assigned are only suggested ratings, the contractor/employer has ultimate responsibilities for NFPA ratings where this system is used.

Additional information regarding the NFPA rating system is available from the National Fire Protection Agency (NFPA) at www.nfpa.org.

6. ACCIDENTAL RELEASE MEASURES

Personal Precautions Avoid contact with skin, eyes and clothing. Ensure adequate ventilation.

Other Information Prevent further leakage or spillage if safe to do so.

Environmental precautions See Section 12 for additional Ecological Information.

Methods for Cleaning Up Soak up with inert absorbent material. Sweep up and shovel into suitable

containers for disposal.

7. HANDLING AND STORAGE

Handling Avoid contact with skin, eyes and clothing. Avoid breathing vapors, spray mists or

sanding dust. In case of insufficient ventilation, wear suitable respiratory

Revision Date: 14-Aug-2020

equipment.

Storage Keep container tightly closed. Keep out of the reach of children.

Incompatible Materials No information available

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Exposure Limits

Chemical name	ACGIH TLV	OSHA PEL
Talc	TWA: 2 mg/m³ particulate matter	20 mppcf - TWA
	containing no asbestos and <1%	
	crystalline silica, respirable particulate	
	matter	
Titanium dioxide	TWA: 10 mg/m ³	15 mg/m³ - TWA
Dipropylene glycol monomethyl ether	STEL: 150 ppm	100 ppm - TWA
	TWA: 100 ppm	600 mg/m ³ - TWA
	S*	prevent or reduce skin absorption
Silica, crystalline	TWA: 0.025 mg/m³ respirable	50 μg/m ³ - TWA Respirable crystalline
	particulate matter	silica 50 μg/m³ - TWA
		-

Legend

ACGIH - American Conference of Governmental Industrial Hygienists Exposure Limits

OSHA - Occupational Safety & Health Administration Exposure Limits

N/E - Not Established

Engineering Measures Ensure adequate ventilation, especially in confined areas.

Personal Protective Equipment

Eve/Face Protection Safety glasses with side-shields.

Skin Protection Protective gloves and impervious clothing.

Respiratory Protection In operations where exposure limits are exceeded, use a NIOSH approved

respirator that has been selected by a technically qualified person for the specific work conditions. When spraying the product or applying in confined areas, wear a

NIOSH approved respirator specified for paint spray or organic vapors.

Hygiene Measures Avoid contact with skin, eyes and clothing. Remove and wash contaminated

clothing before re-use. Wash thoroughly after handling.

9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance liquid

Odor little or no odor

Odor Threshold No information available

Density (lbs/gal) Specific Gravity11.1 - 11.5 **1**.33 - 1.38

pH No information available Viscosity (cps) No information available

SXA-1100 - STIX WATERBORNE BONDING PRIMER

WHITE

Revision Date: 14-Aug-2020

Solubility(ies)No information availableWater solubilityNo information availableEvaporation RateNo information availableVapor pressureNo information availableVapor densityNo information available

50 - 60 Wt. % Solids 35 - 45 Vol. % Solids Wt. % Volatiles 40 - 50 55 - 65 Vol. % Volatiles **VOC Regulatory Limit (g/L)** < 100 **Boiling Point (°F)** 212 **Boiling Point (°C)** 100 Freezing point (°F) 32 Freezing Point (°C)

Flash point (°F)

Flash Point (°C)

Method

Flammability (solid, gas)

Upper flammability limit:

Lower flammability limit:

Not applicable

Not applicable

Not applicable

Not applicable

Autoignition Temperature (°F)No information availableAutoignition Temperature (°C)No information availableDecomposition Temperature (°F)No information availableDecomposition Temperature (°C)No information availablePartition coefficientNo information available

10. STABILITY AND REACTIVITY

Reactivity Not Applicable

Chemical Stability Stable under normal conditions.

Conditions to avoid Prevent from freezing.

Incompatible Materials No materials to be especially mentioned.

Hazardous Decomposition ProductsNone under normal use.

Possibility of hazardous reactions None under normal conditions of use.

11. TOXICOLOGICAL INFORMATION

Product Information

Information on likely routes of exposure

Principal Routes of Exposure Eye contact, skin contact and inhalation.

Acute Toxicity

Product InformationNo information available

Revision Date: 14-Aug-2020

Symptoms related to the physical, chemical and toxicological characteristics

Symptoms No information available

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Eye contact May cause slight irritation.

Skin contact Substance may cause slight skin irritation. Prolonged or repeated contact may dry

skin and cause irritation.

Inhalation May cause irritation of respiratory tract.

Ingestion Ingestion may cause gastrointestinal irritation, nausea, vomiting and diarrhea.

SensitizationNo information availableNeurological EffectsNo information availableMutagenic EffectsNo information available

Reproductive Effects Possible risk of impaired fertility. Possible risk of harm to the unborn child.

Developmental EffectsNo information available.Target organ effectsNo information available.STOT - single exposureNo information available.

STOT - repeated exposure Causes damage to organs through prolonged or repeated exposure if inhaled.

Other adverse effects
Aspiration Hazard
No information available.
No information available

Numerical measures of toxicity

The following values are calculated based on chapter 3.1 of the GHS document

ATEmix (oral) 55013 mg/kg

Component Information

Chemical name	Oral LD50	Dermal LD50	Inhalation LC50
Titanium dioxide 13463-67-7	> 10000 mg/kg (Rat)	-	-
Dipropylene glycol monomethyl ether 34590-94-8	= 5.35 g/kg(Rat)	= 9500 mg/kg (Rabbit)	-
2,2,4-trimethyl-1,3-pentanediol diisobutyrate 6846-50-0	> 3200 mg/kg (Rat)	-	> 5.3 mg/L (Rat)6 h

Chronic Toxicity

Carcinogenicity

The information below indicates whether each agency has listed any ingredient as a carcinogen:.

Chemical name	IARC	NTP	OSHA
	2B - Possible Human		Listed
Titanium dioxide	Carcinogen		
	1 - Human Carcinogen	Known Human	Listed
Silica, crystalline		Carcinogen	

• Crystalline Silica has been determined to be carcinogenic to humans by IARC (1) when in respirable form. Risk of cancer depends on duration and level of inhalation exposure to spray mist or dust from sanding the dried paint.

• Although IARC has classified titanium dioxide as possibly carcinogenic to humans (2B), their summary concludes: "No significant exposure to titanium dioxide is thought to occur during the use of products in which titanium dioxide is bound to other materials, such as paint."

Revision Date: 14-Aug-2020

Legend

IARC - International Agency for Research on Cancer NTP - National Toxicity Program OSHA - Occupational Safety & Health Administration

12. ECOLOGICAL INFORMATION

Ecotoxicity Effects

The environmental impact of this product has not been fully investigated.

Product Information

Acute Toxicity to Fish

No information available

Acute Toxicity to Aquatic Invertebrates

No information available

Acute Toxicity to Aquatic Plants

No information available

Persistence / Degradability

No information available.

Bioaccumulation

There is no data for this product.

Mobility in Environmental Media

No information available.

Ozone

No information available

Component Information

Acute Toxicity to Fish

Titanium dioxide

LC50: > 1000 mg/L (Fathead Minnow - 96 hr.)

Acute Toxicity to Aquatic Invertebrates

No information available

Acute Toxicity to Aquatic Plants

No information available

13. DISPOSAL CONSIDERATIONS

Waste Disposal Method

Dispose of in accordance with federal, state, and local regulations. Local requirements may vary, consult your sanitation department or state-designated environmental protection agency for more disposal options.

Revision Date: 14-Aug-2020

14. TRANSPORT INFORMATION

DOT Not regulated

ICAO / IATA Not regulated

IMDG / IMO Not regulated

15. REGULATORY INFORMATION

International Inventories

TSCA: United StatesYes - All components are listed or exempt.
Yes - All components are listed or exempt.

Federal Regulations

SARA 311/312 hazardous categorization

Acute health hazard	No
Chronic Health Hazard	Yes
Fire hazard	No
Sudden release of pressure hazard	No
Reactive Hazard	No

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product contains a chemical or chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372:

Chemical name	CAS No.	Weight-%	CERCLA/SARA 313
			(de minimis concentration)
Dipropylene glycol monomethyl ether	34590-94-8	1 - 5	1.0

Clean Air Act, Section 112 Hazardous Air Pollutants (HAPs) (see 40 CFR 61)

This product contains the following HAPs:

Chemical name	CAS No.	Weight-%	Hazardous Air Pollutant
			<u>(HAP)</u>
Dipropylene glycol monomethyl ether	34590-94-8	1 - 5	Listed

US State Regulations

California Proposition 65

MARNING: Cancer and Reproductive Harm– www.P65warnings.ca.gov

Revision Date: 14-Aug-2020

State Right-to-Know

Chemical name	Massachusetts	New Jersey	Pennsylvania
Talc	X	X	X
Titanium dioxide	X	X	X
Magnesium carbonate	X	X	
Dipropylene glycol monomethyl ether	X	X	X
Silica, crystalline	X	X	X

Legend

X - Listed

16. OTHER INFORMATION

HMIS - Health: 2* Flammability: 0 Reactivity: 0 PPE: -

HMIS Legend

- 0 Minimal Hazard
- 1 Slight Hazard
- 2 Moderate Hazard
- 3 Serious Hazard
- 4 Severe Hazard
- * Chronic Hazard
- X Consult your supervisor or S.O.P. for "Special" handling instructions.

Note: The PPE rating has intentionally been left blank. Choose appropriate PPE that will protect employees from the hazards the material will present under the actual normal conditions of use.

Caution: HMIS® ratings are based on a 0-4 rating scale, with 0 representing minimal hazards or risks, and 4 representing significant hazards or risks. Although HMIS® ratings are not required on MSDSs under 29 CFR 1910.1200, the preparer, has chosen to provide them. HMIS® ratings are to be used only in conjunction with a fully implemented HMIS® program by workers who have received appropriate HMIS® training. HMIS® is a registered trade and service mark of the NPCA. HMIS® materials may be purchased exclusively from J. J. Keller (800) 327-6868.

WARNING! If you scrape, sand, or remove old paint, you may release lead dust. LEAD IS TOXIC. EXPOSURE TO LEAD DUST CAN CAUSE SERIOUS ILLNESS, SUCH AS BRAIN DAMAGE, ESPECIALLY IN CHILDREN. PREGNANT WOMEN SHOULD ALSO AVOID EXPOSURE. Wear a NIOSH approved respirator to control lead exposure. Clean up carefully with a HEPA vacuum and a wet mop. Before you start, find out how to protect yourself and your family by contacting the National Lead Information Hotline at 1-800-424-LEAD or log on to www.epa.gov/lead.

Prepared By Product Stewardship Department

Benjamin Moore & Co. 101 Paragon Drive Montvale, NJ 07645

800-225-5554

Revision Date: 14-Aug-2020 **Revision Summary** Not available

Disclaimer

The information contained herein is presented in good faith and believed to be accurate as of the effective date shown above. This information is furnished without warranty of any kind. Employers should use this information only as a

Revision Date: 14-Aug-2020

supplement to other information gathered by them and must make independent determination of suitability and completeness of information from all sources to assure proper use of these materials and the safety and health of employees. Any use of this data and information must be determined by the user to be in accordance with applicable federal, provincial, and local laws and regulations.

End of Safety Data Sheet