



SUMA BIO-FLOOR CLEANER D3.7 A Bacteria Fortified Liquid Floor Cleaner and Deodorizer

Version Number: 1

Preparation date: 2015-09-09

1. IDENTIFICATION

Product name: SUMA BIO-FLOOR CLEANER D3.7 A Bacteria Fortified Liquid Floor Cleaner and Deodorizer
Product Code: 93163905, 100897137, 100897324,
SDS #: MS0800782
Recommended use:

- Industrial/Institutional
- Deodorizing Floor Cleaner
- This product is intended to be diluted prior to use

Uses advised against: Uses other than those identified are not recommended

Manufacturer, importer, supplier:
 US Headquarters
 Sealed Air
 8215 Forest Point Blvd.
 Charlotte, NC 28273-5509
 Phone: 1-888-352-2249
 SDS Internet Address: <https://sds.sealedair.com>

Canadian Headquarters
 Sealed Air - Canada
 3755 Laird Road
 Mississauga, Ontario L5L 0B3
 Phone: 1-800-668-7171

Emergency telephone number: 1-800-851-7145 (U.S.); 1-651-917-6133 (Int'l)

2. HAZARDS IDENTIFICATION

Classification for the undiluted product

Serious eye damage/eye irritation Category 2A
 Specific target organ toxicity (repeated exposure) Category 2

**Signal Word:****Warning.**

Precautionary Statements

MAY CAUSE DAMAGE TO ORGANS THROUGH PROLONGED OR REPEATED EXPOSURE. CAUSES SERIOUS EYE IRRITATION.
 Avoid contact with eyes, skin and clothing. Wash affected areas thoroughly after handling. May cause irritation to mouth, throat and stomach. Wear chemical-splash goggles and chemical-resistant gloves. IF SWALLOWED: Rinse mouth. Drink a cupful of milk or water. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing for at least 15 minutes. If eye irritation persists: Get medical advice or attention. Dispose of in accordance with all federal, state and local applicable regulations.

Health hazards not otherwise classified (HHNOC) - Not applicable

Physical hazards not otherwise classified (PHNOC) - Not applicable

Classification for the diluted product @ 1:32

This product, when diluted as stated on the label, is not classified as hazardous according to OSHA 29CFR 1910.1200 (HazCom 2012-GHS) and Canadian Hazardous Products Regulations (HPR) (WHMIS 2015-GHS).

Precautionary Statements

None required.

3. COMPOSITION/INFORMATION ON INGREDIENTS

Classified Ingredients

Ingredient(s)	CAS #	Weight %
Alcohol ethoxylates	68439-46-3	10 - 20%
Propylene glycol methyl ether	107-98-2	5 - 10%
Alkyl Glucoside	68515-73-1	3% - < 5%
Tetrasodium salt of EDTA	64-02-8	3% - < 5%
Alcohol ethoxylate	68002-97-1	1% - < 3%
Alkyl poly glycoside	110615-47-9	1% - < 3%

*Exact percentages are being withheld as trade secret information

4. FIRST AID MEASURES

Undiluted Product:

Eyes: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing for at least 15 minutes. If eye irritation persists: Get medical advice/attention.

Skin: Rinse with plenty of water. If irritation occurs and persists, get medical attention.

Inhalation: No specific first aid measures are required.

Ingestion: IF SWALLOWED: Rinse mouth. Drink a cupful of milk or water.

Most Important Symptoms/Effects: No information available.

Immediate medical attention and special treatment needed: Not applicable.

Diluted Product:

Eyes: Rinse with plenty of water. If irritation occurs and persists, get medical attention.

Skin: Rinse with plenty of water. If irritation occurs and persists, get medical attention.

Inhalation: No specific first aid measures are required.

Ingestion: Rinse mouth with water.

5. FIRE-FIGHTING MEASURES

Specific methods: No special methods required

Suitable extinguishing media: Not applicable.

Specific hazards: Not applicable.

Special protective equipment for firefighters: As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

Extinguishing media which must not be used for safety reasons: No information available.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions: No information available.

Environmental precautions and clean-up methods: Clean-up methods - large spillage. Absorb spill with inert material (e.g. dry sand or earth), then place in a chemical waste container. Use a water rinse for final clean-up.

7. HANDLING AND STORAGE

Handling: Avoid contact with skin and eyes. Wash thoroughly after handling. Do not taste or swallow. Product residue may remain on/in empty containers. All precautions for handling the product must be used in handling the empty container and residue. FOR COMMERCIAL AND INDUSTRIAL USE ONLY.

Storage: Keep tightly closed in a dry, cool and well-ventilated place.

Aerosol Level (if applicable) : Not applicable

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Exposure Guidelines:

Ingredient(s)	CAS #	ACGIH	OSHA
Alcohol ethoxylates	68439-46-3	-	-
Propylene glycol methyl ether	107-98-2	100 ppm (STEL) 50 ppm (TWA)	-
Alkyl Glucoside	68515-73-1	-	-
Tetrasodium salt of EDTA	64-02-8	-	-
Alcohol ethoxylate	68002-97-1	-	-
Alkyl poly glycoside	110615-47-9	-	-

Undiluted Product:

Engineering measures to reduce exposure:

None known

Personal Protective Equipment

Eye protection:	Chemical-splash goggles.
Hand protection:	Chemical-resistant gloves.
Skin and body protection:	No personal protective equipment required under normal use conditions.
Respiratory protection:	No personal protective equipment required under normal use conditions.
Hygiene measures:	Handle in accordance with good industrial hygiene and safety practice.

Diluted Product:

Personal Protective Equipment

Eye protection:	No personal protective equipment required under normal use conditions.
Hand protection:	No personal protective equipment required under normal use conditions.
Skin and body protection:	No personal protective equipment required under normal use conditions.
Respiratory protection:	No personal protective equipment required under normal use conditions.
Hygiene measures:	Handle in accordance with good industrial hygiene and safety practice.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical State: Liquid

Evaporation Rate: No information available

Odor threshold: No information available.

Melting point/range: Not determined

Autoignition temperature: No information available

Solubility in other solvents: No information available

Density: 8.65 lbs/gal 1.037 Kg/L

Bulk density: No information available

Flash point: > 200 °F > 93.3 °C

Dilution Flash Point: > 200 °F > 93.3 °C

Elemental Phosphorus: 0.00 % by wt.

pH: 9.45

Dilution pH: 10.2 @ 1:32

Metal Corrosion: Not determined

Explosion limits: - upper: Not determined - lower: Not determined

Color: Hazy Light Green Lime

Odor: Surfactant

Boiling point/range: Not determined

Decomposition temperature: Not determined

Solubility: Completely Soluble

Relative Density (relative to water): 1.037

Vapor density: No information available

Vapor pressure: No information available.

Partition coefficient (n-octanol/water): No information available

Viscosity: No information available

VOC: 0 % *

VOC % by wt. at use dilution 0 % *

Flammability (Solid or Gas): Not applicable

* - Title 17, California Code of Regulations, Division 3, Chapter 1, Subchapter 8.5, Article 2, Consumer Products, Sections 94508

10. STABILITY AND REACTIVITY

Reactivity:

Not Applicable

Stability:

The product is stable

Hazardous decomposition products:

None reasonably foreseeable.

Materials to avoid:

Do not mix with any other product or chemical unless specified in the use directions.

Conditions to avoid:

No information available.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure:

Skin contact, Inhalation, Ingestion, Eye contact

Delayed, immediate, or chronic effects and symptoms from short and long-term exposure

Skin contact: May be mildly irritating to skin. Symptoms may include redness and/or transient discomfort.

Eye contact: Causes serious eye irritation. Symptoms may include pain, redness, and watering.

Ingestion: May be irritating to mouth, throat and stomach. Symptoms may include stomach pain and nausea.

Inhalation: May be irritating to nose, throat, and respiratory tract. Symptoms may include coughing and difficulty breathing.

Sensitization: No known effects.

Target Organs (SE): None known

Target Organs (RE): None known

Numerical measures of toxicity

ATE - Oral (mg/kg): 4600

ATE - Inhalatory, mists (mg/l): >20

12. ECOLOGICAL INFORMATION

Ecotoxicity: No information available.

Persistence and Degradability: No information available.

Bioaccumulation: No information available.

13. DISPOSAL CONSIDERATIONS

Waste from residues / unused products: This product, as sold, if discarded or disposed, is not a hazardous waste according to Federal regulations (40 CFR 261.4 (b)(4)). Dispose in compliance with all Federal, state, provincial, and local laws and regulations. This product, when diluted as stated on this SDS, is not a hazardous waste according to Federal regulations (40 CFR 261.4 (b)(4)). Under RCRA, it is the responsibility of the user of the product to determine, at the time of disposal, whether the waste solution meets RCRA criteria for hazardous waste. Dispose in compliance with all Federal, state, provincial, and local laws and regulations.

Contaminated Packaging: Do not re-use empty containers.

RCRA Hazard Class (undiluted product): Not Regulated

RCRA Hazard Class (diluted product): Not Regulated

14. TRANSPORT INFORMATION

DOT/TDG/IMDG: Proper shipping descriptions can vary by pack size. Please refer to the Diversey HazMat Library, **only available through Internet Explorer**, <http://naextranet.diverseyc.com/dot/>, for up to date shipping information.

DOT (Ground) Bill of Lading Description: CLEANING, WASHING, BUFFING, OR POLISHING COMPOUNDS LIQUID

IMDG (Ocean) Bill of Lading Description: CLEANING, WASHING, BUFFING, OR POLISHING COMPOUNDS LIQUID

15. REGULATORY INFORMATION

International Inventories at CAS# Level

All components of this product are listed on the following inventories: U.S.A. (TSCA), Canada (DSL/NDSL).

U.S. Regulations

California Proposition 65: This product is not subject to the reporting requirements under California's Proposition 65.

RIGHT TO KNOW (RTK)

Ingredient(s)	CAS #	MARTK:	NJRTK:	PARTK:	RIRTK:
Water	7732-18-5	-	-	-	-
Alcohol ethoxylates	68439-46-3	-	-	-	-
Propylene glycol methyl ether	107-98-2	X	X	X	-
Alkyl Glucoside	68515-73-1	-	-	-	-
Tetrasodium salt of EDTA	64-02-8	-	-	-	-
Alcohol ethoxylate	68002-97-1	-	-	-	-
Alkyl poly glycoside	110615-47-9	-	-	-	-

CERCLA/ SARA

SARA 311/312 Hazard Categories

Canadian Regulations

16. OTHER INFORMATION

NFPA (National Fire Protection Association)

Rating Scale: (Low Hazard) 0 - 4 (Extreme Hazard)

Health 2

Flammability 0

Instability 0

Version Number: 1

Preparation date: 2015-09-09

Reason for revision: Not applicable

Prepared by: NAPRAC

Notice to Reader: This document has been prepared using data from sources considered technically reliable. It does not constitute a warranty, express or implied, as to the accuracy of the information contained within. Actual conditions of use and handling are beyond seller's control. User is responsible to evaluate all available information when using product for any particular use and to comply with all Federal, State, Provincial and Local laws and regulations.