

INSLX[®]

SAFETY DATA SHEET

Revision Date: 30-Oct-2014

Revision Number: 1

1. PRODUCT AND COMPANY IDENTIFICATION

Product Name TUFFCRETE ACRYLIC EPOXY CLEAR BONDING PRIMER/SEALER CLEAR

Product Code FLB-100
Alternate Product Code TC0110
Product Class WATERBORNE EPOXY
Color Clear
Recommended use Paint
Restrictions on use No information available

Manufacturer Benjamin Moore & Co.
101 Paragon Drive , NJ 07645
Phone: 800-225-5554
insl-x.com

Emergency Telephone Number(s)
CHEMTREC (US): 800-424-9300
CHEMTREC (outside US): (703)-527-3887

2. HAZARDS IDENTIFICATION

Classification

This chemical is not considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.122)

Label elements

Not a dangerous substance or mixture according to the Globally Harmonized System (GHS)

Appearance liquid

Odor little or no odor

Hazards not otherwise classified (HNOC)

Not Applicable

Other information

No information available

3. COMPOSITION INFORMATION ON COMPONENTS

This product contains no hazardous components present at reportable quantities.

4. FIRST AID MEASURES

General Advice	No hazards which require special first aid measures.
Eye Contact	Rinse thoroughly with plenty of water for at least 15 minutes and consult a physician.
Skin Contact	Wash off immediately with soap and plenty of water removing all contaminated clothes and shoes.
Inhalation	Move to fresh air. If symptoms persist, call a physician.
Ingestion	Clean mouth with water and afterwards drink plenty of water. Consult a physician if necessary.
Most Important Symptoms/Effects	No information available.
Notes To Physician	Treat symptomatically

5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media	Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
Protective Equipment And Precautions For Firefighters	As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.
Specific Hazards Arising From The Chemical	Closed containers may rupture if exposed to fire or extreme heat.
Sensitivity To Mechanical Impact	No
Sensitivity To Static Discharge	No
Flash Point Data	
Flash Point (°F)	Not applicable
Flash Point (°C)	Not applicable
Flash Point Method	Not applicable
Flammability Limits In Air	
Lower Explosion Limit	Not applicable
Upper Explosion Limit	Not applicable

NFPA **Health:** 1 **Flammability:** 0 **Instability:** 0 **Special:** Not Applicable

NFPA Legend

- 0 - Not Hazardous
- 1 - Slightly
- 2 - Moderate
- 3 - High
- 4 - Severe

The ratings assigned are only suggested ratings, the contractor/employer has ultimate responsibilities for NFPA ratings where this system is used.

Additional information regarding the NFPA rating system is available from the National Fire Protection Agency (NFPA) at www.nfpa.org.

6. ACCIDENTAL RELEASE MEASURES

Personal Precautions	Avoid contact with skin, eyes and clothing. Ensure adequate ventilation.
Other Information	Prevent further leakage or spillage if safe to do so.
Environmental Precautions	See Section 12 for additional Ecological Information.
Methods For Clean-Up	Soak up with inert absorbent material. Sweep up and shovel into suitable containers for disposal.

7. HANDLING AND STORAGE

Handling	Avoid contact with skin, eyes and clothing. Avoid breathing vapors, spray mists or sanding dust. In case of insufficient ventilation, wear suitable respiratory equipment.
Storage	Keep container tightly closed. Keep out of the reach of children.
Incompatible Materials	No information available

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Exposure Limits	
Engineering Measures	Ensure adequate ventilation, especially in confined areas.
Personal Protective Equipment	
Eye/Face Protection	Safety glasses with side-shields.
Skin Protection	Protective gloves and impervious clothing
Respiratory Protection	In case of insufficient ventilation wear suitable respiratory equipment.
Hygiene Measures	Avoid contact with skin, eyes and clothing. Remove and wash contaminated clothing before re-use. Wash thoroughly after handling.

9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance	liquid
Odor	little or no odor
Odor Threshold	No information available
Density (lbs/gal)	8.3 - 8.6

9. PHYSICAL AND CHEMICAL PROPERTIES

Specific Gravity	0.99 - 1.03
pH	No information available
Viscosity (cps)	No information available
Solubility	No information available
Water Solubility	No information available
Evaporation Rate	No information available
Vapor Pressure	No information available
Vapor Density	No information available
Wt. % Solids	15 - 25
Vol. % Solids	15 - 25
Wt. % Volatiles	75 - 85
Vol. % Volatiles	75 - 85
VOC Regulatory Limit (g/L)	< 340
Boiling Point (°F)	212
Boiling Point (°C)	100
Freezing Point (°F)	32
Freezing Point (°C)	0
Flash Point (°F)	Not applicable
Flash Point (°C)	Not applicable
Flash Point Method	Not applicable
Flammability (solid, gas)	Not applicable
Upper Explosion Limit	Not applicable
Lower Explosion Limit	Not applicable
Autoignition Temperature (°F)	No information available
Autoignition Temperature (°C)	No information available
Decomposition Temperature (°F)	No information available
Decomposition Temperature (°C)	No information available
Partition Coefficient (n-octanol/water)	No information available.

10. STABILITY AND REACTIVITY

Reactivity	Not Applicable
Chemical Stability	Stable under normal conditions.
Conditions To Avoid	Prevent from freezing
Incompatible Materials	No materials to be especially mentioned.
Hazardous Decomposition Products	None under normal use.
Possibility Of Hazardous Reactions	None under normal conditions of use.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure

Product Information

Inhalation	No information available
Eye contact	No information available
Skin contact	No information available
Ingestion	No information available

Acute Toxicity
Product No information available

Information on toxicological effects

Symptoms No information available

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Sensitization:	No information available
Mutagenic Effects	No information available
Reproductive Effects	No information available

Numerical measures of toxicity

Acute Toxicity
Component

Carcinogenicity

There are no known carcinogenic chemicals in this product above reportable levels.

12. ECOLOGICAL INFORMATION

Ecotoxicity Effects

Product

Acute Toxicity to Fish
No information available

Acute Toxicity to Aquatic Invertebrates
No information available

Acute Toxicity to Aquatic Plants
No information available

Persistence / Degradability
No information available

Bioaccumulation / Accumulation
No information available

Mobility in Environmental Media
No information available

Ozone

No information available

Component

Acute Toxicity to Fish

No information available

Acute Toxicity to Aquatic Invertebrates

No information available

Acute Toxicity to Aquatic Plants

No information available

13. DISPOSAL CONSIDERATIONS

Waste Disposal Method

Dispose of in accordance with federal, state, provincial, and local regulations. Local requirements may vary, consult your sanitation department or state-designated environmental protection agency for more disposal options.

14. TRANSPORT INFORMATION

DOT Not regulated

ICAO / IATA Not regulated

IMDG / IMO Not regulated

15. REGULATORY INFORMATION

International Inventories

United States TSCA Yes - All components are listed or exempt.

Canada DSL Yes - All components are listed or exempt.

Federal Regulations

SARA 311/312 hazardous categorization

Acute Health Hazard	No
Chronic Health Hazard	No
Fire Hazard	No
Sudden Release of Pressure Hazard	No
Reactive Hazard	No

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product contains a chemical or chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372:

Clean Air Act, Section 112 Hazardous Air Pollutants (HAPs) (see 40 CFR 61)

This product contains the following HAPs:

None

State Regulations

California Proposition 65

This product may contain small amounts of materials known to the state of California to cause cancer or reproductive harm.

State Right-to-Know

Legend

X - Listed

16. OTHER INFORMATION

HMIS **Health: 1** **Flammability: 0** **Reactivity: 0** **PPE: -**

HMIS Legend

- 0 - Minimal Hazard
- 1 - Slight Hazard
- 2 - Moderate Hazard
- 3 - Serious Hazard
- 4 - Severe Hazard
- * - Chronic Hazard
- X - Consult your supervisor or S.O.P. for "Special" handling instructions.

Note: The PPE rating has intentionally been left blank. Choose appropriate PPE that will protect employees from the hazards the material will present under the actual normal conditions of use.

Caution: HMIS® ratings are based on a 0-4 rating scale, with 0 representing minimal hazards or risks, and 4 representing significant hazards or risks. Although HMIS® ratings are not required on MSDSs under 29 CFR 1910.1200, the preparer, has chosen to provide them. HMIS® ratings are to be used only in conjunction with a fully implemented HMIS® program by workers who have received appropriate HMIS® training. HMIS® is a registered trade and service mark of the NPCA. HMIS® materials may be purchased exclusively from J. J. Keller (800) 327-6868.

WARNING! If you scrape, sand, or remove old paint, you may release lead dust. LEAD IS TOXIC. EXPOSURE TO LEAD DUST CAN CAUSE SERIOUS ILLNESS, SUCH AS BRAIN DAMAGE, ESPECIALLY IN CHILDREN. PREGNANT WOMEN SHOULD ALSO AVOID EXPOSURE. Wear a NIOSH approved respirator to control lead exposure. Clean up carefully with a HEPA vacuum and a wet mop. Before you start, find out how to protect yourself and your family by contacting the National Lead Information Hotline at 1-800-424-LEAD or log on to www.epa.gov/lead.

Prepared By Product Stewardship Department
Benjamin Moore & Co.
101 Paragon Drive
Montvale, NJ 07645
855-724-6802

Revision Date: 30-Oct-2014
Revision Summary Not available

Disclaimer

The information contained herein is presented in good faith and believed to be accurate as of the effective date shown above. This information is furnished without warranty of any kind. Employers should use this information only as a supplement to other information gathered by them and must make independent determination of suitability and completeness of information from all sources to assure proper use of these materials and the safety and health of employees. Any use of this data and information must be determined by the user to be in accordance with applicable federal, provincial, and local laws and regulations.

END OF SAFETY DATA SHEET

INSLX[®]

SAFETY DATA SHEET

Revision Date: 11-Nov-2014

Revision Number: 1

1. PRODUCT AND COMPANY IDENTIFICATION

Product Name LATEX FIRE RETARDANT PAINT WHITE
Product Code LFR-110
Alternate Product Code TC5901
Product Class WATER THINNED PAINT
Color White
Recommended use Paint
Restrictions on use No information available

Manufacturer Benjamin Moore & Co.
101 Paragon Drive , NJ 07645
Phone: 800-225-5554
insl-x.com

Emergency Telephone Number(s)
CHEMTREC (US): 800-424-9300
CHEMTREC (outside US): (703)-527-3887

2. HAZARDS IDENTIFICATION

Classification

Carcinogenicity Category 1A

Label elements

Danger

Hazard statements

May cause cancer



Appearance liquid

Odor little or no odor

Precautionary Statements - Prevention

Obtain special instructions before use
Do not handle until all safety precautions have been read and understood
Use personal protective equipment as required

Precautionary Statements - Response

If exposed or concerned get medical attention

Precautionary Statements - Storage

Store locked up

Precautionary Statements - Disposal

Dispose of contents/container to an approved waste disposal plant

Hazards not otherwise classified (HNOC)

Not Applicable

Other information

No information available

3. COMPOSITION INFORMATION ON COMPONENTS

Chemical Name	CAS-No	Weight % (max)
Titanium dioxide	13463-67-7	10
Distillates, petroleum, solvent-refined heavy paraffinic	64741-88-4	1

4. FIRST AID MEASURES

General Advice	No hazards which require special first aid measures.
Eye Contact	Rinse thoroughly with plenty of water for at least 15 minutes and consult a physician.
Skin Contact	Wash off immediately with soap and plenty of water removing all contaminated clothes and shoes.
Inhalation	Move to fresh air. If symptoms persist, call a physician.
Ingestion	Clean mouth with water and afterwards drink plenty of water. Consult a physician if necessary.
Most Important Symptoms/Effects	No information available.
Notes To Physician	Treat symptomatically

5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media	Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
Protective Equipment And Precautions For Firefighters	As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.
Specific Hazards Arising From The Chemical	Closed containers may rupture if exposed to fire or extreme heat.
Sensitivity To Mechanical Impact	No
Sensitivity To Static Discharge	No
Flash Point Data	

Flash Point (°F) Not applicable
 Flash Point (°C) Not applicable
 Flash Point Method Not applicable

Flammability Limits In Air
 Lower Explosion Limit Not applicable
 Upper Explosion Limit Not applicable

NFPA **Health:** 1 **Flammability:** 0 **Instability:** 0 **Special:** Not Applicable

NFPA Legend

- 0 - Not Hazardous
- 1 - Slightly
- 2 - Moderate
- 3 - High
- 4 - Severe

The ratings assigned are only suggested ratings, the contractor/employer has ultimate responsibilities for NFPA ratings where this system is used. Additional information regarding the NFPA rating system is available from the National Fire Protection Agency (NFPA) at www.nfpa.org.

6. ACCIDENTAL RELEASE MEASURES

Personal Precautions Avoid contact with skin, eyes and clothing. Ensure adequate ventilation.

Other Information Prevent further leakage or spillage if safe to do so.

Environmental Precautions See Section 12 for additional Ecological Information.

Methods For Clean-Up Soak up with inert absorbent material. Sweep up and shovel into suitable containers for disposal.

7. HANDLING AND STORAGE

Handling Avoid contact with skin, eyes and clothing. Avoid breathing vapors, spray mists or sanding dust. In case of insufficient ventilation, wear suitable respiratory equipment.

Storage Keep container tightly closed. Keep out of the reach of children.

Incompatible Materials No information available

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Exposure Limits

Chemical Name	ACGIH	OSHA
Titanium dioxide	10 mg/m ³ - TWA	15 mg/m ³ - TWA
Distillates, petroleum, solvent-refined heavy paraffinic	N/E	N/E

Engineering Measures Ensure adequate ventilation, especially in confined areas.

Personal Protective Equipment

Eye/Face Protection	Safety glasses with side-shields.
Skin Protection	Protective gloves and impervious clothing
Respiratory Protection	In case of insufficient ventilation wear suitable respiratory equipment.

Hygiene Measures

Avoid contact with skin, eyes and clothing. Remove and wash contaminated clothing before re-use. Wash thoroughly after handling.

9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance	liquid
Odor	little or no odor
Odor Threshold	No information available
Density (lbs/gal)	10.7 - 11.0
Specific Gravity	1.28 - 1.32
pH	No information available
Viscosity (cps)	No information available
Solubility	No information available
Water Solubility	No information available
Evaporation Rate	No information available
Vapor Pressure	No information available
Vapor Density	No information available
Wt. % Solids	55 - 65
Vol. % Solids	40 - 50
Wt. % Volatiles	35 - 45
Vol. % Volatiles	50 - 60
VOC Regulatory Limit (g/L)	< 50
Boiling Point (°F)	212
Boiling Point (°C)	100
Freezing Point (°F)	32
Freezing Point (°C)	0
Flash Point (°F)	Not applicable
Flash Point (°C)	Not applicable
Flash Point Method	Not applicable
Flammability (solid, gas)	Not applicable
Upper Explosion Limit	Not applicable
Lower Explosion Limit	Not applicable
Autoignition Temperature (°F)	No information available
Autoignition Temperature (°C)	No information available
Decomposition Temperature (°F)	No information available
Decomposition Temperature (°C)	No information available
Partition Coefficient (n-octanol/water)	No information available.

10. STABILITY AND REACTIVITY

Reactivity	Not Applicable
Chemical Stability	Stable under normal conditions.
Conditions To Avoid	Prevent from freezing

Incompatible Materials	No materials to be especially mentioned.
Hazardous Decomposition Products	None under normal use.
Possibility Of Hazardous Reactions	None under normal conditions of use.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure

Product Information

Inhalation	No information available
Eye contact	No information available
Skin contact	No information available
Ingestion	No information available

Acute Toxicity

Product	No information available
----------------	--------------------------

Information on toxicological effects

Symptoms	No information available
-----------------	--------------------------

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Sensitization:	No information available
Mutagenic Effects	No information available
Reproductive Effects	No information available

Numerical measures of toxicity

The following values are calculated based on chapter 3.1 of the GHS document

ATEmix (oral)	12353 mg/kg
ATEmix (dermal)	13400 mg/kg

Acute Toxicity

Component

Titanium dioxide

LD50 Oral: > 10000 mg/kg (Rat)
 LD50 Dermal: > 10000 mg/m³ (Rabbit)
 LC50 Inhalation (Dust): > 6.82 mg/L (Rat, 4 hr.)

Distillates, petroleum, solvent-refined heavy paraffinic

LD50 Oral: > 5,000 mg/kg (Rat)
 LD50 Dermal: > 2,000 mg/kg
 LC50 Inhalation (Vapor): > 3.9 mg/L (Rat, 4 hr.)

Carcinogenicity

The information below indicates whether each agency has listed any ingredient as a carcinogen:

Chemical Name	IARC	NTP	OSHA Carcinogen
Titanium dioxide	2B - Possible Human Carcinogen		Listed
Distillates, petroleum, solvent-refined heavy paraffinic	1 - Human Carcinogen		

- Although IARC has classified titanium dioxide as possibly carcinogenic to humans (2B), their summary concludes: "No significant exposure to titanium dioxide is thought to occur during the use of products in which titanium dioxide is bound to other materials, such as paint."

Legend

IARC - International Agency for Research on Cancer
 NTP - National Toxicity Program
 OSHA - Occupational Safety & Health Administration

12. ECOLOGICAL INFORMATION

Ecotoxicity Effects

Product

Acute Toxicity to Fish

No information available

Acute Toxicity to Aquatic Invertebrates

No information available

Acute Toxicity to Aquatic Plants

No information available

Persistence / Degradability

No information available

Bioaccumulation / Accumulation

No information available

Mobility in Environmental Media

No information available

Ozone

No information available

Component

Acute Toxicity to Fish

No information available

Titanium dioxide

LC50: >1000 mg/L (Fathead Minnow - 96 hr.)

Acute Toxicity to Aquatic Invertebrates

Acute Toxicity to Aquatic Plants

No information available

13. DISPOSAL CONSIDERATIONS**Waste Disposal Method**

Dispose of in accordance with federal, state, provincial, and local regulations. Local requirements may vary, consult your sanitation department or state-designated environmental protection agency for more disposal options.

14. TRANSPORT INFORMATION

DOT Not regulated

ICAO / IATA Not regulated

IMDG / IMO Not regulated

15. REGULATORY INFORMATION**International Inventories**

United States TSCA Yes - All components are listed or exempt.
Canada DSL Yes - All components are listed or exempt.

Federal Regulations**SARA 311/312 hazardous categorization**

Acute Health Hazard	No
Chronic Health Hazard	Yes
Fire Hazard	No
Sudden Release of Pressure Hazard	No
Reactive Hazard	No

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product contains a chemical or chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372:

Clean Air Act, Section 112 Hazardous Air Pollutants (HAPs) (see 40 CFR 61)

This product contains the following HAPs:

None

State Regulations

California Proposition 65

This product may contain small amounts of materials known to the state of California to cause cancer or reproductive harm.

State Right-to-Know

Chemical Name	Massachusetts	New Jersey	Pennsylvania
Titanium dioxide	X	X	X

Legend

X - Listed

16. OTHER INFORMATION**HMIS** **Health:** 1* **Flammability:** 0 **Reactivity:** 0 **PPE:** -**HMIS Legend**

0 - Minimal Hazard

1 - Slight Hazard

2 - Moderate Hazard

3 - Serious Hazard

4 - Severe Hazard

* - Chronic Hazard

X - Consult your supervisor or S.O.P. for "Special" handling instructions.

Note: The PPE rating has intentionally been left blank. Choose appropriate PPE that will protect employees from the hazards the material will present under the actual normal conditions of use.

Caution: HMIS® ratings are based on a 0-4 rating scale, with 0 representing minimal hazards or risks, and 4 representing significant hazards or risks. Although HMIS® ratings are not required on MSDSs under 29 CFR 1910.1200, the preparer, has chosen to provide them. HMIS® ratings are to be used only in conjunction with a fully implemented HMIS® program by workers who have received appropriate HMIS® training. HMIS® is a registered trade and service mark of the NPCA. HMIS® materials may be purchased exclusively from J. J. Keller (800) 327-6868.

WARNING! If you scrape, sand, or remove old paint, you may release lead dust. LEAD IS TOXIC. EXPOSURE TO LEAD DUST CAN CAUSE SERIOUS ILLNESS, SUCH AS BRAIN DAMAGE, ESPECIALLY IN CHILDREN. PREGNANT WOMEN SHOULD ALSO AVOID EXPOSURE. Wear a NIOSH approved respirator to control lead exposure. Clean up carefully with a HEPA vacuum and a wet mop. Before you start, find out how to protect yourself and your family by contacting the National Lead Information Hotline at 1-800-424-LEAD or log on to www.epa.gov/lead.

Prepared By Product Stewardship Department
Benjamin Moore & Co.
101 Paragon Drive
Montvale, NJ 07645
855-724-6802

Revision Date: 11-Nov-2014
Revision Summary Not available

Disclaimer

The information contained herein is presented in good faith and believed to be accurate as of the effective date shown above. This information is furnished without warranty of any kind. Employers should use this information only as a supplement to other information gathered by them and must make independent determination of suitability and completeness of information from all sources to assure proper use of these materials and the safety and health of employees. Any use of this data and information must be determined by the user to be in accordance with applicable federal, provincial, and local laws and regulations.

END OF SAFETY DATA SHEET