



## All Purpose Virex® Disinfectant Cleaner

Version Number: 4

Preparation date: 2018-07-31

### 1. IDENTIFICATION

**Product name:** All Purpose Virex® Disinfectant Cleaner  
**Product Code:** CBD540533, CBD540540, CBD540557  
**SDS #:** MS0801134  
**Recommended use:** • Disinfectant  
**Uses advised against:** Uses other than those identified are not recommended

**Manufacturer, importer, supplier:**  
 US Headquarters  
 Diversey, Inc.  
 P.O. Box 19747  
 Charlotte, NC 28219-0747  
 Phone: 1-888-352-2249  
 SDS Internet Address: <https://sds.diversey.com>

Canadian Headquarters  
 Diversey Canada, Inc.  
 3755 Laird Road Units 8-11  
 Mississauga, Ontario L5L 0B3  
 Phone: 1-800-668-7171

**Emergency telephone number:** 1-800-851-7145; 1-651-917-6133 (Int'l)

### 2. HAZARDS IDENTIFICATION

#### Classification for the undiluted product

Serious eye damage/eye irritation Category 2A  
 Specific target organ toxicity (repeated exposure) Category 2



**Signal Word:**

**Warning.**

#### Hazard and Precautionary Statements

**CAUSES SERIOUS EYE IRRITATION. MAY CAUSE DAMAGE TO ORGANS THROUGH PROLONGED OR REPEATED EXPOSURE.**

Wash affected areas thoroughly after handling. Wear chemical-splash goggles and chemical-resistant gloves. Do not breathe mist or spray. Get medical attention or advice if you feel unwell. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing for at least 15 minutes. If eye irritation persists: Get medical advice or attention. Dispose of in accordance with all federal, state and local applicable regulations.

**Health hazards not otherwise classified (HHNOC)** - Not applicable

**Physical hazards not otherwise classified (PHNOC)** - Not applicable

### 3. COMPOSITION/INFORMATION ON INGREDIENTS

#### Classified Ingredients

Ingredient(s)	CAS #	Weight %
Diethylene glycol butyl ether	112-34-5	5 - 10%
Tetrasodium salt of EDTA	64-02-8	1 - < 3%

n-Alkyl (60% C14, 30% C16, 5% C12, 5% C18) dimethyl benzyl ammonium chloride	68391-01-5	> 0.1 - < 1%
n-Alkyl (68% C12, 32% C14) dimethyl ethylbenzyl ammonium chloride	68956-79-6	> 0.1 - < 1%

\*Exact percentages are being withheld as trade secret information

#### 4. FIRST AID MEASURES

##### **Undiluted Product:**

**Eyes:** IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing for at least 15 minutes. If eye irritation persists: Get medical advice/attention.

**Skin:** No specific first aid measures are required.

**Inhalation:** No specific first aid measures are required.

**Ingestion:** If large amounts swallowed or symptoms develop, get medical attention.

**Most Important Symptoms/Effects:** Irritation.

**Immediate medical attention and special treatment needed:** Not applicable.

#### 5. FIRE-FIGHTING MEASURES

**Specific methods:**

No special methods required

**Suitable extinguishing media:**

The product is not flammable. Extinguish fire using agent suitable for surrounding fire.

**Specific hazards:**

Not applicable.

**Special protective equipment for firefighters:** As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

**Extinguishing media which must not be used for safety reasons:** No information available.

#### 6. ACCIDENTAL RELEASE MEASURES

**Personal precautions:**

Put on appropriate personal protective equipment (see Section 8.).

**Environmental precautions and clean-up methods:**

Clean-up methods - large spillage. Absorb spill with inert material (e.g. dry sand or earth), then place in a chemical waste container. Use a water rinse for final clean-up.

#### 7. HANDLING AND STORAGE

**Handling:** Avoid contact with skin and eyes. FOR COMMERCIAL AND INDUSTRIAL USE ONLY.

**Storage:** Keep tightly closed in a dry, cool and well-ventilated place.

**Aerosol Level (if applicable):** Not applicable.

#### 8. EXPOSURE CONTROLS / PERSONAL PROTECTION

**Exposure Guidelines:**

This product, as supplied, does not contain any hazardous materials with occupational exposure limits established by the region specific regulatory bodies.

##### **Undiluted Product:**

**Engineering measures to reduce exposure:**

Good general ventilation should be sufficient to control airborne levels.

##### **Personal Protective Equipment**

**Eye protection:**

Safety glasses with side-shields.

**Hand protection:**

No personal protective equipment required under normal use conditions.

**Skin and body protection:**

No personal protective equipment required under normal use conditions.

**Respiratory protection:**

No personal protective equipment required under normal use conditions.

**Hygiene measures:**

Handle in accordance with good industrial hygiene and safety practice.

#### 9. PHYSICAL AND CHEMICAL PROPERTIES

**Physical State:** Liquid  
**Evaporation Rate:** No information available  
**Odor threshold:** No information available.  
**Melting point/range:** Not determined  
**Autoignition temperature:** No information available  
**Solubility in other solvents:** No information available  
**Density:** 8.43 lbs/gal 1.011 Kg/L  
**Bulk density:** No information available  
**Flash point (°F):** > 200 °F > 93.4 °C  
**Viscosity:** 0 cP  
**VOC:** 0 %\*  
**Flammability (Solid or Gas):** Not applicable  
**Sustained combustion:** Not applicable  
**Explosion limits:** - upper: Not determined - lower: Not determined

**Color:** Clear Light Colorless Yellow  
**Odor:** Citrus  
**Boiling point/range:** Not determined  
**Decomposition temperature:** Not determined  
**Solubility:** Completely Soluble  
**Relative Density (relative to water):** 1.011  
**Vapor density:** No information available  
**Vapor pressure:** No information available.  
**Partition coefficient (n-octanol/water):** No information available  
**Elemental Phosphorus:** 0.00 % by wt.  
**pH:** 12.13  
**Corrosion to metals:** Not determined

\* - Title 17, California Code of Regulations, Division 3, Chapter 1, Subchapter 8.5, Article 2, Consumer Products, Sections 94508

## 10. STABILITY AND REACTIVITY

**Reactivity:** Not Applicable  
**Stability:** The product is stable  
**Hazardous decomposition products:** None reasonably foreseeable.  
**Materials to avoid:** Strong acids. Do not mix with any other product or chemical unless specified in the use directions.  
**Conditions to avoid:** Do not freeze. Extremes of temperature and direct sunlight.

## 11. TOXICOLOGICAL INFORMATION

**Information on likely routes of exposure:**  
Skin contact, Inhalation, Eye contact, Ingestion

**Delayed, immediate, or chronic effects and symptoms from short and long-term exposure**

**Skin contact:** May be mildly irritating to skin. Symptoms may include redness and/or transient discomfort.

**Eye contact:** Causes serious eye irritation. Symptoms may include pain, redness, and watering.

**Ingestion:** May be irritating to mouth, throat and stomach. Symptoms may include stomach pain and nausea.

**Inhalation:** May be irritating to nose, throat, and respiratory tract. Symptoms may include coughing and difficulty breathing.

**Sensitization:** No known effects.

**Target Organs (SE):** None known

**Target Organs (RE):** Repeated or prolonged exposure to some of the chemicals in this product may cause damage to the respiratory system

**Numerical measures of toxicity**

**ATE - Oral (mg/kg):** >5000

**ATE - Dermal (mg/kg):** >5000

**ATE - Inhalatory, mists (mg/l):** >20

## 12. ECOLOGICAL INFORMATION

**Ecotoxicity:** No information available.

**Persistence and Degradability:** No information available.

**Bioaccumulation:** No information available.

## 13. DISPOSAL CONSIDERATIONS

Do not contaminate water, food, or feed by storage or disposal.

**Waste from residues / unused products (undiluted product):**

All Purpose Virex® Disinfectant Cleaner

This product, as sold, if discarded or disposed, is not a hazardous waste according to Federal regulations (40 CFR 261.4 (b)(4)). Under RCRA, it is the responsibility of the user of the product to determine, at the time of disposal, whether the waste solution meets RCRA criteria for hazardous waste. Dispose in compliance with all Federal, state, provincial, and local laws and regulations.

**Waste from residues / unused products (diluted product):**

Not applicable.

**Pesticide Storage:**

Store in original container in areas inaccessible to children. Open dumping is prohibited. Do not reuse empty container

**Pesticide Disposal:**

Pesticide wastes are acutely hazardous. Improper disposal of excess pesticide, spray mixture, or rinsate is a violation of Federal Law

**Container Disposal:**

Triple rinse (or equivalent). Then offer for recycling or reconditioning, or puncture and dispose of in a sanitary landfill, or incinerate, or, if allowed by State and local authorities burn. If burned, stay out of smoke

**RCRA Hazard Class (undiluted product):** Not Regulated.

**RCRA Hazard Class (diluted product):** Not Applicable.

## 14. TRANSPORT INFORMATION

**DOT (Ground) Bill of Lading Description:** NOT REGULATED

**IMDG (Ocean) Bill of Lading Description:** NOT REGULATED

## 15. REGULATORY INFORMATION

**International Inventories at CAS# Level**

All components of this product are listed on the following inventories: U.S.A. (TSCA).

**U.S. Regulations**

**EPA Reg. No. :** 1839-83-70627

This chemical is a pesticide product registered by the United States Environmental Protection Agency and is subject to certain labeling requirements under federal pesticide law. These requirements differ from the classification criteria and hazard information required for safety data sheets (SDS), and for workplace labels of non-pesticide chemicals. The hazard information required on the pesticide label is reproduced below. The pesticide label also includes other important information, including directions for use.

CAUTION: KEEP OUT OF REACH OF CHILDREN. Causes moderate eye irritation. Avoid contact with eyes or clothing. Wash thoroughly with soap and water after handling and before eating, drinking, chewing gum, or using tobacco.

**CERCLA/ SARA**

Ingredient(s)	CAS #	Weight %	CERCLA/SARA RQ (lbs)	Section 302 TPQ (lbs)	Section 313
Diethylene glycol butyl ether	112-34-5	5 - 10%			X

Ingredient(s)	CAA HAP	CAA ODS	CWA Priority Pollutants
Diethylene glycol butyl ether	X		

**Canadian Regulations**

Ingredient(s)	CAS #	NPRI
Diethylene glycol butyl ether	112-34-5	X

## 16. OTHER INFORMATION

**NFPA (National Fire Protection Association)**

Rating Scale: (Low Hazard) 0 - 4 (Extreme Hazard)

**Health** 2

**Flammability** 0

**Instability** 0

**Version Number:** 4

**Preparation date:** 2018-07-31

**Reason for revision:** Not applicable  
**Prepared by:** NAPRAC  
**Additional advice:** • Contains an added fragrance, see "Odor" heading in section 9 for specific description

*The information in this document is based on our best present knowledge. However, it does not constitute a guarantee for any specific product features and does not establish a legally binding contract*